

CM 5300  
Countertop coffee machine  
with OneTouch for Two for the ultimate coffee enjoyment.



- Creamy milk froth for coffee specialties – Cappuccinatore
- Perfect results and intense coffee flavor – AromaticSystem
- Two coffees at once at the touch of a button – OneTouch for Two
- Convenient cleaning programs for care and maintenance

EAN: 4002516047612 / Material number: 10969250 / Old Material Number: 29530020USA

Construction type and design	
Countertop bean-to-cup coffee machine	•
Color	Obsidian Black
Convenience features	
AromaticSystem	•
OneTouch preparation	•
One Touch and OneTouch for Two	•
Grinding grade selectable	•
Additional coffee types in ground coffee form possible	•
Ground quantity programmable	•
Water quantity programmable	•
Water temperature programmable	•
Amount of milk can be programmed	•
Amount of milk froth can be programmed	•
Pre-brewing programmable	•
User convenience	
Control panel	DirectSensor
Height adjustment of infinitely adjustable central spout min in in.(cm)	3 1/4 (8.0)
Height adjustment of infinitely adjustable central spout max in in.(cm)	5 3/8 (13.5)
Multilingua	•
No. of bean types	1
No. of bean containers	1
Bean container capacity, each in oz (g)	200
Bean container capacity, total in oz (g)	7.05 (200)
Capacity of water container in fl oz (l)	43.96 (1.3)
Capacity of waste container in servings	6
Drip tray capacity in fl oz (l)	27.05 (0.8)
Easily accessible containers	•
Programmable stand-by time	•
Drink specialties	
Ristretto, single	•
Ristretto, double	•
Espresso, single	•
Espresso, double	•
Coffee, single	•
Coffee, double	•
Long coffee, single	•
Long coffee, double	•
Cappuccino, single	•
Cappuccino, double	•
Latte macchiato, single	•
Latte macchiato, double	•
Hot milk, single	•
Latte macchiato, double	•
Milk froth, single	•
Milk froth, double	•
Caffè latte, single	•
Caffè latte, double	•

CM 5300  
Countertop coffee machine  
with OneTouch for Two for the ultimate coffee enjoyment.



EAN: 4002516047612 / Material number: 10969250 / Old Material Number: 29530020USA

Coffee pot	•
<b>Efficiency and sustainability</b>	
Energy-saving Eco mode option	•
<b>Cleaning convenience</b>	
Manual descaling	•
Automatic rinsing of the milk pipework from the water container	•
Convenient cleaning programs	•
Auto-Off function	•
ComfortClean	•
Removable milk pipework	•
Removable brew unit	•
<b>Safety</b>	
System lock	•
<b>Technical data</b>	
Appliance width in in.(mm)	9 1/2 (241)
Appliance height in in.(mm)	14 1/4 (360)
Appliance depth in in.(mm)	18 1/8 (460)
Total connected load in kW	1.45
Voltage in V	120
Fuse rating in A	15
Number of phases	1
Length of electrical wire in ft (m)	3 (1.2)
<b>Standard accessories</b>	
Descaling tablets	•
Cleaning tablets	•
<b>Available display languages</b>	
Available display languages via MultiLingua	bahasa malaysia, dansk, deutsch, english, español, français, hrvatski, italiano, magyar, nederlands, norsk, polski, portugês, русский, română, slovenčina, slovenščina, srpski, suomi, svenska, türkçe, українська, čeština, ελληνικά, , , ,