## Miele

Classic C1 Pure Suction PowerLine - SBAN0 canister vacuum cleaners
High suction power for thorough vacuuming at an attractive entry level price.



- High suction power 1200 W
- Versatile applications universal floorhead
- Particularly lightweight 13 lbs with vacuuming accessories
- Effortless vacuuming of large areas w/ 29.5 ft operating radius

EAN: 4002516149071 / Material number: 11181020 / Old Material Number: 41BAN045USA

Construction type	
Construction type	
Canister vacuum cleaner with dustbag	Olansia Od
Product line	Classic C1
Motor type	PowerLine
Product type	SBAN0
Appliance color	Graphite grey
Control panel	
Electronic suction power setting	6-stage rotary selector
Ergonomic carrying handle	<u> </u>
Ergonomic handle	<u>•</u>
XXL handle	<u> </u>
Silence system	<u> </u>
Telescopic suction wand	Stainless steel telescopic
	tube
Park system for vacuuming breaks	<u>•</u>
Park system for storage	One side
Efficiency and sustainability	
Nominal power consumption in W	1000
Mobility	
Caster wheels gentle on floors	<u> </u>
Three-point maneuverability	•
Operating radius in ft (m)	29 (9)
Cord length in ft (m)	18 (5.5)
Flat design in in.(mm)	11 (279)
Filter system	
FilterBag type	HyClean GN
FilterBag™ volume in qt (US) (I)	4.8 (4.5) qt (US) (I)
FilterBag™ change indicator	•
Exhaust filter	AirClean filter
Motor protection filter	•
Safety	
Locking system for floorhead and handle	•
Automatic FilterBag™ positioning	•
Technical data	
Max. power in W	1200
Diameter in in. (mm)	18 1/4 (463)
Height in inch (mm)	279
Weight in lbs (kg)	12 (5.2)
Accessories supplied	
Three-piece accessory set	On VarioClip
Upholstery nozzle	•
Crevice nozzle	•
Dusting brush with synthetic bristles	•
Filter	AirClean filter
Cleaning brush	No