Miele

PWM 908 [EL DP]

Professional washing machine, Little Giants, electric heating, drain pump and short program cycle times and programs specific to the target group.



- Drum volume 2.58 (73) ft³ (l), load size 20 (9.0) lb (kg)
- 22% less water consumption and 28% less energy consumption*
- Tested for intensive use unique Miele quality
- Top convenience with full-touch color display M Touch Flex
- Thorough cleaning with professional washing programs

EAN: 4002516229414 / Material number: 11204460 / Old Material Number: 51908159NAM

Construction type and design	
Design	Front-loader, stackable
Product line	Performance Plus
Front	Lotus White
Control panel color	Stainless Steel
Load in lbs	20 (9.0)
Drum volume in cubic feet (I)	2.58 (73)
Door opening [Ø] in in.(mm)	11 13/16 (300)
Door opening angle in degrees	167
Door hinging	right
Maintenance-free synchronous motor	•
Honeycomb drum with perforated rear wall	•
Application	
Suitable for the hotel and catering industry	•
Suitable for senior living facilities	•
Suitable for launderettes	•
Suitable for residential homes and apartments	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centers	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemical industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks and holiday complexes	•
Suitable for public/community care facilities	•
Performance data	
Tested virucidal efficacy	•
Certified hygiene	•
Specific water consumption for cold water connection in	6.10
gal/lb	0.10
Specific energy consumption for cold water connection in	0.12
kWh/lb	52
Specific water consumption for hot water connection in I/kg	5.80
Specific energy consumption for hot water connection in	0.06
kWh/lb	
Water consumption for cold water connection in I	55.0
Energy consumption for cold water connection in kWh	1.10
Program duration in minutes with cold water connection	59
Water consumption for hot water connection in I	52.0
Energy consumption for hot water connection in kW	0.57
Program duration in minutes with hot water connection	49
Residual moisture with cold rinse in %	48
Residual moisture with hot rinse in %	45
Spin speed in rpm	1600
g factor	704
Tested operating hours	30000
1 ootog oporating hours	33300

Based on the Cottons program with a hot water connection, compared to the predecessor model.



PWM 908 [EL DP]

Professional washing machine, Little Giants, electric heating, drain pump and short program cycle times and programs specific to the target group.



EAN: 4002516229414 / Material number: 11204460 / Old Material Number: 51908159NAM

Control	
Control system	M Touch Flex
Programmability	programmable
Max. delay start in h	96
Countdown indicator	•
Program sequence indicator	•
Language can be selected easily at any time	
Dispensing	_
Detergent dispenser drawer	3 compartments
CapDosing	•
Flexible dispensing adapter (option)	•
Maximum number of connections for liquid dispenser	6
pumps [number]	O
Empty sensor	•
Standard electrical connection	
Type of heating	Electric
Electrical connection	2~ 208-240V 60HZ
Heater rating in kW	3.80-5.00
Total connected load in kW	4.00-5.20
Fuse rating in A	30
NEMA plug: Twist Lock L6-30	
Water connection/drainage	
	1x 1/2" hose w/ 3/4" th.
Cold water [number]	union
Hot water [number]	1x 1/2" hose w/ 3/4" th.
Thot water [named]	union
Drain pump	DN 22
Dimensions and weight	
External dimensions, net height in inches	33 1/2 (850)
External dimensions, net width in inches	23 1/2 (596)
External dimensions, net depth in inches	28 1/8 (714)
External dimensions, gross height in inches	37 1/16 (940)
External dimensions, gross width in inches	26 (660)
External dimensions, gross depth in inches	30 1/4 (768)
Net weight in lbs.(kg)	230 (104.0)
Gross weight in lbs.	239 (108)
Maximum floor load in N/m ²	2820
Emission values	
Emissions – sound pressure at workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in BTU/h	1.00
Features	
3-dimensional imbalance monitoring	•
Commercial shock absorber	•
Hard-wearing stainless-steel flange	•
Disinfection rinse	•
EcoSpeed	•
SoftSteam	•
Efficient rib technology	•
Temperature monitoring	`
Special heater element	-
Automatic load control	`
AUTOTTATIC TOAU COTTUO	



PWM 908 [EL DP]

Professional washing machine, Little Giants, electric heating, drain pump and short program cycle times and programs specific to the target group.



EAN: 4002516229414 / Material number: 11204460 / Old Material Number: 51908159NAM

Volumetric flow meter	•
LED drum lighting, class 1	•
Communication slot	•
Add laundry	•
Appliance-independent accessories	•
Efficiency and sustainability	
Recycling rate in %	95
Connection options	
Payment system (optional)	•
Optical interface for service access	•
WiFi Conn@ct	•
Standards, test certificates, and symbols	
CE	•
Splash protection IPX4	•
WEEE	•