

## PDR 908 [EL]

Professional vented dryer, Little Giants, electrically heated  
with extremely short program runtimes. Performance 18 (8.0) lb (kg) in 62 min.



- Drum volume 4.59 (130.00) ft<sup>3</sup> (l), load size 18 (8.0) lb (kg)
- Tested for intensive use – unique Miele quality
- Top convenience with full-touch color display – M Touch Flex
- Precision drying of all fabrics – PerfectDry
- Future-proof networking via WiFi

EAN: 4002516195733 / Material number: 11204510 / Old Material Number: 52908459NAM

Construction type and design	
Design	Front-loader, stackable
Linie	Performance Plus
Front	Stainless Steel
Control panel color	Stainless Steel
Load in lbs.(kg)	18 (8.0)
Drum volume in ft <sup>3</sup> (l)	4.59 (130.00)
Drying system	Exhaust air
Door opening [Ø] in in.(mm)	14 5/8 (370)
Door opening angle in degrees	167
Door hinging	left
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas and fit ness centers	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemical industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks and holiday complexes	•
Performance data	
Maximum evaporation capacity in l/hour and gal. qts./hour	4 (4) gal (US)/min (l)
Specific energy consumption in kWh/kg and kWh/p	0.49
Specific energy consumption for cottons/Normal drying, residual moisture 48% in kWh/kg	0.49
Specific energy consumption for mixed fabric/Normal drying, residual moisture 40% in kWh/kg	0.41
Program cycle in min.	62
Program cycle time for cottons/Normal drying, residual moisture 48% in min.	62
Program cycle time for cottons/Normal drying, residual moisture 40% in min.	57
Control	
Control system	M Touch Flex
Programmability	programmable
Program controls	Residual moisture controlled
Max. delay start in h	24
Countdown indicator	•
Program sequence indicator	•
Language can be selected easily at any time	•
Standard electrical connection	
Type of heating	Electric
Electrical connection	2~208-240V 60HZ

## PDR 908 [EL]

Professional vented dryer, Little Giants, electrically heated  
with extremely short program runtimes. Performance 18 (8.0) lb (kg) in 62 min.



EAN: 4002516195733 / Material number: 11204510 / Old Material Number: 52908459NAM

Electric heater rating in kW	3.03-4.04
Total connected load in kW	3.40-4.30
Fuse rating in A	30
NEMA plug: Twist Lock L6-30	•
<b>Dimensions and weight of dryer</b>	
External dimensions, net height in inches	33 1/2 (850)
External dimensions, net width in inches	23 7/8 (605)
External dimensions, net depth in inches	28 1/4 (717)
External dimensions, gross height in inches	37 1/16 (940)
External dimensions, gross width in inches	26 (660)
External dimensions, gross depth in inches	32 5/16 (820)
Net weight in lbs. (kg)	114 (51.5)
Gross weight in lbs. (kg)	126 (57)
Maximum floor load in N/m <sup>2</sup>	920
<b>Emission values</b>	
Emissions – sound pressure at workplace	<70 dB(A) re 20 µPa
Heat output to the room in MJ/h and BTUs /h	0.76
<b>Features</b>	
Intelligent drum reversal	•
Axial airflow	•
Large-surface filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Communication slot	•
Drum lighting	•
Machine-independent accessories	•
<b>Connection options</b>	
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFiConn@ct	•
<b>Standards, test certificates, and symbols</b>	
WEEE	•
CSA	•
c ETL US	•