

PDR 908 [EL MAR 3 AC 400-480V 50-60Hz]
 Vented dryer, electric heating
 Lloyd's Register approved, load size 18 (8.0) lb (kg).



- Drum volume 4.59 (130.00) ft³ (l), load size 18 (8.0) lb (kg)
- Tested for intensive use – unique Miele quality
- Top convenience with full-touch color display – M Touch Flex
- Precision drying of all fabrics – PerfectDry

EAN: 4002516227953 / Material number: 11250960 / Old Material Number: 52908387MAR

Construction type and design	
Design	Front loader
Linie	Performance Plus
Front	Lotus White
Control panel color	Stainless Steel
Drum volume in ft ³ (l)	4.59 (130.00)
Drying system	Exhaust air
Door opening [Ø] in in.(mm)	14 5/8 (370)
Door opening angle in degrees	167
Door hinging	left
Stainless steel honeycomb drum	Yes
Application	
Suitable for off-shore use	•
Suitable for Marine use	•
Performance data	
Maximum evaporation capacity in l/hour and gal. qts./hour	5 (5) gal (US)/min (l)
Specific energy consumption in kWh/kg an d kWh/p	0.50
Specific energy consumption for cottons/Normal drying, residual moisture 48% in kWh/kg	0.50
Specific energy consumption for mixed fabric/Normal drying, residual moisture 40% in kWh/kg	0.42
Program cycle in min.	52
Program cycle time for cottons/Normal drying, residual moisture 48% in min.	52
Program cycle time for cottons/Normal drying, residual moisture 40% in min.	47
Control	
Control system	M Touch Flex
Programmability	programmable
Program controls	Residual moisture controlled
Max. delay start in h	24
Countdown indicator	•
Program sequence indicator	•
Language can be selected easily at any time	•
Standard electrical connection	
Type of heating	Electric
Electrical connection	3~ 440V 50/60HZ
Electric heater rating in kW	5.16
Total connected load in kW	5.40
Fuse rating in A	10
Possible voltage variant 1	
Electrical connection	3~ 400V 50/60HZ
Heater rating in kW	4.26
Total connected load in kW	4.50
Fuse rating in A	10
Possible voltage variant 2	
Electrical connection	3~ 480V 50/60HZ
Heater rating in kW	6.14
Total connected load in kW	6.40
Fuse rating in A	10

PDR 908 [EL MAR 3 AC 400-480V 50-60Hz]
 Vented dryer, electric heating
 Lloyd's Register approved, load size 18 (8.0) lb (kg).



EAN: 4002516227953 / Material number: 11250960 / Old Material Number: 52908387MAR

Dimensions and weight of dryer	
External dimensions, net height in inches	33 1/2 (850)
External dimensions, net width in inches	23 1/2 (596)
External dimensions, net depth in inches	28 1/4 (717)
External dimensions, gross height in inches	37 1/16 (940)
External dimensions, gross width in inches	26 (660)
External dimensions, gross depth in inches	32 5/16 (820)
Net weight in lbs. (kg)	114 (51.5)
Gross weight in lbs. (kg)	126 (57)
Maximum floor load in N/m ²	920
Emission values	
Emissions – sound pressure at workplace	<70 dB(A) re 20 µPa
Heat output to the room in MJ/h and BTUs /h	0.76
Features	
Intelligent drum reversal	•
Axial airflow	•
Large-surface filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Communication slot	•
Drying basket (optional)	•
Drum lighting	•
Machine-independent accessories	•
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
LAN/WLAN-Modul (Option)	•
WiFiConn@ct	•
Standards, test certificates, and symbols	
CE	•
Splash-proof safety rating IPX4	•
WEEE	•
Lloyd's Register	•
Complies with Machinery Directive 2006/42/EC	•