

PDR 908 [EL MAR 3N AC 400V 50-60Hz]
 Vented dryer, electric heating
 Lloyd's Register approved, load size 18 (8.0) lb (kg).



- Drum volume 4.59 (130.00) ft³ (l), load size 18 (8.0) lb (kg)
- Tested for intensive use – unique Miele quality
- Top convenience with full-touch color display – M Touch Flex
- Precision drying of all fabrics – PerfectDry

EAN: 4002516218463 / Material number: 11251050 / Old Material Number: 52908482MAR

| Construction type and design | |
|---|------------------------------|
| Design | Front loader |
| Linie | Performance Plus |
| Front | Stainless Steel |
| Control panel color | Stainless Steel |
| Drum volume in ft ³ (l) | 4.59 (130.00) |
| Drying system | Exhaust air |
| Door opening [Ø] in in.(mm) | 14 5/8 (370) |
| Door opening angle in degrees | 167 |
| Door hinging | left |
| Stainless steel honeycomb drum | Yes |
| Application | |
| Suitable for off-shore use | • |
| Suitable for Marine use | • |
| Performance data | |
| Maximum evaporation capacity in l/hour and gal. qts./hour | 5.50 |
| Specific energy consumption in kWh/kg and kWh/p | 0.50 |
| Specific energy consumption for cottons/Normal drying, residual moisture 48% in kWh/kg | 0.50 |
| Specific energy consumption for mixed fabric/Normal drying, residual moisture 40% in kWh/kg | 0.42 |
| Program cycle in min. | 42 |
| Program cycle time for cottons/Normal drying, residual moisture 48% in min. | 42 |
| Program cycle time for cottons/Normal drying, residual moisture 40% in min. | 37 |
| Control | |
| Control system | M Touch Flex |
| Programmability | programmable |
| Program controls | Residual moisture controlled |
| Max. delay start in h | 24 |
| Countdown indicator | • |
| Program sequence indicator | • |
| Language can be selected easily at any time | • |
| Standard electrical connection | |
| Type of heating | Electric |
| Electrical connection | 3N~ 400V 50/60HZ |
| Electric heater rating in kW | 6.14 |
| Total connected load in kW | 6.40 |
| Fuse rating in A | 10 |
| Possible voltage variant 1 | |
| Electrical connection | 230V~ 50/60HZ |
| Heater rating in kW | 2.90 |
| Total connected load in kW | 3.24 |
| Fuse rating in A | 16 |
| Possible voltage variant 2 | |
| Electrical connection | 3~ 230V 50/60HZ |
| Heater rating in kW | 6.14 |
| Total connected load in kW | 6.40 |
| Fuse rating in A | 16 |

PDR 908 [EL MAR 3N AC 400V 50-60Hz]
 Vented dryer, electric heating
 Lloyd's Register approved, load size 18 (8.0) lb (kg).



EAN: 4002516218463 / Material number: 11251050 / Old Material Number: 52908482MAR

| Dimensions and weight of dryer | |
|--|---------------------|
| External dimensions, net height in inches | 33 1/2 (850) |
| External dimensions, net width in inches | 23 7/8 (605) |
| External dimensions, net depth in inches | 28 1/4 (717) |
| External dimensions, gross height in inches | 37 1/16 (940) |
| External dimensions, gross width in inches | 26 (660) |
| External dimensions, gross depth in inches | 32 5/16 (820) |
| Net weight in lbs. (kg) | 114 (51.5) |
| Gross weight in lbs. (kg) | 126 (57) |
| Maximum floor load in N/m ² | 920 |
| Emission values | |
| Emissions – sound pressure at workplace | <70 dB(A) re 20 µPa |
| Heat output to the room in MJ/h and BTUs /h | 0.76 |
| Features | |
| Intelligent drum reversal | • |
| Axial airflow | • |
| Large-surface filter | • |
| PerfectDry | • |
| SoftLift drum ribs | • |
| Low temperature function | • |
| Communication slot | • |
| Drying basket (optional) | • |
| Drum lighting | • |
| Machine-independent accessories | • |
| Connection options | |
| Payment system (optional) | • |
| Optical interface for service access | • |
| Peak load cut-out/energy management (optional) | • |
| LAN/WLAN-Modul (Option) | • |
| WiFiConn@ct | • |
| Standards, test certificates, and symbols | |
| CE | • |
| Splash-proof safety rating IPX4 | • |
| WEEE | • |
| Lloyd's Register | • |
| Complies with Machinery Directive 2006/42/EC | • |