

PDR 908 HP [MAR 2 AC 208-240V 60Hz]
 Professional heat-pump dryer
 Lloyd's Register approved, load size 18 (8.0) lb (kg).



- Drum volume 4.59 (130.00) ft³ (l), load size 18 (8.0) lb (kg)
- Tested for intensive use – unique Miele quality
- Top convenience with full-touch color display – M Touch Flex
- Precision drying of all fabrics – PerfectDry

EAN: 4002516218807 / Material number: 11251250 / Old Material Number: 52908289MAR

Construction type and design	
Design	Front loader
Linie	Performance Plus
Front	Stainless Steel
Control panel color	Stainless Steel
Load in lbs.(kg)	18 (8.0)
Drum volume in ft ³ (l)	4.59 (130.00)
Drying system	Heat pump
Door opening [Ø] in in.(mm)	14 5/8 (370)
Door opening angle in degrees	167
Door hinging	left
Stainless steel honeycomb drum	Yes
Application	
Suitable for off-shore use	•
Suitable for Marine use	•
Performance data	
Maximum evaporation capacity in l/hour and gal. qts./hour	3 (3) gal (US)/min (l)
Specific energy consumption in kWh/kg an d kWh/p	0.20
Specific energy consumption for cottons/Normal drying, residual moisture 48% in kWh/kg	0.20
Specific energy consumption for mixed fabric/Normal drying, residual moisture 40% in kWh/kg	0.17
Program cycle in min.	88
Program cycle time for cottons/Normal drying, residual moisture 48% in min.	88
Program cycle time for cottons/Normal drying, residual moisture 40% in min.	76
Control	
Control system	M Touch Flex
Programmability	programmable
Program controls	Residual moisture controlled
Max. delay start in h	24
Countdown indicator	•
Program sequence indicator	•
Language can be selected easily at any time	•
Standard electrical connection	
Type of heating	Heat pump
Electrical connection	2~ 208-240V 60HZ
Total connected load in kW	1.20
Fuse rating in A	15
Dimensions and weight of dryer	
External dimensions, net height in inches	33 1/2 (850)
External dimensions, net width in inches	23 7/8 (605)
External dimensions, net depth in inches	30 5/8 (777)
External dimensions, gross height in inches	37 1/16 (940)
External dimensions, gross width in inches	26 (660)
External dimensions, gross depth in inches	32 5/16 (820)
Net weight in lbs. (kg)	159 (72.0)
Gross weight in lbs. (kg)	172 (78)
Maximum floor load in N/m ²	920

PDR 908 HP [MAR 2 AC 208-240V 60Hz]
 Professional heat-pump dryer
 Lloyd's Register approved, load size 18 (8.0) lb (kg).



EAN: 4002516218807 / Material number: 11251250 / Old Material Number: 52908289MAR

Emission values	
Emissions – sound pressure at workplace	<70 dB(A) re 20 µPa
Heat output to the room in Mj/h and BTUs /h	3.60
Features	
Intelligent drum reversal	•
Axial airflow	•
Fluff filter in the door	•
Low-maintenance heat exchanger filter system	•
PerfectDry	•
SoftLift drum ribs	•
Gentle tumble function	•
Condensed water drainage	•
Communication slot	•
Drying basket (optional)	•
Drum lighting	•
Machine-independent accessories	•
Efficiency and sustainability	
Contains fluorinated greenhouse gases	•
Hermetically sealed system	•
Coolant	R134a
Refrigerant quantity in kg	0.59
Refrigerant global warming potential in kg CO ₂ e	1430
Appliance global warming potential in kg CO ₂ e	844.00
Connection options	
Payment system (optional)	•
Optical interface for service access	•
LAN/WLAN-Modul (Option)	•
Standards, test certificates, and symbols	
WEEE	•
Lloyd's Register	•
Complies with Machinery Directive 2006/42/EC	•