

PWM 908 [EL DP MAR 3 AC 400-480V 50-60Hz]  
 Professional washing machine, Little Giants, electric heating, drain pump  
 Lloyd's Register approved, load size 18 (8.0) lb (kg).



- Drum volume 2.58 (73) ft<sup>3</sup> (l), load size 18 (8.0) lb (kg)
- 22% less water consumption and 28% less energy consumption\*
- Tested for intensive use – unique Miele quality
- Top convenience with full-touch color display – M Touch Flex
- Thorough cleaning with professional washing programs

\* Based on the Cottons program with a hot water connection, compared to the predecessor model.

EAN: 4002516223504 / Material number: 11251290 / Old Material Number: 51908387MAR

<b>Construction type and design</b>	
Design	Front loader
Product line	Performance Plus
Front	Stainless Steel
Control panel color	Stainless Steel
Load in lbs	18 (8.0)
Drum volume in cubic feet (l)	2.58 (73)
Door opening [Ø] in in.(mm)	11 13/16 (300)
Door opening angle in degrees	167
Door hinging	right
Maintenance-free synchronous motor	•
Honeycomb drum with perforated rear wall	•
<b>Application</b>	
Suitable for off-shore use	•
Suitable for Marine use	•
<b>Performance data</b>	
Tested virucidal efficacy	•
Certified hygiene	•
Specific water consumption for cold water connection in gal/lb	6.40
Specific energy consumption for cold water connection in kWh/lb	0.13
Specific water consumption for hot water connection in l/kg	6.00
Specific energy consumption for hot water connection in kWh/lb	0.06
Water consumption for cold water connection in l	51.0
Energy consumption for cold water connection in kWh	1.05
Program duration in minutes with cold water connection	59
Water consumption for hot water connection in l	48.0
Energy consumption for hot water connection in kW	0.50
Program duration in minutes with hot water connection	49
Residual moisture with cold rinse in %	48
Residual moisture with hot rinse in %	45
Spin speed in rpm	1600
g factor	704
Tested operating hours	30000
<b>Control</b>	
Control system	M Touch Flex
Programmability	programmable
Max. delay start in h	96
Countdown indicator	•
Program sequence indicator	•
Language can be selected easily at any time	•
<b>Dispensing</b>	
Detergent dispenser drawer	3 compartments
CapDosing	•
Flexible dispensing adapter (option)	•
Maximum number of connections for liquid dispenser pumps [number]	6
Empty sensor	•

PWM 908 [EL DP MAR 3 AC 400-480V 50-60Hz]  
 Professional washing machine, Little Giants, electric heating, drain pump  
 Lloyd's Register approved, load size 18 (8.0) lb (kg).



EAN: 4002516223504 / Material number: 11251290 / Old Material Number: 51908387MAR

<b>Standard electrical connection</b>	
Type of heating	Electric
Electrical connection	3~ 440V
Heater rating in kW	4.00
Total connected load in kW	4.20
Fuse rating in A	10
<b>Possible voltage variant 1</b>	
Electrical connection	3- 400V
Heater rating in kW	3.40
Total connected load in kW	3.60
Fuse rating in A	10
<b>Possible voltage variant 2</b>	
Electrical connection	3~ 480V 50/60HZ
Heater rating in kW	4.80
Total connected load in kW	5.00
Fuse rating in A	10
<b>Water connection/drainage</b>	
Cold water [number]	1x 1/2" hose w/ 3/4" th. union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union
Drain pump	DN 22
<b>Dimensions and weight</b>	
External dimensions, net height in inches	33 1/2 (850)
External dimensions, net width in inches	23 7/8 (605)
External dimensions, net depth in inches	28 1/8 (714)
External dimensions, gross height in inches	37 1/16 (940)
External dimensions, gross width in inches	26 (660)
External dimensions, gross depth in inches	30 1/4 (768)
Net weight in lbs.(kg)	239 (108.0)
Gross weight in lbs.	247 (112)
Maximum floor load in N/m <sup>2</sup>	2820
<b>Emission values</b>	
Emissions – sound pressure at workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in BTU/h	1.00
<b>Features</b>	
3-dimensional imbalance monitoring	•
Commercial shock absorber	•
Hard-wearing stainless-steel flange	•
Disinfection rinse	•
EcoSpeed	•
SoftSteam	•
Efficient rib technology	•
Temperature monitoring	•
Special heater element	•
Automatic load control	•
Volumetric flow meter	•
LED drum lighting, class 1	•
Communication slot	•
Add laundry	•
Appliance-independent accessories	•

PWM 908 [EL DP MAR 3 AC 400-480V 50-60Hz]  
 Professional washing machine, Little Giants, electric heating, drain pump  
 Lloyd's Register approved, load size 18 (8.0) lb (kg).



EAN: 4002516223504 / Material number: 11251290 / Old Material Number: 51908387MAR

<b>Efficiency and sustainability</b>	
Recycling rate in %	95
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
LAN/WiFi module (optional)	•
WiFi Conn@ct	•
<b>Standards, test certificates, and symbols</b>	
WEEE	•
Lloyd's Register	•
Complies with Machinery Directive 2006/42/EC	•