

PWM 908 [EL DP MAR 2 AC 208-240V 60Hz]

Professional washing machine, Little Giants, electric heating, drain pump

Lloyd's Register approved, load size 18 (8.0) lb (kg).



- Drum volume 2.58 (73) ft³ (l), load size 18 (8.0) lb (kg)
- 22% less water consumption and 28% less energy consumption*
- Tested for intensive use – unique Miele quality
- Top convenience with full-touch color display – M Touch Flex
- Thorough cleaning with professional washing programs

* Based on the Cottons program with a hot water connection, compared to the predecessor model.

EAN: 4002516259732 / Material number: 11251390 / Old Material Number: 51908389MAR

Construction type and design	
Design	Front loader
Product line	Performance Plus
Front	Stainless Steel
Control panel color	Stainless Steel
Load in lbs	18 (8.0)
Drum volume in cubic feet (l)	2.58 (73)
Door opening [Ø] in in.(mm)	11 13/16 (300)
Door opening angle in degrees	167
Door hinging	right
Maintenance-free synchronous motor	•
Honeycomb drum with perforated rear wall	•
Application	
Suitable for off-shore use	•
Suitable for Marine use	•
Performance data	
Tested virucidal efficacy	•
Certified hygiene	•
Specific water consumption for cold water connection in gal/lb	6.40
Specific energy consumption for cold water connection in kWh/lb	0.13
Specific water consumption for hot water connection in l/kg	6.00
Specific energy consumption for hot water connection in kWh/lb	0.06
Water consumption for cold water connection in l	51.0
Energy consumption for cold water connection in kWh	1.05
Program duration in minutes with cold water connection	59
Water consumption for hot water connection in l	48.0
Energy consumption for hot water connection in kW	0.50
Program duration in minutes with hot water connection	49
Residual moisture with cold rinse in %	48
Residual moisture with hot rinse in %	45
Spin speed in rpm	1600
g factor	704
Tested operating hours	30000
Control	
Control system	M Touch Flex
Programmability	programmable
Max. delay start in h	96
Countdown indicator	•
Program sequence indicator	•
Language can be selected easily at any time	•
Dispensing	
Detergent dispenser drawer	3 compartments
CapDosing	•
Flexible dispensing adapter (option)	•
Maximum number of connections for liquid dispenser pumps [number]	6
Empty sensor	•

PWM 908 [EL DP MAR 2 AC 208-240V 60Hz]

Professional washing machine, Little Giants, electric heating, drain pump

Lloyd's Register approved, load size 18 (8.0) lb (kg).



EAN: 4002516259732 / Material number: 11251390 / Old Material Number: 51908389MAR

Standard electrical connection	
Type of heating	Electric
Electrical connection	2~208-240V 60HZ
Heater rating in kW	3.80-5.00
Total connected load in kW	4.00-5.20
Fuse rating in A	30
Water connection/drainage	
Cold water [number]	1x 1/2" hose w/ 3/4" th. union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union
Drain pump	DN 22
Dimensions and weight	
External dimensions, net height in inches	33 1/2 (850)
External dimensions, net width in inches	23 7/8 (605)
External dimensions, net depth in inches	28 1/8 (714)
External dimensions, gross height in inches	37 1/16 (940)
External dimensions, gross width in inches	26 (660)
External dimensions, gross depth in inches	30 1/4 (768)
Net weight in lbs.(kg)	230 (104.0)
Gross weight in lbs.	239 (108)
Maximum floor load in N/m ²	2820
Emission values	
Emissions – sound pressure at workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in BTU/h	1.00
Features	
3-dimensional imbalance monitoring	•
Commercial shock absorber	•
Hard-wearing stainless-steel flange	•
Disinfection rinse	•
EcoSpeed	•
SoftSteam	•
Efficient rib technology	•
Temperature monitoring	•
Special heater element	•
Automatic load control	•
Volumetric flow meter	•
LED drum lighting, class 1	•
Communication slot	•
Add laundry	•
Appliance-independent accessories	•
Efficiency and sustainability	
Recycling rate in %	95
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
LAN/WiFi module (optional)	•
WiFi Conn@ct	•
Standards, test certificates, and symbols	
WEEE	•

PWM 908 [EL DP MAR 2 AC 208-240V 60Hz]

Professional washing machine, Little Giants, electric heating, drain pump

Lloyd's Register approved, load size 18 (8.0) lb (kg).



EAN: 4002516259732 / Material number: 11251390 / Old Material Number: 51908389MAR

Lloyd's Register

Complies with Machinery Directive 2006/42/EC

