

Classic C1 Pure Suction HomeCare PowerLine - SBCNO
canister vacuum cleaners
with comprehensive accessories for nearly every cleaning challenge.



- High suction power – 1200 W
- Versatile applications – universal floorhead
- Particularly lightweight – 13 lbs with vacuuming accessories
- Effortless vacuuming of large areas w/ 29.5 ft operating radius
- Maximum air hygiene with HEPA filter: *Ideal for allergy sufferers

* According to EN 60312-1

EAN: 4002516199953 / Material number: 11262170 /
Old Material Number: 41BCN035USA

Design	
Canister vacuum cleaner with dustbag	•
Product line	Classic C1
Motor type	PowerLine
Product type	SBCNO
Appliance color	Autumn red
User convenience	
Electronic suction power setting	6-stage rotary selector
Ergonomic carrying handle	•
Ergonomic handle	•
XXL handle	•
Silence system	•
Telescopic suction wand	Stainless steel telescopic wand
Park system for vacuuming breaks	•
Park system for storage	on one side
Mobility	
Caster wheels gentle on floors	•
Three-point maneuverability	•
Operating radius in ft (m)	29 (9)
Cord length in ft (m)	18 (5.5)
Filter system	
FilterBag type	HyClean GN
FilterBag™ volume in qt (US) (l)	4.8 (4.5) qt (US) (l)
FilterBag™ change indicator	•
Exhaust filter	HEPA AirClean filter
Motor protection filter	•
Safety	
Locking system for floorhead and handle	•
Automatic FilterBag™ positioning	•
Technical data	
Power	1200
Width in inches (mm)	18 1/4 (463)
Height in inch (mm)	279
Weight in lbs (kg)	12 (5.2)
Standard accessories	
Three-piece accessory set	On VarioClip
Upholstery nozzle	•
Crevice nozzle	•
Dusting brush with synthetic bristles	•
Floorhead	•