

PWM 507 [EL DP MAR 1N AC 230 V 60Hz]

Professional washing machine, Little Giants, electric heating, drain pump

Lloyd's Register approved, load size 16 (7.0) lb (kg).



- Drum volume 2.26 (64) ft<sup>3</sup> (l), load size 16 (7.0) lb (kg)
- 22% less water consumption and 28% less energy consumption\*
- Tested for intensive use – unique Miele quality
- Language-neutral fascia with selector dial – M Select
- Thorough cleaning with professional washing programs

\* Based on the Cottons program with a hot water connection, compared to the predecessor model.

EAN: 4002516296638 / Material number: 11300950 / Old Material Number: 51507185MAR

## Construction type and design

Design	Front loader
Product line	Performance
Front	Lotus White
Control panel color	Stainless Steel
Load in lbs	16 (7.0)
Drum volume in cubic feet (l)	2.26 (64)
Door opening [Ø] in in.(mm)	11 13/16 (300)
Door opening angle in degrees	167
Door hinging	right
Maintenance-free synchronous motor	•
Honeycomb drum with perforated rear wall	•

## Application

Suitable for off-shore use	•
Suitable for Marine use	•

## Performance data

Tested virucidal efficacy	•
Certified hygiene	•
Specific water consumption for cold water connection in gal/lb	7.00
Specific energy consumption for cold water connection in kWh/lb	0.14
Specific energy consumption for hot water connection in kWh/lb	0.06
Water consumption for cold water connection in l	49.0
Energy consumption for cold water connection in kWh	0.98
Program duration in minutes with cold water connection	69
Water consumption for hot water connection in l	46.0
Energy consumption for hot water connection in kW	0.44
Program duration in minutes with hot water connection	59
Residual moisture with cold rinse in %	48
Residual moisture with hot rinse in %	45
Spin speed in rpm	1600
g factor	704
Tested operating hours	30000

## Control

Control system	M Select
Programmability	programmable
Max. delay start in h	24
Countdown indicator	•
Program sequence indicator	•
Fascia panel with easy-to-understand symbols	•
Language can be selected easily at any time	•

## Dispensing

Detergent dispenser drawer	3 compartments
CapDosing	•
Flexible dispensing adapter (option)	•
Maximum number of connections for liquid dispenser pumps [number]	6
Empty sensor	•

PWM 507 [EL DP MAR 1N AC 230 V 60Hz]

Professional washing machine, Little Giants, electric heating, drain pump

Lloyd's Register approved, load size 16 (7.0) lb (kg).



EAN: 4002516296638 / Material number: 11300950 / Old Material Number: 51507185MAR

<b>Standard electrical connection</b>	
Type of heating	Electric
Electrical connection	230V~ 60HZ
Heater rating in kW	2.65
Total connected load in kW	2.85
Fuse rating in A	16
<b>Possible voltage variant 1</b>	
Electrical connection	230V~
Heater rating in kW	2.65
Total connected load in kW	2.85
Fuse rating in A	16
<b>Water connection/drainage</b>	
Cold water [number]	1x 1/2" hose w/ 3/4" th. union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union
Drain pump	DN 22
<b>Dimensions and weight</b>	
External dimensions, net height in inches	33 1/2 (850)
External dimensions, net width in inches	23 1/2 (596)
External dimensions, net depth in inches	28 1/8 (714)
External dimensions, gross height in inches	37 3/16 (944)
External dimensions, gross width in inches	26 (660)
External dimensions, gross depth in inches	30 1/4 (768)
Net weight in lbs.(kg)	217 (98.0)
Gross weight in lbs.	225 (102)
Maximum floor load in N/m <sup>2</sup>	2820
<b>Emission values</b>	
Emissions – sound pressure at workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in BTU/h	1.00
<b>Features</b>	
3-dimensional imbalance monitoring	•
Commercial shock absorber	•
Hard-wearing stainless-steel flange	•
Disinfection rinse	•
EcoSpeed	•
SoftSteam	•
Efficient rib technology	•
Temperature monitoring	•
Special heater element	•
Automatic load control	•
Volumetric flow meter	•
LED drum lighting, class 1	•
Communication slot	•
Add laundry	•
Appliance-independent accessories	•
<b>Efficiency and sustainability</b>	
Recycling rate in %	95
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•

PWM 507 [EL DP MAR 1N AC 230 V 60Hz]

Professional washing machine, Little Giants, electric heating, drain pump

Lloyd's Register approved, load size 16 (7.0) lb (kg).



EAN: 4002516296638 / Material number: 11300950 / Old Material Number: 51507185MAR

Peak load cut-out/energy management (optional)

•

WiFi Conn@ct

•

**Standards, test certificates, and symbols**

WEEE

•

Lloyd's Register

•

Complies with Machinery Directive 2006/42/EC

•