

PWM 507 [EL DP MAR 3 AC 400-480V 50-60Hz]
 Professional washing machine, Little Giants, electric heating, drain pump
 Lloyd's Register approved, load size 16 (7.0) lb (kg).



- Drum volume 2.26 (64) ft³ (l), load size 16 (7.0) lb (kg)
- 22% less water consumption and 28% less energy consumption*
- Tested for intensive use – unique Miele quality
- Language-neutral fascia with selector dial – M Select
- Thorough cleaning with professional washing programs

* Based on the Cottons program with a hot water connection, compared to the predecessor model.

EAN: 4002516264545 / Material number: 11300960 / Old Material Number: 51507187MAR

Construction type and design	
Design	Front loader
Product line	Performance
Front	Lotus White
Control panel color	Stainless Steel
Load in lbs	16 (7.0)
Drum volume in cubic feet (l)	2.26 (64)
Door opening [Ø] in in.(mm)	11 13/16 (300)
Door opening angle in degrees	167
Door hinging	right
Maintenance-free synchronous motor	•
Honeycomb drum with perforated rear wall made of stainless steel	•
Application	
Suitable for off-shore use	•
Suitable for Marine use	•
Performance data	
Tested virucidal efficacy	•
Certified hygiene	•
Specific water consumption for cold water connection in gal/lb	7.00
Specific energy consumption for cold water connection in kWh/lb	0.14
Specific water consumption for hot water connection in l/kg	6.60
Specific energy consumption for hot water connection in kWh/lb	0.06
Water consumption for cold water connection in l	49.0
Energy consumption for cold water connection in kWh	0.98
Program duration in minutes with cold water connection	59
Water consumption for hot water connection in l	46.0
Energy consumption for hot water connection in kW	0.44
Program duration in minutes with hot water connection	49
Residual moisture with cold rinse in %	48
Residual moisture with hot rinse in %	45
Spin speed in rpm	1600
g factor	704
Tested operating hours	30000
Control	
Control system	M Select
Programmability	programmable
Max. delay start in h	24
Countdown indicator	•
Program sequence indicator	•
Fascia panel with easy-to-understand symbols	•
Language can be selected easily at any time	•
Dispensing	
Detergent dispenser drawer	3 compartments
CapDosing	•
Flexible dispensing adapter (option)	•
Maximum number of connections for liquid dispenser pumps [number]	6

PWM 507 [EL DP MAR 3 AC 400-480V 50-60Hz]
 Professional washing machine, Little Giants, electric heating, drain pump
 Lloyd's Register approved, load size 16 (7.0) lb (kg).



EAN: 4002516264545 / Material number: 11300960 / Old Material Number: 51507187MAR

Empty sensor	•
Standard electrical connection	
Type of heating	Electric
Electrical connection	3~ 440V
Heater rating in kW	4.00
Total connected load in kW	4.20
Fuse rating in A	10
Possible voltage variant 1	
Electrical connection	3~ 400V
Heater rating in kW	3.40
Total connected load in kW	3.60
Fuse rating in A	10
Possible voltage variant 2	
Electrical connection	3~ 480V 50/60HZ
Heater rating in kW	4.80
Total connected load in kW	5.00
Fuse rating in A	10
Water connection/drainage	
Cold water [number]	1x 1/2" hose w/ 3/4" th. union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union
Drain pump	DN 22
Dimensions and weight	
External dimensions, net height in inches	33 1/2 (850)
External dimensions, net width in inches	23 1/2 (596)
External dimensions, net depth in inches	28 1/8 (714)
External dimensions, gross height in inches	37 3/16 (944)
External dimensions, gross width in inches	26 (660)
External dimensions, gross depth in inches	30 1/4 (768)
Net weight in lbs.(kg)	217 (98.0)
Gross weight in lbs.	225 (102)
Maximum floor load in N	2820
Emission values	
Emissions – sound pressure at workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in BTU/h	1.00
Features	
3-dimensional imbalance monitoring	•
Commercial shock absorber	•
Hard-wearing stainless-steel flange	•
Disinfection rinse	•
EcoSpeed	•
SoftSteam	•
Efficient rib technology	•
Temperature monitoring	•
Special heater element	•
Automatic load control	•
Volumetric flow meter	•
LED drum lighting, class 1	•
Communication slot	•
Add laundry	•

PWM 507 [EL DP MAR 3 AC 400-480V 50-60Hz]
 Professional washing machine, Little Giants, electric heating, drain pump
 Lloyd's Register approved, load size 16 (7.0) lb (kg).



EAN: 4002516264545 / Material number: 11300960 / Old Material Number: 51507187MAR

Appliance-independent accessories	•
Efficiency and sustainability	
Recycling rate in %	95
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak-load negotiation / energy management (optional)	•
WiFi Conn@ct	•
Standards, test certificates, and symbols	
WEEE	•
Lloyd's Register	•
Complies with Machinery Directive 2006/42/EC	•