

DU 900 RV

Drying unit, with ventilation slots, electric

For machines 35 7/8" (900 mm) wide & optimum internal & external drying of items.

EAN: 4002516265177 / Material number: 11382320 / Old Material Number: 69250006USA



- With top-box paneling; air supply via the room.
- Includes 2 x H14 HEPA filters
- Maximum safety – HEPA filter directly in front of wash cabinet
- Air flow rate 147 cfm/250 m³/h
- HEPA filter service life: 1,000 hours

| | |
|--|---------------|
| Product category | |
| Large-capacity washer-disinfectors, laboratory | • |
| Machine affiliation | |
| PLW 8615 | • |
| PLW 8616 | • |
| Dimensions and weight | |
| External dimensions, net height in inches | 840 |
| External dimensions, net width in inches | 845 |
| External dimensions, net depth in inches | 1045 |
| External dimensions, gross height in inches | 39 (990) |
| External dimensions, gross width in inches | 33 3/8 (845) |
| External dimensions, gross depth in inches | 47 1/4 (1200) |
| Net weight in lbs | 256 (116.00) |
| Gross weight in lbs | 294 (133.00) |