

DU 1150 RV

Drying unit, with ventilation slots, electric

For machines 45 1/4" (1150 mm) wide & optimum int. & ext. drying of wash items.

EAN: 4002516265184 / Material number: 11382350 / Old Material Number: 69250007USA



- With top-box paneling; air supply via the room.
- Includes 2 x H14 HEPA filters
- Maximum safety – HEPA filter directly in front of wash cabinet
- Air flow rate 147 cfm/250 m³/h
- HEPA filter service life: 1,000 hours

Product category	
Large-capacity washer-disinfectors, laboratory	•
Machine affiliation	
PLW 8617	•
Dimensions and weight	
External dimensions, net height in inches	855
External dimensions, net width in inches	850
External dimensions, net depth in inches	1190
External dimensions, gross height in inches	39 7/8 (1010)
External dimensions, gross width in inches	33 1/2 (850)
External dimensions, gross depth in inches	47 1/4 (1200)
Net weight in lbs	265 (120.00)
Gross weight in lbs	303 (137.00)