


G 7156 SCVi XXL

Fully integrated dishwashers
with 3D MultiFlex Tray for maximum convenience.



- QuickIntenseWash, superior cleaning and drying in under 60 min
- Everything completely dry – AutoOpen drying
- Fresh water dishwashers – from ?? in the Automatic program
- Very easy door opening and closing – ComfortClose
- Versatile and secure – ExtraComfort basket design

EAN: 4002516261452 / Material number: 11387590 / Old Material Number: 21715662USA

Type	
Fully integrated dishwashers	•
24 inch dishwasher	•
Design	
Fascia color	Stainless Steel.
Fascia panel version	Fully integrated fascia
Control type	Programme selector button
Control panel	1-line display with plain text
Display color	White
MultiLingua	•
Convenience	
Door closing aid	ComfortClose
Operating noise dB(A) re 1 pW	43
Countdown indicator	•
Delay start up to 24 hours	•
In-operation indication	Display
Display language selection	•
Efficiency and sustainability	
EcoFeedback	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
ENERGY STAR® Most Efficient	•
Quality of results	
Fresh water dishwasher	•
SensorDry	•
Active condensation drying	•
Perfect GlassCare	•
Wash programs	
QuickIntenseWash	•
Normal	•
Pots & Pans	•
IntenseWash	•
China & Crystal	•
SaniWash	•
Rinse & Hold	•
Dishwashing options	
IntenseZone	•
Express	•
Extra Clean	•
Extra dry	•
Baskets	
Cutlery loading	3D MultiFlex Tray
FlexCare glass holder	2
FlexCare cup rack	2
Basket design	ExtraComfort
Safety	
Waterproof system	•
Check filter saturation indicator	•

G 7156 SCVi XXL

Fully integrated dishwashers
with 3D MultiFlex Tray for maximum convenience.



EAN: 4002516261452 / Material number: 11387590 / Old Material Number: 21715662USA

Child Safety lock

•

Technical data

Niche width min in in.(mm)	23 5/8 (600)
Niche width max in in.(mm)	23 5/8 (600)
Niche height min in in.(mm)	33 3/4 (855)
Niche height max in in.(mm)	36 1/4 (920)
Niche depth in in.(mm)	21 3/4 (550)
Appliance width in in.(mm)	23 5/8 (598)
Appliance height in in.(mm)	33 3/4 (855)
Appliance depth in in.(mm)	21 3/4 (550)
Appliance depth with door open in in.(cm)	47 1/2 (120.5)
Net weight in lbs. (kg)	106 (48.0)
Total connected load in kW	1.40
Voltage in V	120
Fuse rating in A	15
Number of phases	1
Electrical frequency standard	60
Length of water inlet hose in ft (m)	5 (1.50)
Length of water drain hose in ft (m)	5 (1.50)
Length of electrical wire in ft (m)	4 (1.20)
Min. front panel weight in kg	4.0
Max. front panel weight in kg	10.0
[can be retrofitted by Service to min.]	7.0
[can be retrofitted by Service to max.]	14.0

Available display languages

Available display languages via MultiLingua
deutsch, english, español,
français, português,

Standard accessories

1 x UltraTabs box (20 tabs)

•

Voucher for 1 x box of UltraTabs (20 tabs) or 9 boxes at a reduced price

•