

G 7316 SCU XXL AutoDos

Built-under dishwashers

42 dB | Cutlery tray | ExtraComfort baskets | AutoDos | Delay start



- Tested for the equivalent of 20 years' service life*
- Convenient, great results and perfect for everyday use – ExtraComfort baskets
- Convenient, efficient, sustainable – perfect results with automatic dispensing from PowerDisk
- More information options and modern domestic appliance networking – Miele@home
- QuickIntenseWash, superior cleaning and drying in under 60 min
- Completely dry – Miele AutoOpen drying

* During the development phase of the G 5000 and G 7000 dishwasher series, Miele tested models and core components in 5,600 wash cycles (= 280 wash cycles per year over a period of 20 years) in various programs. More at: mieleusa.com/20years

EAN: 4002516260394 / Material number: 11388020 /
Old Material Number: 21731637USA

General information	
Model number	G 7316 SCU XXL AutoDos
Manufacturer material number	11388020
EAN number	4002516260394
Marketing class	Platinum
Type	
Pre-finished	•
24 inch dishwasher	•
Design	
Fascia color	Clean Touch Steel
Fascia panel version	Straight fascia
Control type	Softkeys
Control panel	1-line plain text display
Display color	White
MultiLingua	•
Convenience	
Networking with Miele@home	•
Automatic dispensing with PowerDisk	•
Door closing aid	ComfortClose
Operating noise dB(A) re 1 pW	42
Countdown indicator	•
Delay start up to 24 hours	•
In-operation indicator	Display
Display language selection	•
Smart Extras	
Alexa voice control	•
Dishwashing Assistant	•
Google voice control	•
AutoStart	•
MobileStart	•
Push notifications	•
Fill levels	•
AI Diagnostics	•
RemoteUpdate	•
Smart Home Integration	•
Efficiency	
Noise emissions in dB(A)	42
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
ENERGY STAR® Most Efficient	•
Quality of results	
Fresh water dishwasher	•
AutoOpen drying	•
SensorDry	•
Active condensation drying	•
Perfect GlassCare	•

G 7316 SCU XXL AutoDos

Built-under dishwashers

42 dB | Cutlery tray | ExtraComfort baskets | AutoDos | Delay start



EAN: 4002516260394 / Material number: 11388020 /
Old Material Number: 21731637USA

Wash programs	
QuickIntenseWash	•
Normal	•
Pots & Pans	•
IntenseWash	•
Gentle	•
SaniWash	•
ExtraQuiet 40 dB(A)	•
Appliance care	•
Rinse & Hold	•
Filters	•
Dishwashing options	
AutoDos	•
IntenseZone	•
Express	•
Extra Clean	•
Extra dry	•
Baskets	
Cutlery loading	3D MultiFlex Tray
FlexCare glass holder	2
FlexCare cup rack	2
Basket design	ExtraComfort
Safety	
Waterproof system	•
Check filter saturation indicator	•
Child Safety lock	•
Technical data	
Niche width min in in.(mm)	23 5/8 (600)
Niche width max in in.(mm)	23 5/8 (600)
Niche height min in in.(mm)	33 3/4 (855)
Niche height max in in.(mm)	36 1/4 (920)
Niche depth in in.(mm)	22 1/2 (570)
Appliance width in in.(mm)	23 5/8 (598)
Appliance height in in.(mm)	33 3/4 (855)
Appliance depth in in.(mm)	22 1/2 (570)
Appliance depth with door open in in.(cm)	47 1/2 (120.5)
Net weight in lbs. (kg)	110 (49.5)
Total connected load in kW	1.40
Voltage in V	120
Fuse rating in A	15
Number of phases	1
Electrical frequency standard	60
Length of water inlet hose in m	5 (1.50)
Length of water drain hose in m	5 (1.50)
Length of electrical wire in ft (m)	4 (1.20)
Standard accessories	
1 x PowerDisk	•
Voucher for 6 x PowerDisk	•

G 7316 SCU XXL AutoDos

Built-under dishwashers

42 dB | Cutlery tray | ExtraComfort baskets | AutoDos | Delay start



EAN: 4002516260394 / Material number: 11388020 /
Old Material Number: 21731637USA

Available display languages

Available display languages via MultiLingua

□□□□, deutsch,
english, français, português,
español