

G 7591 SCVi AutoDos
Fully integrated ADA dishwasher
39 dB | Cutlery tray | MaxiComfort baskets | Knock2open | BrilliantLight



- Tested for the equivalent of 20 years' service life*
- Maximum flexibility and premium basket design – MaxiComfort baskets
- Combining perfection in kitchen design with automatic opening – Knock2open
- A perfect view for convenient loading even in the dark – BrilliantLight
- Convenient, efficient, sustainable – perfect results with automatic dispensing from PowerDisk
- More information options and modern domestic appliance networking – Miele@home

* During the development phase of the G 5000 and G 7000 dishwasher series, Miele tested models and core components in 5,600 wash cycles (= 280 wash cycles per year over a period of 20 years) in various programs. More at: mieleusa.com/20years

EAN: 4002516261551 / Material number: 11388260 /
Old Material Number: 21759162USA

General information	
Model number	G 7591 SCVi AutoDos
Manufacturer material number	11388260
EAN number	4002516261551
Marketing class	Platinum
Type	
Fully integrated dishwashers	•
24 inch dishwasher	•
Design	
Fascia color	Clean Touch Steel/Obsidian Black
Fascia panel version	Fully integrated fascia
Control type	Softkeys
Control panel	1-line plain text display
Display color	White
MultiLingua	•
Convenience	
Networking with Miele@home	•
Automatic dispensing with PowerDisk	•
Knock2open	•
Door closing aid	AutoClose incl. ComfortClose
LED Lighting	•
Operating noise dB(A) re 1 pW	40
Countdown indicator	•
Delay start up to 24 hours	•
In-operation indicator	optical and acoustic, volume control
Display language selection	•
Smart Extras	
Alexa voice control	•
Dishwashing Assistant	•
Google voice control	•
AutoStart	•
MobileStart	•
Push notifications	•
Fill levels	•
AI Diagnostics	•
RemoteUpdate	•
Smart Home Integration	•
Efficiency	
Noise emissions in dB(A)	40
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
ENERGY STAR® Most Efficient	•

G 7591 SCVi AutoDos
Fully integrated ADA dishwasher
39 dB | Cutlery tray | MaxiComfort baskets | Knock2open | BrilliantLight



EAN: 4002516261551 / Material number: 11388260 /
Old Material Number: 21759162USA

Quality of results	
Fresh water dishwasher	•
AutoOpen drying	•
SensorDry	•
Active condensation drying	•
Perfect GlassCare	•
Wash programs	
QuickIntenseWash	•
Economy	•
Normal	•
SensorWash	•
Pots & Pans	•
IntenseWash	•
Gentle	•
SaniWash	•
Energy Saver	•
Extra Quiet	•
Glasses — No Rinse Aid	•
Appliance care	•
Rinse & Hold	•
Filters	•
Dishwashing options	
AutoDos	•
IntenseZone	•
Express	•
Extra Clean	•
Extra dry	•
Baskets	
Cutlery loading	3D MultiFlex Tray
FlexCare glass holder	4
FlexCare cup rack	2
Basket design	MaxiComfort
Safety	
Waterproof system	•
Check filter saturation indicator	•
Technical data	
Niche width min in in.(mm)	23 5/8 (600)
Niche width max in in.(mm)	23 5/8 (600)
Niche height min in in.(mm)	32 1/8 (815)
Niche height max in in.(mm)	34 3/4 (880)
Niche depth in in.(mm)	21 3/4 (550)
Appliance width in in.(mm)	23 5/8 (598)
Appliance height in in.(mm)	32 1/8 (815)
Appliance depth in in.(mm)	21 3/4 (550)
Appliance depth with door open in in.(cm)	45 7/8 (116.5)
Net weight in lbs. (kg)	106 (48.0)
Total connected load in kW	1.40
Voltage in V	120

G 7591 SCVi AutoDos
Fully integrated ADA dishwasher
39 dB | Cutlery tray | MaxiComfort baskets | Knock2open | BrilliantLight



EAN: 4002516261551 / Material number: 11388260 / Old Material Number: 21759162USA	
Fuse rating in A	15
Number of phases	1
Electrical frequency standard	60
Length of water inlet hose in m	5 (1.50)
Length of water drain hose in m	5 (1.50)
Length of electrical wire in ft (m)	4 (1.20)
Min. front panel weight in kg	3.0
Max. front panel weight in kg	11.0
[can be retrofitted by Service to min.]	8.0
[can be retrofitted by Service to max.]	17.0
Replacing bulbs	Customer Service
Standard accessories	
1 x PowerDisk	•
Voucher for 6 x PowerDisk	•
Available display languages	
Available display languages via MultiLingua	
🇬🇧🇩🇪🇫🇷🇵🇹, deutsch, english, français, português, español	