

G 7966 SCVi XXL AutoDos
Fully integrated dishwashers
– the Miele all-rounder for handleless kitchen designs.



- Automatic dispensing – AutoDos with integrated PowerDisk
- ExtraComfort Baskets w/3D MultiFlex Tray adjusts for more volume
- Miele@home w/ AutoStart, remotely program your dishwasher
- Automatic door opening after two knocks – Knock2open
- Quick swipe operation – M Touch display

EAN: 4002516261582 / Material number: 11388300 / Old Material Number: 21796662USA

Type	
Fully integrated dishwashers	•
24 inch dishwasher	•
Design	
Fascia color	Clean Touch Steel/Obsidian Black
Fascia panel version	Fully integrated fascia
Control type	Softkeys
Control panel	1-line display with plain text
Display color	White
MultiLingua	•
Convenience	
Networking with Miele@home	•
Automatic dispensing with PowerDisk	•
Knock2open	•
LED Lighting	•
Operating noise dB(A) re 1 pW	40
Countdown indicator	•
Delay start up to 24 hours	•
In-operation indication	Display
Display language selection	•
Efficiency and sustainability	
EcoFeedback	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
ENERGY STAR® Most Efficient	•
Quality of results	
Fresh water dishwasher	•
SensorDry	•
Active condensation drying	•
Perfect GlassCare	•
Wash programs	
QuickIntenseWash	•
Economy	•
Normal	•
SensorWash	•
Pots & Pans	•
IntenseWash	•
China & Crystal	•
SaniWash	•
Energy Saver	•
Extra Quiet 39 dB(A)	•
Glasses – No Rinse Aid	•
Appliance care	•
Rinse & Hold	•
Dishwashing options	
AutoDos	•
IntenseZone	•

G 7966 SCVi XXL AutoDos
Fully integrated dishwashers
– the Miele all-rounder for handleless kitchen designs.



EAN: 4002516261582 / Material number: 11388300 / Old Material Number: 21796662USA

Express	•
Extra Clean	•
Extra dry	•
Baskets	
Cutlery loading	3D MultiFlex Tray
FlexCare glass holder	4
FlexCare cup rack	2
Basket design	MaxiComfort
Safety	
Waterproof system	•
Check filter saturation indicator	•
Child Safety lock	•
Technical data	
Niche width min in in.(mm)	23 5/8 (600)
Niche width max in in.(mm)	23 5/8 (600)
Niche height min in in.(mm)	33 3/4 (855)
Niche height max in in.(mm)	36 1/4 (920)
Niche depth in in.(mm)	21 3/4 (550)
Appliance width in in.(mm)	23 5/8 (598)
Appliance height in in.(mm)	33 3/4 (855)
Appliance depth in in.(mm)	21 3/4 (550)
Appliance depth with door open in in.(cm)	47 1/2 (120.5)
Net weight in lbs. (kg)	109 (49.0)
Total connected load in kW	1.40
Voltage in V	120
Fuse rating in A	15
Number of phases	1
Electrical frequency standard	60
Length of water inlet hose in ft (m)	5 (1.50)
Length of water drain hose in ft (m)	5 (1.50)
Length of electrical wire in ft (m)	4 (1.20)
Min. front panel weight in kg	4.0
Max. front panel weight in kg	12.0
Replacing bulbs	Customer Service
Available display languages	
Available display languages via MultiLingua	bahasa malaysia, dansk, deutsch, english (AU), english (GB), english (US), español, français (FR), hrvatski, italiano, magyar, nederlands, norsk, polski, portuguese, русский, română, slovenčina, slovenščina, srpski, suomi, svenska, türkçe, українська, čeština, ελληνικά,
Standard accessories	
1 x PowerDisk	•
Voucher for 6 x PowerDisk	•