

PR 900

Built-in report printer

For printing process protocols.



- Thermal printer with 2 3/8" (60 mm) paper width
- Can be installed on the outfeed side with 2-door models

EAN: 4002516362081 / Material number: 11491220 / Old Material Number: 69247004D

Product category	
Large-capacity washer-disinfectors, laboratory	•
Machine affiliation	
PLW 8615	•
PLW 8616	•
Product characteristics	
Color	Black
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in inches	37 7/16 (950) in (mm)
External dimensions, net width in inches	3 1/16 (77) in (mm)
External dimensions, net depth in inches	2 3/4 (69) in (mm)
External dimensions, gross height in inches	4 15/16 (125)
External dimensions, gross width in inches	7 7/8 (200)
External dimensions, gross depth in inches	39 3/8 (1000)
Net weight in lbs	7 (2.87)
Gross weight in lbs	8 (3.59)