

## PFD 104 SCVi XXL [120V/208-240V]

Fully integrated Full-sizedishwasher with 3D MultiFlex cutlery tray  
for large loads of dishware in households, offices and utility areas.



- Wash performance: 16 place settings in just 24 min\*
- 13% less energy consumption
- Door opens automatically after two knocks – Knock2open
- Everything completely dry – AutoOpen assisted drying
- Innovative design and maximum convenience – 3D MultiFlex Tray

\* Depending on site conditions (temperature of incoming water / power connection) values given may vary.

EAN: 4002516366942 / Material number: 11605520 / Old Material Number: 61010405CDN

Construction type and design	
Model	Fully integrated dishwasher
XXL dishwashers	•
Range	ProfiLine
Wash system	Fresh water front loader
Number of levels	2
Front	Without front
Side walls	Galvanised
Control panel color	Obsidian Black
Minimum front panel weight in lbs (kg)	11 (5) lb (kg)
Maximum front panel weight in lbs (kg)	26 (12) lb (kg)
Application	
Suitable for retirement and care homes	•
Suitable for Bed & Breakfast	•
Suitable for child care facilities	•
Suitable for universities and schools	•
Suitable for offices	•
Suitable for domestic use	•
Suitable for small businesses	•
Suitable for sports clubs	•
Performance data	
Tested virucidal efficacy	•
Certified hygiene	•
Circulation pump, Qmax in gal/min (l/min)	19.8 (75)
Shortest program duration in min.	24
Maximum final rinse temperature in °F (°C)	180 (82)
Cleaning performance, place settings/cycle	16
Service life in wash cycles	12500
Miele MOVE	
Network-enabled with Miele MOVE	•
Control	
Control system	Electronic controls
Program selection	Program selectors
Max. delay start in h	24
Countdown indicator	•
Programs [quantity]	8
Program sequence indicator	•
Choice of display language	•
Check filter indicator	•
Standard electrical connection	
Electrical connection	2N AC 120/208-240V, 60HZ
Heater rating in kW	3.50-3.80
Total connected load in kW	3.70-4.00
Fuse rating in A	30
Length of power cord in ft (m)	5 (1.70)
NEMA plug: 14-30	•
Possible voltage variant 1	
Electrical connection	AC 120V 60HZ
Heater rating in kW	1.30

## PFD 104 SCVi XXL [120V/208-240V]

Fully integrated Full-sized dishwasher with 3D MultiFlex cutlery tray for large loads of dishware in households, offices and utility areas.



EAN: 4002516366942 / Material number: 11605520 / Old Material Number: 61010405CDN

Total connected load in kW	1.40
Fuse rating in A	15
<b>Water connection/drainage</b>	
Cold or hot water [number]	1
Required flow pressure in bar	1.00-10.00
Drain hose [DN]	22
Maximum delivery head for drain pump in inches (cm)	39 3/8 (100)
Integrated water softener	•
Maximum water hardness in gpg (mmol/l)	38.02 (6.50)
Water protection system	Waterproof system
Length of water inlet hose in inches (cm)	59 1/8 (150)
Length of water drain hose in inches (cm)	59 1/8 (150)
<b>Dimensions and weight</b>	
External dimensions, net height in inches	33 5/16 (845)
External dimensions, net width in inches	23 9/16 (598)
External dimensions, net depth in inches	21 11/16 (550)
External dimensions, gross height in inches	37 13/16 (960)
External dimensions, gross width in inches	26 7/16 (670)
External dimensions, gross depth in inches	27 9/16 (700)
Usable space in wash cabinet, width in inches (mm)	22 7/8 (580)
Usable space in wash cabinet, height in inches (mm)	20 1/8 (510)
Usable space in wash cabinet, depth of upper basket in inches (mm)	17 3/4 (450)
Usable space in wash cabinet, depth of lower basket in inches (mm)	17 3/4 (450)
In-feed height above floor in inches (mm)	8 5/16 (210)
Required niche width in mm	23 5/8 (600)
Net weight [kg]	113 (51)
Gross weight in lbs.	128 (58)
Maximum floor load in N/m <sup>2</sup>	1000
<b>Emission values</b>	
Emission sound pressure level in workplace (LpA)	33 dB(A) re 20 µPa
Sound power (LwA) in dB(A) re 1 pW	45.0
<b>Programs</b>	
Universal	•
Short	•
SaniWash	•
Cold/Pre-wash	•
Glasses	•
Plastic	•
EnergySave/Economy	•
Intensive	•
<b>Baskets</b>	
MaxiComfort P baskets	•
Flexible FlexLine basket design	•
FlexCare glass holder [number]	4
FlexCare cup rack [number]	2
Height-adjustable upper basket	•
Patented 3D MultiFlex tray	•
<b>Features</b>	
Commercial-grade electrical connection	•

## PFD 104 SCVi XXL [120V/208-240V]

Fully integrated Full-sizedishwasher with 3D MultiFlex cutlery tray  
for large loads of dishware in households, offices and utility areas.



EAN: 4002516366942 / Material number: 11605520 / Old Material Number: 61010405CDN

Drying

AutoOpen assisted drying,  
Active condensation drying,  
Additional drying

1 Combi dispenser/door for powder and liquid media	•
Wash cabinet made from high-quality stainless steel	•
LED Lighting	•
Knock2open	•
AutoClose	•
EcoFeedback	•
Brilliant GlassCare	•
Adjustable final rinse temperature	•
Optical interface	•
SmartStart	•
FlexiTimer with EcoStart	•
WiFi module	•
<b>Standards, test certificates, and symbols</b>	
CE	•
Complies with Machinery Directive 2006/42/EC	•
VDE	•
EMC radio suppressed	•
DIN EN 17735	•
EN 1717	•
UL	•