


PRI 421 [EL SOM LAM IB RF]

Rotary iron, electric

with leaf-spring padding, feed-in belts and return feed for marine applications.



- Performance 67.0 kg/h*, roller diameter 14 3/8 (365) in (mm), working width 80 3/8 (2040) in (mm)
- Fast cooling of textiles – EasyFold feed table
- State-of-the-art controls – Touch display
- Selection of the most important settings – favorite programs
- Perfect rotary ironing performance – flexibly positioned heater plate

* With 50% residual moisture – performance data according to DIN 11 902: The achievable laundry throughput depends on overall conditions such as, for example, the type of laundry and the experience of the operator.


EAN: 4002516367635 / Material number: 11606190 / Old Material Number: 53421106SOM

Construction type and design	
Design	Infeed of laundry at the front, outfeed at the back
Can be set up against a wall	•
Linie	Professional
Outer casing	Iron Grey
Drum diameter in in.(mm)	14 3/8 (365)
Working width in in.(mm)	80 3/8 (2040)
Heater plate material	Aluminium
Padding	Leaf-spring padding
Ironer cover	ARAMID needle-felt cloth
Application	
Suitable for off-shore use	•
Suitable for Marine use	•
Performance data	
Max. ironing performance at 25 % residual moisture in kg/h	113.0
Max. ironing performance at 50 % residual moisture in kg/h	67.0
Tested operating hours	20000
Control	
Control system	Touch display
Touch display (optional)	Touch-Display PRI
Program setting	Setting of defined program parameters
Minimum ironer speed, can be set in ft/min	1.5
Maximum ironer speed, can be set in ft/min	5.4
Adjustable temperature	Infinitely variable
Standard electrical connection	
Type of heating	Electric
Electrical connection	3 AC 450V 50-60HZ
Electric heater rating in kW	24.00
Total connected load in kW	24.60
Fuse rating in A	50
Possible voltage variant 1	
Electrical connection	3 AC 440V 50-60HZ
Electric heater rating in kW	22.90
Total connected load in kW	23.50
Fuse rating in A	50
Dimensions and weight	
External dimensions, height in mm	43 3/4 (1110)
External dimensions, width in mm	108 5/8 (2759)
External dimensions, depth in mm	56 3/4 (1441)
External dimensions, gross height in inches	54 11/16 (1388)
External dimensions, gross width in inches	112 7/8 (2866)
External dimensions, gross depth in inches	43 3/16 (1096)
Net weight in kg	1010 (458)
Gross weight in lbs.	1184 (537)
Maximum floor load in N/m ²	4493
Emission values	
Emissions – sound pressure at workplace	56 dB(A) re 20 µPa
Heat output to the room in Mj/h and BTUs /h	13.70

PRI 421 [EL SOM LAM IB RF]

Rotary iron, electric

with leaf-spring padding, feed-in belts and return feed for marine applications.



EAN: 4002516367635 / Material number: 11606190 / Old Material Number: 53421106SOM

Features

Patented EasyFold out-feed table	•
Outfeed table extension (optional)	•
HPC heater plate	•
Finger guard	•
FlexControl footswitch	•
In-feed table with feed-in bands	•
Laundry pick-off bands	•
Laundry crates	•
Laundry return feed	•
Cover (optional)	•
Favorites program	•
Incorrect feed recognition	•
Air suspension	•
Pause function	•
High contact pressure	•
Heater plate cleaning and waxing indicator	•
Emergency shut off	•
APRI 319 care set for the heater plate included in the scope of delivery	•
Appliance-independent accessories	•

Connection options

Peak load cut-out/energy management (optional)	•
--	---

Standards, test certificates, and symbols

VDE	•
CE	•
WEEE	•
VDE-EMC	•
Splash-proof IPX0	•
UKCA	•
Complies with Machinery Directive 2006/42/EC	•