

WXR860 WCS TDos & IntenseWash

W1 front-loading washing machine:

With TwinDos, IntenseWash, and Miele@home for ultimate cleanliness and comfort.



- Tested for 20 years of perfect laundry care
- Save energy in the best energy efficiency class (A)
- M Touch – simple control by tapping or swiping
- Precise and automatic detergent dispensing with TwinDos®
- There's no faster way to wash – QuickIntenseWash

EAN: 4002516376804 / Material number: 11613700 / Old Material Number: 11XR8605USA

Design	
Stackable	•
Side-by-side	•
Slot-in	•
Door hinging	left
Type	
Product brand	W1 White Edition
Front loaders	•
Spinning	
Max. spin speed	1600
Rinse hold	•
Without spin" function	•
Design	
Appliance color	Lotus white
Control panel color	Lotus white
Door design	Lotus white with chrome ring
Fascia panel version	5° inclined
Control type	Touch control
Control panel	MTouch
Cleaning performance	
Innovative IntenseWash technology	•
TwinDos automatic dispensing of detergent	•
CapDosing portioned dispensing	•
Proven virus hygiene	•
Gentle laundry care	
Honeycomb drum	•
Load in lbs. (kg)	18 (8.0)
User convenience	
Networking with Miele@home	•
Delay start up to 24 hours	•
Countdown indicator	•
Time display	•
Programme sequence indicator	•
Information text	•
Favorite programs	•
Drum lighting	LED
MultiLingua	•
AutoClean dispenser drawer	•
AddLoad	•
Efficiency and sustainability	
Hot water connection	•
EcoFeedback	•
Low-temperature washing "Cold" and "68°F"	•
Automatic load control	•
Flow meter	•
Foam control	•
ProfiEco motor	•
Wash programs	
Delicates	•

WXR860 WCS TDos & IntenseWash

W1 front-loading washing machine:

With TwinDos, IntenseWash, and Miele@home for ultimate cleanliness and comfort.



EAN: 4002516376804 / Material number: 11613700 / Old Material Number: 11XR8605USA

Express	•
Dark garments	•
Denim	•
Outdoor	•
Proofing	•
Trainers	•
Clean machine	•
Starch	•
Normal	•
Wrinkle-free	•
Sanitize	•
Dress shirts	•
Extra White	•
QuickIntenseWash	•
Table Linens/Drapes	•
Sportswear	•
Woolens	•
Silks	•
Drain/Spin	•
QuickRinse	•
Baby Clothes	•
Towels	•
Downs	•
Pillows	•
Washing extras	
SingleWash	•
Soak	•
Pre-rinse	•
SoftSteam with steam	•
Choosing the degree of soiling	•
Acoustic signal	•
AllergoWash	•
Quality	
Counterweights made of cast iron	•
Safety	
Water protection system	Watercontrol-System
Child lock	•
Lock code	•
Optical interface	•
Technical data	
Dimensions (width) in in. (mm)	23 1/2 (596)
Dimensions (height) in in. (mm)	33 1/2 (850)
Dimensions (depth) in in. (mm)	25 3/8 (643)
Depth with door open in in. (mm)	42 1/2 (1077)
Weight in lbs. (kg)	212 (96)
Total connected load in kW	1.30
Voltage in V	120
Fuse rating in A	15
Frequency in Hz	60
Length of supply lead in ft. (m)	6 (2)

WXR860 WCS TDos & IntenseWash

W1 front-loading washing machine:

With TwinDos, IntenseWash, and Miele@home for ultimate cleanliness and comfort.



EAN: 4002516376804 / Material number: 11613700 / Old Material Number: 11XR8605USA

Standard accessories	
3 capsules	•
UltraPhase 1+2	•