

WWD160 WCS

W1 front-loading washing machine:

8 kg | 1600 rpm | Pre-Ironing | Miele@home | CapDosing | Honeycomb Drum



- Exclusive CapDosing range for different fabrics and stains*
- The Pre-ironing extra reduces creasing and saves up to 50% time and effort**
- Wash small & large loads efficiently – automatic load recognition
- 12 programs including Express
- ENERGY STAR® qualified

* Patent EP 2 365 120

** Patent EP 2 088 231

EAN: 4002516376903 / Material number: 11614040 /
Old Material Number: 11WD1601USA

Design	
Stackable	•
Side-by-side	•
Slot-in	•
Door hinging	left
Type	
Product brand	W1 White Edition
Front loaders	•
Spinning	
Max. spin speed	1600
Rinse hold	•
Without spin ¹ function	•
Design	
Appliance color	Lotus white
Control panel color	Lotus white
Door design	Obsidian Black with white ring
Rotary selector color	Lotus White
Fascia panel version	5° inclined
Control type	Selector dial
Control panel	DirectSensor yellow, 7 segment
Cleaning performance	
CapDosing portioned dispensing	•
Gentle laundry care	
Honeycomb drum	•
Load in lbs. (kg)	18 (8.0)
User convenience	
Networking with Miele@home	•
Delay start up to 24 hours	•
Countdown indicator	•
AutoClean dispenser drawer	•
AddLoad	•
Efficiency and sustainability	
Hot water connection	•
Low-temperature washing "Cold" and "68°F"	•
Automatic load control	•
Flow meter	•
Foam control	•
ProfiEco motor	•
Wash programs	
Delicates	•
Express	•
Outdoor	•
Proofing	•
Normal	•
Sanitize	•
Handwash	•

WWD160 WCS

W1 front-loading washing machine:

8 kg | 1600 rpm | Pre-Ironing | Miele@home | CapDosing | Honeycomb Drum



EAN: 4002516376903 / Material number: 11614040 /

Old Material Number: 11WD1601USA

Dress shirts	•
Extra White	•
Darks/Denims	•
Drain/Spin	•
Washing extras	
SoftSteam with steam	•
Safety	
Water protection system	Watercontrol-System
Child lock	•
Lock code	•
Optical interface	•
Technical data	
Dimensions (width) in in. (mm)	23 1/2 (596)
Dimensions (height) in in. (mm)	33 1/2 (850)
Dimensions (depth) in in. (mm)	25 3/8 (643)
Depth with door open in in. (mm)	42 1/2 (1077)
Weight in lbs. (kg)	203 (92)
Total connected load in kW	1.30
Voltage in V	120
Fuse rating in A	15
Frequency in Hz	60
Water intake hose length in ft. (m)	5 (1.60)
Water drain hose length in ft. (m)	4 (1.50)
Length of supply lead in ft. (m)	6 (2)