

WWD660 WCS TDos

W1 front-loading washing machine:

8 kg | 1600 rpm | Auto Dosing | Pre-Ironing | Miele@home | CapDosing



- Precise and automatic detergent dispensing with TwinDos®*
- The Pre-ironing extra reduces creasing and saves up to 50% time and effort**
- Exclusive CapDosing range for different fabrics and stains***
- Wash small & large loads efficiently – automatic load recognition
- ENERGY STAR® qualified

* Patent EP 2 784 205

** Patent EP 2 088 231

*** Patent EP 2 365 120

EAN: 4002516376705 / Material number: 11614100 /
Old Material Number: 11WD6601USA

| | |
|---|--------------------------------|
| Design | |
| Stackable | • |
| Side-by-side | • |
| Slot-in | • |
| Door hinging | left |
| Type | |
| Product brand | W1 White Edition |
| Front loaders | • |
| Spinning | |
| Max. spin speed | 1600 |
| Rinse hold | • |
| Without spin" function | • |
| Design | |
| Appliance color | Lotus white |
| Control panel color | Lotus white |
| Door design | Obsidian Black with white ring |
| Rotary selector color | Lotus White |
| Fascia panel version | 5° inclined |
| Control type | Selector dial |
| Control panel | DirectSensor yellow, 7 segment |
| Cleaning performance | |
| TwinDos automatic dispensing of detergent | • |
| CapDosing portioned dispensing | • |
| Gentle laundry care | |
| Honeycomb drum | • |
| Load in lbs. (kg) | 18 (8.0) |
| User convenience | |
| Networking with Miele@home | • |
| Delay start up to 24 hours | • |
| Countdown indicator | • |
| AutoClean dispenser drawer | • |
| AddLoad | • |
| Efficiency and sustainability | |
| Hot water connection | • |
| Low-temperature washing "Cold" and "68°F" | • |
| Automatic load control | • |
| Flow meter | • |
| Foam control | • |
| ProfiEco motor | • |
| Wash programs | |
| Delicates | • |
| Express | • |
| Outdoor | • |
| Proofing | • |
| Normal | • |
| Sanitize | • |

WWD660 WCS TDos

W1 front-loading washing machine:

8 kg | 1600 rpm | Auto Dosing | Pre-Ironing | Miele@home | CapDosing



EAN: 4002516376705 / Material number: 11614100 /
Old Material Number: 11WD6601USA

| | |
|-------------------------------------|---------------------|
| Handwash | • |
| Dress shirts | • |
| Extra White | • |
| Darks/Denims | • |
| Drain/Spin | • |
| Washing extras | |
| SoftSteam with steam | • |
| Safety | |
| Water protection system | Watercontrol-System |
| Child lock | • |
| Lock code | • |
| Optical interface | • |
| Technical data | |
| Dimensions (width) in in. (mm) | 23 1/2 (596) |
| Dimensions (height) in in. (mm) | 33 1/2 (850) |
| Dimensions (depth) in in. (mm) | 25 3/8 (643) |
| Depth with door open in in. (mm) | 42 1/2 (1077) |
| Weight in lbs. (kg) | 212 (96) |
| Total connected load in kW | 1.30 |
| Voltage in V | 120 |
| Fuse rating in A | 15 |
| Frequency in Hz | 60 |
| Water intake hose length in ft. (m) | 5 (1.60) |
| Water drain hose length in ft. (m) | 4 (1.50) |
| Length of supply lead in ft. (m) | 6 (2) |

WWD660 WCS TDos

W1 front-loading washing machine:

8 kg | 1600 rpm | Auto Dosing | Pre-Ironing | Miele@home | CapDosing



W1 drawing, facia 5 degree, measures in mm



W1 drawing, facia 5 degree, measures in mm



W1 drawing, facia 5 degree, measures in mm



W1 drawing, facia 5 degree, measures in mm