

## WXF660 WCS TDos

W1 front-loading washing machine:

8 kg | 1600 rpm | Auto Dosing | Pre-Ironing | Miele@home | CapDosing



- Precise and automatic detergent dispensing with TwinDos®\*
- The Pre-ironing extra reduces creasing and saves up to 50% time and effort\*\*
- Exclusive CapDosing range for different fabrics and stains\*\*\*
- Wash small & large loads efficiently – automatic load recognition
- ENERGY STAR® qualified

\* Patent EP 2 784 205

\*\* Patent EP 2 088 231

\*\*\* Patent EP 2 365 120

EAN: 4002516377115 / Material number: 11614130 / Old Material Number: 11XF6605USA

|   |                              |
|---|------------------------------|
| <b>Design</b>                             |                              |
| Stackable                                 | •                            |
| Side-by-side                              | •                            |
| Slot-in                                   | •                            |
| Door hinging                              | left                         |
| <b>Type</b>                               |                              |
| Product brand                             | W1 White Edition             |
| Front loaders                             | •                            |
| <b>Spinning</b>                           |                              |
| Max. spin speed                           | 1600                         |
| Rinse hold                                | •                            |
| Without spin" function                    | •                            |
| <b>Design</b>                             |                              |
| Appliance color                           | Lotus white                  |
| Control panel color                       | Lotus white                  |
| Door design                               | Lotus white with chrome ring |
| Rotary selector color                     | Lotus White / Chrome ring    |
| Fascia panel version                      | 5° inclined                  |
| Control type                              | Selector dial                |
| Control panel                             | ComfortSensor white, 1 line  |
| <b>Cleaning performance</b>               |                              |
| TwinDos automatic dispensing of detergent | •                            |
| CapDosing portioned dispensing            | •                            |
| <b>Gentle laundry care</b>                |                              |
| Honeycomb drum                            | •                            |
| Load in lbs. (kg)                         | 18 (8.0)                     |
| <b>User convenience</b>                   |                              |
| Networking with Miele@home                | •                            |
| Delay start up to 24 hours                | •                            |
| Countdown indicator                       | •                            |
| Programme sequence indicator              | •                            |
| Drum lighting                             | LED                          |
| MultiLingua                               | •                            |
| AutoClean dispenser drawer                | •                            |
| AddLoad                                   | •                            |
| <b>Efficiency and sustainability</b>      |                              |
| Hot water connection                      | •                            |
| EcoFeedback                               | •                            |
| Low-temperature washing "Cold" and "68°F" | •                            |
| Automatic load control                    | •                            |
| Flow meter                                | •                            |
| Foam control                              | •                            |
| ProfiEco motor                            | •                            |
| <b>Wash programs</b>                      |                              |
| Delicates                                 | •                            |
| Express                                   | •                            |
| Outdoor                                   | •                            |

WXF660 WCS TDoS

W1 front-loading washing machine:

8 kg | 1600 rpm | Auto Dosing | Pre-Ironing | Miele@home | CapDosing



EAN: 4002516377115 / Material number: 11614130 / Old Material Number: 11XF6605USA

|                                     |                     |
|-------------------------------------|---------------------|
| Proofing                            | •                   |
| Clean machine                       | •                   |
| Normal                              | •                   |
| Wrinkle-free                        | •                   |
| Sanitize                            | •                   |
| Handwash                            | •                   |
| Dress shirts                        | •                   |
| Extra White                         | •                   |
| Darks/Denims                        | •                   |
| Table Linens/Drapes                 | •                   |
| Sportswear                          | •                   |
| Woolens                             | •                   |
| Silks                               | •                   |
| Drain/Spin                          | •                   |
| QuickRinse                          | •                   |
| Baby Clothes                        | •                   |
| Towels                              | •                   |
| Downs                               | •                   |
| Pillows                             | •                   |
| <b>Washing extras</b>               |                     |
| Soak                                | •                   |
| Pre-rinse                           | •                   |
| SoftSteam with steam                | •                   |
| Choosing the degree of soiling      | •                   |
| Acoustic signal                     | •                   |
| AllergoWash                         | •                   |
| <b>Safety</b>                       |                     |
| Water protection system             | Watercontrol-System |
| Child lock                          | •                   |
| Lock code                           | •                   |
| Optical interface                   | •                   |
| <b>Technical data</b>               |                     |
| Dimensions (width) in in. (mm)      | 23 1/2 (596)        |
| Dimensions (height) in in. (mm)     | 33 1/2 (850)        |
| Dimensions (depth) in in. (mm)      | 25 3/8 (643)        |
| Depth with door open in in. (mm)    | 42 1/2 (1077)       |
| Weight in lbs. (kg)                 | 212 (96)            |
| Total connected load in kW          | 1.30                |
| Voltage in V                        | 120                 |
| Fuse rating in A                    | 15                  |
| Frequency in Hz                     | 60                  |
| Water intake hose length in ft. (m) | 5 (1.60)            |
| Water drain hose length in ft. (m)  | 4 (1.50)            |
| Length of supply lead in ft. (m)    | 6 (2)               |
| <b>Standard accessories</b>         |                     |
| 3 capsules                          | •                   |
| UltraPhase 1+2                      | •                   |
| Voucher for 5 x UltraPhases         | •                   |