

WXI860 WCS TDos & IntenseWash

W1 front-loading washing machine:

8 kg | 1600 rpm | Auto Dosing | IntenseWash | Pre-Ironing | SingleWash



- There's no faster way to wash – QuickIntenseWash
- Precise and automatic detergent dispensing with TwinDos®*
- Exclusive CapDosing range for different fabrics and stains**
- The Pre-ironing extra reduces creasing and saves up to 50% time and effort***
- ENERGY STAR® qualified

* Patent EP 2 784 205

** Patent EP 2 365 120

*** Patent EP 2 088 231

EAN: 4002516377023 / Material number: 11614140 /
Old Material Number: 11XI8605USA

Design	
Stackable	•
Side-by-side	•
Slot-in	•
Door hinging	left
Type	
Product brand	W1 White Edition
Front loaders	•
Spinning	
Max. spin speed	1600
Rinse hold	•
Without spin" function	•
Design	
Appliance color	Lotus white
Control panel color	Lotus white
Door design	Lotus white with chrome ring
Rotary selector color	Lotus White / Chrome ring
Fascia panel version	5° inclined
Control type	Selector dial
Control panel	ComfortSensor white, 1 line
Cleaning performance	
Innovative IntenseWash technology	•
TwinDos automatic dispensing of detergent	•
CapDosing portioned dispensing	•
Proven virus hygiene	•
Gentle laundry care	
Honeycomb drum	•
Load in lbs. (kg)	18 (8.0)
User convenience	
Networking with Miele@home	•
Delay start up to 24 hours	•
Countdown indicator	•
Programme sequence indicator	•
Drum lighting	LED
MultiLingua	•
AutoClean dispenser drawer	•
AddLoad	•
Efficiency and sustainability	
Hot water connection	•
EcoFeedback	•
Low-temperature washing "Cold" and "68°F"	•
Automatic load control	•
Flow meter	•
Foam control	•
ProfiEco motor	•
Wash programs	
Delicates	•

WXI860 WCS TDos & IntenseWash

W1 front-loading washing machine:

8 kg | 1600 rpm | Auto Dosing | IntenseWash | Pre-Ironing | SingleWash



EAN: 4002516377023 / Material number: 11614140 /
Old Material Number: 11XI8605USA

Express	•
Outdoor	•
Proofing	•
Clean machine	•
Normal	•
Wrinkle-free	•
Sanitize	•
Handwash	•
Dress shirts	•
Extra White	•
Darks/Denims	•
QuickIntenseWash	•
Table Linens/Drapes	•
Sportswear	•
Woolens	•
Silks	•
Drain/Spin	•
QuickRinse	•
Baby Clothes	•
Towels	•
Downs	•
Pillows	•
Washing extras	
SingleWash	•
Soak	•
Pre-rinse	•
SoftSteam with steam	•
Choosing the degree of soiling	•
AllergoWash	•
Safety	
Water protection system	Watercontrol-System
Child lock	•
Lock code	•
Optical interface	•
Technical data	
Dimensions (width) in in. (mm)	23 1/2 (596)
Dimensions (height) in in. (mm)	33 1/2 (850)
Dimensions (depth) in in. (mm)	25 3/8 (643)
Depth with door open in in. (mm)	42 1/2 (1077)
Weight in lbs. (kg)	212 (96)
Total connected load in kW	1.30
Voltage in V	120
Fuse rating in A	15
Frequency in Hz	60
Water intake hose length in ft. (m)	5 (1.60)
Water drain hose length in ft. (m)	4 (1.50)
Length of supply lead in ft. (m)	6 (2)

WXI860 WCS TDos & IntenseWash

W1 front-loading washing machine:

8 kg | 1600 rpm | Auto Dosing | IntenseWash | Pre-Ironing | SingleWash



EAN: 4002516377023 / Material number: 11614140 /

Old Material Number: 11XI8605USA

Standard accessories

3 capsules

•

UltraPhase 1+2

•

Voucher for 5 x UltraPhases

•