

TXI680WP Eco & Steam T1 Heat-Pump Dryer:



EAN: 4002516379829 / Material number: 11619850 /
Old Material Number: 12XI6802USA

Design	
Stackable	•
Side-by-Side	•
Slot-in	•
Door hinging	right, Reversible
Convertible door hinge	•
Type	
Product brand	T1 White Edition
Heat-pump dryer	•
Design	
Appliance color	Lotus white
Control panel color	Lotus white
Door design	Lotus white with chrome ring
Rotary selector color	Lotus White / Chrome ring
Fascia panel version	5° inclined
Control type	Selector dial
Display	ComfortSensor white, 1 line
Drying results	
PerfectDry precision drying	•
FragranceDos ² fragrance system	•
Intelligent drum reversal	•
Gentle laundry care	
Honeycomb drum	•
Load in lbs. (kg)	8.0
User convenience	
Networking with Miele@home	•
Delay start up to 24 hours	•
Countdown indicator	•
Programme sequence indicator	Yes
Drum lighting	LED
MultiLingua	•
Condensed water container	•
Integrated condensed water drainage	•
AddLoad	•
Efficiency and sustainability	
EcoFeedback	•
EcoDry technology	•
Maintenance-free heat exchanger	•
ProfiEco motor	•
Drying programs	
Delicates	•
Express	•
Outerwear	•
Proofing	•
Normal	•
Wrinkle-free	•
Smoothing	•

TXI680WP Eco & Steam T1 Heat-Pump Dryer:



EAN: 4002516379829 / Material number: 11619850 /
Old Material Number: 12XI6802USA

Woolens/Silks	•
Dress Shirts	•
Time Dry	•
Denims	•
Table Linens/Drapes	•
Bed Linens	•
Cold Air	•
Basket	•
Sportswear	•
Soft Steam	•
Pillows	•
Drying extras	
Anti-crease action	•
Gentle tumble	•
Freshen up	•
Acoustic signal	•
Quality	
Soft ribs	•
Safety	
Lock code	•
Empty out container" indicator	•
Clean filter" indication	•
Optical interface	•
Technical data	
Dimensions (width) in in. (mm)	23 1/2 (596)
Dimensions (height) in in. (mm)	33 1/2 (850)
Dimensions (depth) in in. (mm)	25 3/8 (643)
Depth with door open in in. (mm)	42 1/2 (1077)
Weight in lbs. (kg)	135 (61)
Total connected load in kW	1.00
Voltage in V	120
Fuse rating in A	15
Frequency in Hz	60
Length of supply lead in ft. (m)	6 (2)
Length of supply lead in ft. (m)	6 (2.0)
Length of supply lead in ft. (m)	6 (2)
Type of coolant	R134a
Refrigerant quantity in lbs (kg)	1.03 (0.47)
Standard accessories	
Fragrance flacon	•
Voucher for a second fragrance flacon	•