

G 5006 SCU

Built-under dishwashers

44 dB | Cutlery tray | Comfort baskets | QuickIntenseWash | Delay start



- Tested for the equivalent of 20 years' service life*
- Flexible basket design perfect for everyday use – Comfort baskets
- QuickIntenseWash, superior cleaning and drying in under 60 min
- Thanks to delay start, you can set a start time for the wash cycle up to 24 hours in advance
- Very easy door opening and closing – ComfortClose

* During the development phase of the G 5000 and G 7000 dishwasher series, Miele tested models and core components in 5,600 wash cycles (= 280 wash cycles per year over a period of 20 years) in various programs. More at: mieleusa.com/20years

EAN: 4002516376507 / Material number: 11636690 /
Old Material Number: 21500637USA

General information	
Model number	G 5006 SCU
Manufacturer material number	11636690
EAN number	4002516376507
Marketing class	Silver
Type	
Pre-finished	•
Design	
Fascia color	Clean Touch Steel
Fascia panel version	Straight fascia
Control type	Program selector button
Control panel	7-segment display
Display color	Yellow
Convenience	
Door closing aid	ComfortClose
Operating noise dB(A) re 1 pW	44
Countdown indicator	•
Delay start up to 24 hours	•
In-operation indicator	Display
Efficiency	
Noise emissions in dB(A)	44
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
ENERGY STAR® Most Efficient	•
Quality of results	
Fresh water dishwasher	•
Wash programs	
QuickIntenseWash	•
Normal	•
Pots & Pans	•
SaniWash	•
Rinse & Hold	•
Dishwashing options	
Short	•
Extra Clean	•
Extra dry	•
Baskets	
Cutlery loading	Cutlery tray
FlexCare cup rack	1
Basket design	Comfort
Safety	
Waterproof system	•
Child Safety lock	•
Technical data	
Niche width min in in.(mm)	23 5/8 (600)
Niche width max in in.(mm)	23 5/8 (600)

G 5006 SCU

Built-under dishwashers

44 dB | Cutlery tray | Comfort baskets | QuickIntenseWash | Delay start



EAN: 4002516376507 / Material number: 11636690 /
Old Material Number: 21500637USA

Niche height min in in.(mm)	33 3/4 (855)
Niche height max in in.(mm)	36 1/4 (920)
Niche depth in in.(mm)	22 1/2 (570)
Appliance width in in.(mm)	23 5/8 (598)
Appliance height in in.(mm)	33 3/4 (855)
Appliance depth in in.(mm)	22 1/2 (570)
Appliance depth with door open in in.(cm)	47 1/2 (120.5)
Net weight in lbs. (kg)	102 (46.0)
Total connected load in kW	1.40
Voltage in V	120
Fuse rating in A	15
Number of phases	1
Electrical frequency standard	60
Length of water inlet hose in m	492 (150.00)
Length of water drain hose in m	492 (150.00)
Length of electrical wire in ft (m)	4 (1.20)

Standard accessories

Voucher for 1 x box of UltraTabs (20 tabs) or 3 boxes (60 tabs in each) at a reduced price

•