

## G 5266 SCVi SF

Fully-integrated, full-size dishwasher

for optimum drying results thanks to AutoOpen drying.



- QuickIntenseWash, superior cleaning and drying in under 60 min
- Wonderful use of space – the 3D MultiFlex tray with more room for your cutlery
- Fresh water dishwashers – as little as ?? water consumed in Automatic program
- Clean Touch Steel front w/PureLine handle, fingerprint resistant
- Flexible basket design perfect for everyday use – Comfort baskets

EAN: 4002516376163 / Material number: 11636750 /  
Old Material Number: 21526663USA

<b>Type</b>	
Fully integrated dishwashers	•
24 inch dishwasher	•
<b>Design</b>	
Fascia color	Stainless Steel.
Fascia panel version	Fully integrated fascia
Control type	Programme selector button
Control panel	3-digit 7-segment display
Display color	Yellow
<b>Convenience</b>	
Door closing aid	AutoClose
Operating noise dB(A) re 1 pW	42
Countdown indicator	•
Delay start up to 24 hours	•
In-operation indication	acoustic
<b>Efficiency and sustainability</b>	
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
Energy Star	•
<b>Quality of results</b>	
Fresh water dishwasher	•
SensorDry	•
Active condensation drying	•
Perfect GlassCare	•
<b>Wash programs</b>	
QuickIntenseWash	•
Normal	•
Pots & Pans	•
SaniWash	•
Rinse & Hold	•
<b>Dishwashing options</b>	
Short	•
Extra Clean	•
Extra dry	•
<b>Baskets</b>	
Cutlery loading	3D MultiFlex Tray
FlexCare cup rack	1
Basket design	Comfort
<b>Safety</b>	
Waterproof system	•
<b>Technical data</b>	
Niche width min in in.(mm)	23 5/8 (600)
Niche width max in in.(mm)	23 5/8 (600)
Niche height min in in.(mm)	33 3/4 (855)
Niche height max in in.(mm)	36 1/4 (920)
Niche depth in in.(mm)	22 1/2 (570)

## G 5266 SCVi SF

Fully-integrated, full-size dishwasher

for optimum drying results thanks to AutoOpen drying.



EAN: 4002516376163 / Material number: 11636750 /

Old Material Number: 21526663USA

Appliance width in in.(mm)	23 5/8 (598)
Appliance height in in.(mm)	33 3/4 (855)
Appliance depth in in.(mm)	21 3/4 (550)
Appliance depth with door open in in.(cm)	47 1/2 (120.5)
Net weight in lbs. (kg)	111 (50.0)
Total connected load in kW	1.40
Voltage in V	120
Fuse rating in A	15
Number of phases	1
Electrical frequency standard	60
Length of water inlet hose in ft (m)	5 (1.50)
Length of water drain hose in ft (m)	5 (1.50)
Length of electrical wire in ft (m)	6 (1.70)
Min. front panel weight in kg	4.0
Max. front panel weight in kg	11.0
[can be retrofitted by Service to min.]	7.0
[can be retrofitted by Service to max.]	14.0
<b>Standard accessories</b>	
1 x UltraTabs box (20 tabs)	•
Voucher for 1 x box of UltraTabs (20 tabs) or 3 boxes (60 tabs in each) at a reduced price	•