

G 5892 SCVi SL

Fully integrated dishwasher
with networking for even greater convenience.



- QuickIntenseWash, superior cleaning and drying in under 60 min
- Completely dry – Miele AutoOpen drying
- A perfect view for convenient loading even in the dark – BrilliantLight
- More information options and modern domestic appliance networking – Miele@home
- Maximum flexibility and premium basket design – MaxiComfort baskets

EAN: 4002516376187 / Material number: 11636790 /
Old Material Number: 21589262USA

Type	
Fully integrated dishwashers	•
18 inch dishwasher	•
Design	
Fascia color	Stainless Steel.
Fascia panel version	Fully integrated fascia
Control type	Programme selector button
Control panel	1-line display with plain text
Display color	White
MultiLingua	•
Convenience	
Networking with Miele@home	•
Door closing aid	AutoClose
LED Lighting	•
Operating noise dB(A) re 1 pW	42
Countdown indicator	•
Delay start up to 24 hours	•
In-operation indication	Display, Control indicator, optical and acoustic
Efficiency and sustainability	
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
ENERGY STAR® Most Efficient	•
Quality of results	
Fresh water dishwasher	•
SensorDry	•
Active condensation drying	•
Perfect GlassCare	•
Wash programs	
QuickIntenseWash	•
Economy	•
Normal	•
Pots & Pans	•
China & Crystal	•
SaniWash	•
Energy Saver	•
ExtraQuiet 40 dB(A)	•
Glasses – No Rinse Aid	•
Appliance care	•
Dishwashing options	
Short	•
IntenseZone	•
Express	•
Extra Clean	•
Extra dry	•

G 5892 SCVi SL

Fully integrated dishwasher
with networking for even greater convenience.



EAN: 4002516376187 / Material number: 11636790 /
Old Material Number: 21589262USA

Baskets	
Cutlery loading	MultiFlex Tray 45
FlexCare glass holder	2
Basket design	MaxiComfort 18" (45 cm)
Safety	
Waterproof system	•
Check filter saturation indicator	•
Technical data	
Niche width min in in.(mm)	17 3/4 (450)
Niche width max in in.(mm)	17 3/4 (450)
Niche height min in in.(mm)	32 1/8 (815)
Niche height max in in.(mm)	34 3/4 (880)
Niche depth in in.(mm)	21 3/4 (550)
Appliance width in in.(mm)	17 3/4 (448)
Appliance height in in.(mm)	31 3/4 (805)
Appliance depth in in.(mm)	21 3/4 (550)
Appliance depth with door open in in.(cm)	45 7/8 (116.5)
Net weight in lbs. (kg)	90 (40.8)
Total connected load in kW	1.40
Voltage in V	120
Fuse rating in A	15
Number of phases	1
Electrical frequency standard	60
Length of water inlet hose in ft (m)	5 (1.50)
Length of water drain hose in ft (m)	5 (1.50)
Length of electrical wire in ft (m)	4 (1.20)
Min. front panel weight in kg	2.0
Max. front panel weight in kg	8.0
Standard accessories	
1 x UltraTabs box (20 tabs)	•
Voucher for 1 x box of UltraTabs (20 tabs) or 3 boxes (60 tabs in each) at a reduced price	•