

APWM 900

Lint filter compartment made of stainless steel for filtering lint and large particles out of the suds solution.



- For use with heavily soiled fabrics
- Volume approx. 18.5 gal, adjustable installation height 0-9 3/4"
- For connection to washing machines on a toe-kick
- Easily removable lint filter in stainless steel
- Hose connection Ø 3" (7.5 cm)

EAN: 4002516376668 / Material number: 11637370 / Old Material Number: 59510045D

Product category	
Washing machines	•
Machine/accessory category	
PW 413	•
PW 413 Mop Star 130	•
PW 418	•
PW 5064	•
PW 5062	•
PW 5055	•
PW 5065	•
PW 5064 MOP STAR 60	•
PW 5070	•
PW 5082	•
PW 5084 MOP STAR 80	•
PW 5104 MOP STAR 100	•
PW 5105 Vario	•
PW 5134 MOP STAR 130	•
PW 6055	•
PW 6065	•
PW 6055 Vario	•
PW 6065 Vario	•
PW 6065 Plus	•
PW 6068 Plus	•
PW 6080	•
PW 6088	•
PW 6107	•
PW 6137	•
PW 5136	•
PW 6163	•
PW 6167	•
PW 6207	•
PW 6241	•
PW 6243	•
PW 6321	•
PW 6323	•
PW 811	•
PW 814	•
PW 818	•
PW 9055	•
PW 9065	•
PWM 500-08	•
PWM 500-09	•
PWM 506 Mop Star 60	•
PWM 507	•
PWM 508 Mop Star 80	•
PWM 509	•
PWM 900-09	•
PWM 906	•
PWM 907	•
PWM 908	•

APWM 900

Lint filter compartment made of stainless steel
for filtering lint and large particles out of the suds solution.



EAN: 4002516376668 / Material number: 11637370 / Old Material Number: 59510045D

PWM 511	•
PWM 909	•
PWM 514	•
PWM 520	•
PWM 912	•
PWM 916	•
PWM 920	•
PDW 909	•
Product category	
Lint filter	•
Product characteristics	
Electrical connection	OHNE
Material	Stainless steel
Color	Stainless Steel
Dimensions and weight	
External dimensions, net height in inches	21 7/16 (543)
External dimensions, net width in inches	12 1/4 (310)
External dimensions, net depth in inches	25 9/16 (648)
External dimensions, gross height in inches	23 1/16 (585)
External dimensions, gross width in inches	13 (330)
External dimensions, gross depth in inches	27 9/16 (700)
Net weight [lbs]	32 (14.50)
Gross weight in lbs	35 (15.50)