

CM 6160 MilkPerfection
Countertop coffee machine
With WiFi Conn@ct and a wide selection of specialty coffees for maximum freedom.



- Creamy milk froth for a wide range of specialty coffees
- Perfect results and intense coffee flavor – AromaticSystem
- Two coffees at once at the touch of a button OneTouch for Two
- Convenient cleaning programs for care and maintenance
- Communication with the machine could not be easier – WiFiConn@ct

EAN: 4002516380641 / Material number: 11648170 / Old Material Number: 29616001USA

Construction type and design	
Countertop bean-to-cup coffee machine	•
Color	Lotus white
Consumer benefits	
AromaticSystem	•
OneTouch preparation	•
One Touch and OneTouch for Two	•
DoubleShot	•
Programmable User profile	4
Flavor preserving conical grinding unit	•
Grinding grade selectable	•
Additional coffee types in ground coffee form possible	•
Ground quantity programmable	•
Water quantity programmable	•
Water temperature programmable	•
Amount of milk can be programmed	•
Amount of milk froth can be programmed	•
Pre-brewing programmable	•
TeaTimer	•
Control panel	
Networking with Miele@home	•
Control panel	DirectSensor
PerformanceMode	•
BrilliantLight	•
Expert mode	•
MultiLingua	•
No. of bean types	1
No. of bean containers	1
Bean container capacity, each in oz (g)	300
Bean container capacity, total in oz (g)	10.58 (300)
Capacity of water container in fl oz (I)	60.87 (1.8)
Capacity of waste container in servings	10
Drip tray capacity in fl oz (I)	27.05 (0.8)
Easily accessible containers	•
Programmable stand-by time	•
Individual settings	•
Beverages	
Adjustable beverage portion size in ml	20-300
Ristretto, single	•
Ristretto, double	•
Espresso, single	•
Espresso, double	•
Coffee, single	•
Coffee, double	•
Long coffee, single	•
Long coffee, double	•
Cappuccino, single	•
Cappuccino, double	•
Latte macchiato, single	•
Latte macchiato, double	•



CM 6160 MilkPerfection Countertop coffee machine With WiFi Conn@ct and a wide selection of specialty coffees for maximum freedom.



EAN: 4002516380641 / Material number: 11648170 / Old Material Number: 29616001USA

Latte macchiato, double Milk froth, single Espresso macchiato, single Espresso macchiato, single Espresso macchiato, double Cappuccino italiano, single Cappuccino italiano, single Elat white, double Café au lait, single Café au lait, single Café au lait, double Caffe latte, single Caffe latte, single Allwater Hot water, single Black tea, single Herbal tea, single Fruit tea, single Coffee pot Efficiency and sustainability Energy-saving Eco mode option Power rating in standby mode in W Cleaning convenience Manual descaling Auto-Off function ComfortClean Removable milk pipework Permovable milk pipework Permovable remix pipework Permovable remix pipework Pelight-adjustable serving spout in inches (cm) Applicance height in in.(mm) Applicance height in in.(mm) Applicance height in in.(mm) Applicance height in in.(mm) Tous remix for the milk pipework Puse rating in A 15 Number of phases 16 Pump pressure in bar Length of phases 17 Pump pressure in bar Length of phases 15 Pump pressure in bar Length of electrical wire in ft (m) Accessories supplied Stainless-steel milk rod	Hot milk, single	•
Milk froth, double Milk froth, double Espresso macchiato, single Espresso macchiato, double Cappuccino italiano, single Cappuccino italiano, double Flat white, single Flat white, single Café au lait, single Café au lait, double Café au lait, single Café au lait, single Café au lait, double Allwater Flat white, double Allwater Black tea, single Fruit tea, single Fruit tea, single Green tea, single Green tea, single Coffee pot Efficiency and sustainability Energy-saving Eco mode option Power rating in standby mode in W Cleaning convenience Manual descaling Automatic rinsing of the milk pipework from the water container Convenient cleaning programs Auto-Off function ComfortClean Removable milk pipework Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) 5 5/8 (14.0) Height-adjustable serving spout in inches (cm) 5 16/8 (427) Total connected load in kW 1.45 Number of phases Pump pressure in bar Length of electrical wire in ft (m) Accessories supplied		•
Milk froth, double Espresso macchiato, single Espresso macchiato, double Cappuccino italiano, single Cappuccino italiano, double Flat white, single Cafe au lait, single Café au lait, single Café au lait, single Café au lait, double Café au lait, double Caffe latte, single Black tea, single Hort water, single Fruit tea, single Fruit tea, single Green tea, single Japanese tea, single Japanese tea, single Coffe pot Efficiency and sustainability Energy-saving Eco mode option Power rating in standby mode in W Power rating in networked standby in W Cleaning convenience Manual descaling Automatic rinsing of the milk pipework from the water container Convenient cleaning programs Auto-Off function ComfortClean Removable brew unit Adjustable water hardness Petholical data Height-adjustable serving spout in inches (cm) Appliance wight in in.(mm) 10 (251) Appliance height in in.(mm) 11 (478 (327) Total connected load in kW 1.48 Number of phases 1 Pump pressure in bar Length of electrical wire in ft (m) 4 (1.4) Accessories supplied	 	•
Espresso macchiato, single Espresso macchiato, double Cappuccino italiano, single Elat white, single Flat white, single Café au lait, single Café au lait, double Café latte, single Café al laite, double Allwater Hot water, single Black tea, single Black tea, single Fruit tea, single Fruit tea, single Green tea, single Green tea, single Fruit tea, single Coffee pot Efficiency and sustainability Energy-saving Eco mode option Power rating in standby mode in W Cleaning convenience Manual descaling Auto-Off function Cornvenient cleaning programs Auto-Off function Envolvable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) 10 (251) Appliance width in in.(mm) 14 1/4 (359) Appliance depth in in.(mm) 15 Length of electrical wire in ft (m) Accessories supplied		•
Espresso macchiato, double Cappuccino italiano, single Cappuccino italiano, double Elat white, single Elat white, single Elat white, single Elat white, double Café au lait, single Elat white, double Elat white, single Elat kea, s		•
Cappuccino italiano, single Cappuccino italiano, double Flat white, single Flat white, double Café au lait, single Café au lait, double Café au lait, double Caffe latte, single Caffe latte, single Caffe latte, double		•
Cappuccino italiano, double Flat white, single Flat white, double Café au lait, single Café au lait, double Allwater Hot water, single Black tea, single Black tea, single Fruit tea, single Fruit tea, single Fruit tea, single Green tea, single Fruit tea, single Fruit tea, single Green tea, single Fruit tea, single Fruit tea, single Green tea, single Fruit tea, single Fruit tea, single Fruit tea, single Fruit tea, single Green tea, single Fruit tea		•
Flat white, single Flat white, double Café au lait, single Café au lait, double Café au lait, double Café latte, single Caffè latte, single Caffè latte, single Caffè latte, single Caffè latte, double Allwater Hot water, single Black tea, single Herbal tea, single Fruit tea, single Fruit tea, single Fruit tea, single Vhite tea, single Fruit tea, single Fruit tea, single Vhite tea, single Fruit tea, single Vhite tea, single Vhite tea, single Vhite tea, single Vhite tea, single Voffee pot Fruit tea, single Voffee pot Fruit tea, single Voffee pot V		
Flat white, double Café au lait, single Café au lait, double Caffé latte, double Caffé latte, double Allwater Hot water, single Black tea, single Fruit tea, single Fruit tea, single Fruit tea, single Green tea, single White tea, single Frout tea, single Fruit tea, single Fruit tea, single Green tea, single Fruit tea, single Fruit tea, single Green tea, single Fruit tea, single Offee pot Fficiency and sustainability Energy-saving Eco mode option Power rating in networked standby in W Cleaning convenience Manual descaling Automatic rinsing of the milk pipework from the water container Convenient cleaning programs Auto-Off function ComfortClean Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Appliance depth in in.(mm) Appliance depth in in.(mm) Appliance depth in in.(mm) Appliance depth in in.(mm) Fume pressure in bar Length of electrical wire in ft (m) Accessories supplied		
Café au lait, single Café au lait, double Caffè latte, single Caffè latte, double Allwater Hot water, single Black tea, single Black tea, single Fruit tea, single Fruit tea, single Green tea, single White tea, single Japanese tea, single Japanese tea, single Coffee pot Efficiency and sustainability Energy-saving Eco mode option Power rating in networked standby in W Cleaning convenience Manual descaling Automatic rinsing of the milk pipework from the water container Convenient cleaning programs Auto-Off function ComfortClean Removable milk pipework Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) 10 (251) Appliance depth in in.(mm) 16 7/8 (427) Total connected load in kW Voltage in V Fuse rating in A Number of phases 1 Length of electrical wire in ft (m) Accessories supplied		•
Café au lait, double Caffé latte, single Caffé latte, single Caffé latte, double Allwater Hot water, single Black tea, single Herbal tea, single Fruit tea, single Fruit tea, single Fruit tea, single Green tea, single White tea, single Japanese tea, single Offee pot Freiron data sustainability Energy-saving Eco mode option Power rating in standby mode in W O.1 Power rating in networked standby in W Cleaning convenience Manual descaling Automatic rinsing of the milk pipework from the water container Convenient cleaning programs Auto-Off function ComfortClean Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) 10 (251) Appliance depth in in.(mm) 14 1/4 (359) Appliance depth in in.(mm) 16 7/8 (427) Total connected load in kW Voltage in V Fump pressure in bar Length of electrical wire in ft (m) Accessories supplied		-
Caffè latte, single Caffè latte, double Allwater Hot water, single Black tea, single Herbal tea, single Fruit tea, single Fruit tea, single Green tea, single White tea, single White tea, single Green tea, single White tea, single Coffee pot Efficiency and sustainability Energy-saving Eco mode option Power rating in standby mode in W O.1 Power rating in networked standby in W Cleaning convenience Manual descaling Automatic rinsing of the milk pipework from the water container Convenient cleaning programs Auto-Off function ComfortClean Removable milk pipework Removable milk pipework Removable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Appliance depth in in.(mm) 10 (251) Appliance depth in in.(mm) 114 (4(359) Appliance depth in in.(mm) 15 (200) Appliance depth in in.(mm) 16 (7/8 (427) Total connected load in kW Voltage in V 120 Fuse rating in A Number of phases 1 Length of electrical wire in ft (m) Accessories supplied		•
Caffè latte, double Allwater Hot water, single Black tea, single Herbal tea, single Fruit tea, single Green tea, single Japanese tea, single Offee pot Efficiency and sustainability Energy-saving Eco mode option Power rating in standby mode in W Power rating in networked standby in W Cleaning convenience Manual descaling Automatic rinsing of the milk pipework from the water container Convenient cleaning programs Auto-Off function ComfortClean Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Appliance depth in in.(mm) 10 (251) Appliance depth in in.(mm) 114 (4(359) Appliance depth in in.(mm) 15 (200) Rump ressure in bar Length of electrical wire in ft (m) Accessories supplied		
Allwater Hot water, single Black tea, single Herbal tea, single Fruit tea, single Green tea, single Japanese tea, single White tea, single Japanese tea, sin		
Black tea, single		<u> </u>
Black tea, single Herbal tea, single Fruit tea, single Green tea, single White tea, single Offee tea, single Coffee pot Efficiency and sustainability Energy-saving Eco mode option Power rating in standby mode in W Power rating in networked standby in W Cleaning convenience Manual descaling Automatic rinsing of the milk pipework from the water container Convenient cleaning programs Auto-Off function ComfortClean Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Appliance width in in.(mm) Appliance depth in in.(mm) Appliance depth in in.(mm) Total connected load in kW Voltage in V Fuse rating in A Number of phases Pump pressure in bar Length of electrical wire in ft (m) Accessories supplied		
Herbal tea, single Fruit tea, single Green tea, single White tea, single Japanese tea, single Coffee pot Efficiency and sustainability Energy-saving Eco mode option Power rating in standby mode in W Cleaning convenience Manual descaling Automatic rinsing of the milk pipework from the water container Convenient cleaning programs Auto-Off function ComfortClean Removable milk pipework Removable briew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Appliance depth in in.(mm) Appliance depth in in.(mm) Appliance depth in in.(mm) Total connected load in kW Voltage in V Fump pressure in bar Length of electrical wire in ft (m) Accessories supplied		
Fruit tea, single Green tea, single White tea, single Japanese tea, single Japanese tea, single Coffee pot Efficiency and sustainability Energy-saving Eco mode option Power rating in standby mode in W Power rating in networked standby in W Cleaning convenience Manual descaling Automatic rinsing of the milk pipework from the water container Convenient cleaning programs Auto-Off function ComfortClean Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Appliance depth in in.(mm) Appliance depth in in.(mm) Total connected load in kW Voltage in V Length of electrical wire in ft (m) Accessories supplied		
Green tea, single White tea, single Japanese tea, single Coffee pot Efficiency and sustainability Energy-saving Eco mode option Power rating in standby mode in W O.1 Power rating in networked standby in W Cleaning convenience Manual descaling Automatic rinsing of the milk pipework from the water container Convenient cleaning programs Auto-Off function ComfortClean Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Applicance height in in.(mm) Appliance depth in in.(mm) Total connected load in kW Voltage in V Fuse rating in A Number of phases Pump pressure in bar Length of electrical wire in ft (m) Accessories supplied		
White tea, single Japanese tea, single Coffee pot Efficiency and sustainability Energy-saving Eco mode option Power rating in standby mode in W O.5 Cleaning convenience Manual descaling Automatic rinsing of the milk pipework from the water container Convenient cleaning programs Auto-Off function ComfortClean Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Applicance height in in.(mm) Applicance height in in.(mm) Applicance depth in in.(mm) Total connected load in kW Voltage in V Fuse rating in A Number of phases 1 Pump pressure in bar Length of electrical wire in ft (m) Accessories supplied		
Japanese tea, single Coffee pot Efficiency and sustainability Energy-saving Eco mode option Power rating in standby mode in W Cleaning convenience Manual descaling Automatic rinsing of the milk pipework from the water container Convenient cleaning programs Auto-Off function ComfortClean Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Appliance height in in.(mm) Appliance depth in in.(mm) Total connected load in kW Voltage in V Fuse rating in A Number of phases Pump pressure in bar Length of electrical wire in ft (m) Accessories supplied		
Coffee pot Efficiency and sustainability Energy-saving Eco mode option Power rating in standby mode in W Cleaning convenience Manual descaling Automatic rinsing of the milk pipework from the water container Convenient cleaning programs Auto-Off function ComfortClean Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Applicance height in in.(mm) Appliance depth in in.(mm) Total connected load in kW Voltage in V Fuse rating in A Number of phases Pump pressure in bar Length of electrical wire in ft (m) Accessories supplied		
Efficiency and sustainability Energy-saving Eco mode option Power rating in standby mode in W O.1 Power rating in networked standby in W O.5 Cleaning convenience Manual descaling Automatic rinsing of the milk pipework from the water container Convenient cleaning programs Auto-Off function ComfortClean Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Appliance depth in in.(mm) 10 (251) Appliance depth in in.(mm) 16 7/8 (427) Total connected load in kW Voltage in V 120 Fuse rating in A Number of phases 1 Pump pressure in bar Length of electrical wire in ft (m) Accessories supplied		
Energy-saving Eco mode option Power rating in standby mode in W O.1 Power rating in networked standby in W O.5 Cleaning convenience Manual descaling Automatic rinsing of the milk pipework from the water container Convenient cleaning programs Auto-Off function ComfortClean Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Appliance depth in in.(mm) 10 (251) Appliance depth in in.(mm) 16 7/8 (427) Total connected load in kW Voltage in V 120 Fuse rating in A Number of phases 1 Pump pressure in bar Length of electrical wire in ft (m) Accessories supplied	•	•
Power rating in standby mode in W Power rating in networked standby in W Cleaning convenience Manual descaling Automatic rinsing of the milk pipework from the water container Convenient cleaning programs Auto-Off function ComfortClean Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Applicance height in in.(mm) Appliance depth in in.(mm) Total connected load in kW Voltage in V Pump pressure in bar Length of electrical wire in ft (m) Accessories supplied		
Power rating in networked standby in W Cleaning convenience Manual descaling Automatic rinsing of the milk pipework from the water container Convenient cleaning programs Auto-Off function ComfortClean Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Applicance height in in.(mm) Appliance depth in in.(mm) Total connected load in kW Voltage in V Fump pressure in bar Length of electrical wire in ft (m) Accessories supplied		
Cleaning convenience Manual descaling • Automatic rinsing of the milk pipework from the water container • Convenient cleaning programs • Auto-Off function • ComfortClean • Removable milk pipework • Removable brew unit • Adjustable water hardness • Technical data • Height-adjustable serving spout in inches (cm) 5 5/8 (14.0) Height-adjustable serving spout in inches (cm) 3 1/4 (8.0) Appliance width in in.(mm) 10 (251) Applicance height in in.(mm) 14 1/4 (359) Applicance depth in in.(mm) 16 7/8 (427) Total connected load in kW 1.45 Voltage in V 120 Fuse rating in A 15 Number of phases 1 Pump pressure in bar 15 Length of electrical wire in ft (m) 4 (1.4) Accessories supplied		
Manual descaling Automatic rinsing of the milk pipework from the water container Convenient cleaning programs Auto-Off function ComfortClean Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Applicance height in in.(mm) Appliance depth in in.(mm) Total connected load in kW Voltage in V Fuse rating in A Number of phases Pump pressure in bar Length of electrical wire in ft (m) Accessories supplied		0.5
Automatic rinsing of the milk pipework from the water container Convenient cleaning programs Auto-Off function ComfortClean Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Appliance height in in.(mm) Appliance depth in in.(mm) Total connected load in kW Voltage in V Fuse rating in A Number of phases Length of electrical wire in ft (m) Auto-Off function • Auto-Off function • Auto-Off function • 5 /* 6 /* 8 /* 1 /	9	
container Convenient cleaning programs Auto-Off function ComfortClean Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Appliance height in in.(mm) Appliance depth in in.(mm) Total connected load in kW Voltage in V Fuse rating in A Number of phases Pump pressure in bar Length of electrical wire in ft (m) Auto-Off function • Converted to electrical wire in ft (m) • Auto-Off function • Solution • Solution • Solution • Auto-Off function • Solution		
Auto-Off function ComfortClean Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Appliance height in in.(mm) Appliance depth in in.(mm) Total connected load in kW Voltage in V Fuse rating in A Number of phases Pump pressure in bar Length of electrical wire in ft (m) Agenovable milk pipework e 9 8 8 1 9 8 1 1 1 1 1 1 1 1 1 1 1 1		•
ComfortClean Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Appliance height in in.(mm) Appliance depth in in.(mm) Total connected load in kW Voltage in V Fuse rating in A Number of phases Pump pressure in bar Length of electrical wire in ft (m) Adjustable serving spout in inches (cm) 5 5/8 (14.0) 5 5/8 (14.0) 10 (251) 10 (251) 11 (359) 12 (427) 120 120 15 15 Length of electrical wire in ft (m) Accessories supplied	Convenient cleaning programs	•
Removable milk pipework Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Appliance height in in.(mm) Appliance depth in in.(mm) Appliance depth in in.(mm) Total connected load in kW Voltage in V Fuse rating in A Number of phases Pump pressure in bar Length of electrical wire in ft (m) Addustable serving spout in inches (cm) 5 5/8 (14.0) 10 (251) 11 (251) 12 (251) 14 1/4 (359) 15 (14.0) 15 (15.0) 16 7/8 (427) 17 (15.0) 18 (16.0) 19 (17.0) 19 (17.0) 10 (17.0) 10 (17.0) 11 (17.0) 11 (17.0) 12 (17.0) 13 (17.0) 14 (1.4) 15 (17.0) 16 (17.0) 17 (17.0) 18 (17.0) 18 (17.0) 19 (17.0) 1	Auto-Off function	•
Removable brew unit Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Applicance height in in.(mm) Appliance depth in in.(mm) 16 7/8 (427) Total connected load in kW Voltage in V Fuse rating in A Number of phases Pump pressure in bar Length of electrical wire in ft (m) Addata • 15 • 16 17 18 18 19 19 19 10 10 10 11 11 12 15 15 15 16 17 18 18 18 18 18 18 18 18 18	ComfortClean	•
Adjustable water hardness Technical data Height-adjustable serving spout in inches (cm) Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Applicance height in in.(mm) Appliance depth in in.(mm) Total connected load in kW Voltage in V Fuse rating in A Number of phases Pump pressure in bar Length of electrical wire in ft (m) Accessories supplied 5 5/8 (14.0) 5 5/8 (14.0) 5 1/4 (8.0) 10 (251) 10 (251) 11 (4 (359) 12 (1-4) 15 (1-4) 4 (1.4)	Removable milk pipework	•
Technical dataHeight-adjustable serving spout in inches (cm)5 5/8 (14.0)Height-adjustable serving spout in inches (cm)3 1/4 (8.0)Appliance width in in.(mm)10 (251)Applicance height in in.(mm)14 1/4 (359)Appliance depth in in.(mm)16 7/8 (427)Total connected load in kW1.45Voltage in V120Fuse rating in A15Number of phases1Pump pressure in bar15Length of electrical wire in ft (m)4 (1.4)Accessories supplied	Removable brew unit	•
Height-adjustable serving spout in inches (cm) Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Applicance height in in.(mm) Appliance depth in in.(mm) Total connected load in kW Voltage in V Fuse rating in A Number of phases Pump pressure in bar Length of electrical wire in ft (m) A 14 (8.0) 3 1/4 (8.0) 10 (251) 14 1/4 (359) 16 7/8 (427) 120 Fuse rating in A 15 Number of phases 1 Pump description of electrical wire in ft (m) Accessories supplied	Adjustable water hardness	•
Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Applicance height in in.(mm) Appliance depth in in.(mm) Total connected load in kW Voltage in V Fuse rating in A Number of phases Pump pressure in bar Length of electrical wire in ft (m) Appliance width in in.(mm) 10 (251) 14 1/4 (359) 16 7/8 (427) 1.45 1.45 1.45 1.5 1.5 1.6 1.7 1.6 1.7 1.7 1.7 1.7 1.8 1.9 1.9 1.9 1.9 1.9 1.9 1.9	Technical data	
Height-adjustable serving spout in inches (cm) Appliance width in in.(mm) Applicance height in in.(mm) Appliance depth in in.(mm) Total connected load in kW Voltage in V Fuse rating in A Number of phases Pump pressure in bar Length of electrical wire in ft (m) Appliance width in in.(mm) 10 (251) 14 1/4 (359) 16 7/8 (427) 1.45 1.45 1.45 1.5 1.5 1.6 1.7 1.6 1.7 1.7 1.7 1.7 1.8 1.9 1.9 1.9 1.9 1.9 1.9 1.9	Height-adjustable serving spout in inches (cm)	5 5/8 (14.0)
Appliance width in in.(mm) Applicance height in in.(mm) Appliance depth in in.(mm) Appliance depth in in.(mm) Total connected load in kW Voltage in V Fuse rating in A Number of phases Pump pressure in bar Length of electrical wire in ft (m) Accessories supplied	Height-adjustable serving spout in inches (cm)	
Applicance height in in.(mm) Appliance depth in in.(mm) Total connected load in kW Voltage in V Fuse rating in A Number of phases Pump pressure in bar Length of electrical wire in ft (m) Accessories supplied		
Appliance depth in in.(mm) Total connected load in kW 1.45 Voltage in V 120 Fuse rating in A Number of phases Pump pressure in bar Length of electrical wire in ft (m) Accessories supplied		-
Total connected load in kW 1.45 Voltage in V 120 Fuse rating in A 15 Number of phases 1 Pump pressure in bar 15 Length of electrical wire in ft (m) 4 (1.4) Accessories supplied		
Voltage in V 120 Fuse rating in A 15 Number of phases 1 Pump pressure in bar 15 Length of electrical wire in ft (m) 4 (1.4) Accessories supplied		
Fuse rating in A 15 Number of phases 1 Pump pressure in bar 15 Length of electrical wire in ft (m) 4 (1.4) Accessories supplied		
Number of phases 1 Pump pressure in bar 15 Length of electrical wire in ft (m) 4 (1.4) Accessories supplied		_
Pump pressure in bar 15 Length of electrical wire in ft (m) 4 (1.4) Accessories supplied		
Length of electrical wire in ft (m) 4 (1.4) Accessories supplied		
Accessories supplied		_
		. (,
Commission Steel Hilliam		•



CM 6160 MilkPerfection Countertop coffee machine With WiFi Conn@ct and a wide selection of specialty coffees for maximum freedom.



EAN: 4002516380641 / Material number: 11648170 / Old Material Number: 29616001USA

Descaling tablets	•
Cleaning tablets	•
Brief operating instructions on rear of unit	•
Available display languages	
Available display languages via MultiLingua	bahasa malaysia, dansk, deutsch, english, español, français, hrvatski, italiano, magyar, nederlands, norsk, polski, português,

deutsch, english, español, français, hrvatski, italiano, magyar, nederlands, norsk, polski, português, pycский, română, slovenčina, slovenščina, srpski, suomi, svenska, türkçe, українська, čeština, ελληνικά, , , , ,