

CM 6160 MilkPerfection Countertop coffee machine

With WiFi Conn@ct and a wide selection of specialty coffees for maximum freedom.



- Creamy milk froth for a wide range of specialty coffees
- Perfect results and intense coffee flavor – AromaticSystem
- Two coffees at once at the touch of a button – OneTouch for Two
- Convenient cleaning programs for care and maintenance
- Communication with the machine could not be easier – WiFiConn@ct

EAN: 4002516380658 / Material number: 11648180 / Old Material Number: 29616020USA

Construction type and design	
Countertop bean-to-cup coffee machine	•
Color	Obsidian Black
Convenience features	
AromaticSystem	•
OneTouch preparation	•
One Touch and OneTouch for Two	•
DoubleShot	•
Programmable User profile	4
Flavor preserving conical grinding unit	•
Grinding grade selectable	•
Additional coffee types in ground coffee form possible	•
Ground quantity programmable	•
Water quantity programmable	•
Water temperature programmable	•
Amount of milk can be programmed	•
Amount of milk froth can be programmed	•
Pre-brewing programmable	•
TeaTimer	•
User convenience	
Networking with Miele@home	•
Control panel	DirectSensor
Height adjustment of infinitely adjustable central spout min in in.(cm)	3 1/4 (8.0)
Height adjustment of infinitely adjustable central spout max in in.(cm)	5 5/8 (14.0)
PerformanceMode	•
BrilliantLight	•
Expert mode	•
MultiLingua	•
No. of bean types	1
No. of bean containers	1
Bean container capacity, each in oz (g)	300
Bean container capacity, total in oz (g)	10.58 (300)
Capacity of water container in fl oz (l)	60.87 (1.8)
Capacity of waste container in servings	10
Drip tray capacity in fl oz (l)	27.05 (0.8)
Easily accessible containers	•
Programmable stand-by time	•
Individual settings	•
Drink specialties	
Adjustable beverage portion size in ml	20-300
Ristretto, single	•
Ristretto, double	•
Espresso, single	•
Espresso, double	•
Coffee, single	•
Coffee, double	•
Long coffee, single	•
Long coffee, double	•

CM 6160 MilkPerfection

Countertop coffee machine

With WiFi Conn@ct and a wide selection of specialty coffees for maximum freedom.



EAN: 4002516380658 / Material number: 11648180 / Old Material Number: 29616020USA

Cappuccino, single	•
Cappuccino, double	•
Latte macchiato, single	•
Latte macchiato, double	•
Hot milk, single	•
Latte macchiato, double	•
Milk froth, single	•
Milk froth, double	•
Espresso macchiato, single	•
Espresso macchiato, double	•
Cappuccino italiano, single	•
Cappuccino italiano, double	•
Flat white, single	•
Flat white, double	•
Café au lait, single	•
Café au lait, double	•
Caffè latte, single	•
Caffè latte, double	•
Allwater	•
Hot water, single	•
Black tea, single	•
Herbal tea, single	•
Fruit tea, single	•
Green tea, single	•
White tea, single	•
Japanese tea, single	•
Coffee pot	•
Efficiency and sustainability	
Energy-saving Eco mode option	•
Power rating in standby mode in W	0.1
Power rating in networked standby in W	0.5
Cleaning convenience	
Manual descaling	•
Automatic rinsing of the milk pipework from the water container	•
Convenient cleaning programs	•
Auto-Off function	•
ComfortClean	•
Removable milk pipework	•
Removable brew unit	•
Adjustable water hardness	•
Technical data	
Appliance width in in.(mm)	10 (251)
Appliance height in in.(mm)	14 1/4 (359)
Appliance depth in in.(mm)	16 7/8 (427)
Total connected load in kW	1.45
Voltage in V	120
Fuse rating in A	15
Number of phases	1
Pump pressure in bar	15
Length of electrical wire in ft (m)	4 (1.4)
Standard accessories	
Stainless-steel milk rod	•

Miele

CM 6160 MilkPerfection

Countertop coffee machine

With WiFi Conn@ct and a wide selection of specialty coffees for maximum freedom.