

CM 6360 MilkPerfection
Countertop coffee machine
With WiFi Conn@ct, high-quality milk container, and many specialty coffees.



- Creamy milk froth for a wide range of specialty coffees
- Perfect results and intense coffee flavor – AromaticSystem
- Two coffees at once at the touch of a button – OneTouch for Two
- Convenient cleaning programs for care and maintenance
- Communication with the machine could not be easier – WiFiConn@ct

EAN: 4002516380672 / Material number: 11648200 /
Old Material Number: 29636011USA

Construction type and design

Appliance colour Obsidian black.CS

Available display languages

Available display languages via MultiLingua

bahasa malaysia, dansk, deutsch, english, español, français, hrvatski, italiano, magyar, nederland, norsk, polski, português, русский, română, slovenčina, slovenščina, srpski, suomi, svenska, türkçe, українська, čeština, ελληνικά, [?][?][?][?][?][?], [?][?], [?][?], [?][?], [?][?][?][?], [?][?][?]

Construction type and design

Countertop bean-to-cup coffee machine

Convenience features

AromaticSystem	•
OneTouch preparation	•
One Touch and OneTouch for Two	•
DoubleShot	•
Programmable User profile	8
Flavor preserving conical grinding unit	•
Grinding grade selectable	•
Additional coffee types in ground coffee form possible	•
Ground quantity programmable	•
Water quantity programmable	•
Water temperature programmable	•
Amount of milk can be programmed	•
Amount of milk froth can be programmed	•
Pre-brewing programmable	•
TeaTimer	•

User convenience

Networking with Miele@home	•
Control panel	DirectSensor
PerformanceMode	•
BrilliantLight	•
Expert mode	•
Heated cup storage area	•
MultiLingua	•
No. of bean types	1
No. of bean containers	1
Bean container capacity, each in oz (g)	300
Bean container capacity, total in oz (g)	10.58 (300)
Capacity of water container in fl oz (l)	60.87 (1.8)
Milk container capacity in l	0.7
Capacity of waste container in servings	10
Drip tray capacity in fl oz (l)	27.05 (0.8)
Easily accessible containers	•
Programmable stand-by time	•

CM 6360 MilkPerfection
Countertop coffee machine
With WiFi Conn@ct, high-quality milk container, and many specialty coffees.



EAN: 4002516380672 / Material number: 11648200 /
Old Material Number: 29636011USA

Individual settings	•
Drink specialties	
Adjustable beverage portion size in ml	20-300
Ristretto, single	•
Ristretto, double	•
Espresso, single	•
Espresso, double	•
Coffee, single	•
Coffee, double	•
Long coffee, single	•
Long coffee, double	•
Cappuccino, single	•
Cappuccino, double	•
Latte macchiato, single	•
Latte macchiato, double	•
Hot milk, single	•
Latte macchiato, double	•
Milk froth, single	•
Milk froth, double	•
Espresso macchiato, single	•
Espresso macchiato, double	•
Cappuccino italiano, single	•
Cappuccino italiano, double	•
Flat white, single	•
Flat white, double	•
Café au lait, single	•
Café au lait, double	•
Caffè latte, single	•
Caffè latte, double	•
Allwater	•
Hot water, single	•
Black tea, single	•
Herbal tea, single	•
Fruit tea, single	•
Green tea, single	•
White tea, single	•
Japanese tea, single	•
Coffee pot	•
Efficiency and sustainability	
Energy-saving Eco mode option	•
Power rating in standby mode in W	0.3
Power rating in networked standby in W	1.0
Cleaning convenience	
Manual descaling	•
Automatic rinsing of the milk pipework from the water container	•
Convenient cleaning programs	•
Auto-Off function	•
ComfortClean	•

CM 6360 MilkPerfection

Countertop coffee machine

With WiFi Conn@ct, high-quality milk container, and many specialty coffees.



EAN: 4002516380672 / Material number: 11648200 /

Old Material Number: 29636011USA

Removable milk pipework	•
Removable brew unit	•
Adjustable water hardness	•

Technical data

Height-adjustable serving spout in inches (cm)	5 5/8 (14.0)
Height-adjustable serving spout in inches (cm)	3 1/4 (8.0)
Appliance width in in.(mm)	10 (251)
Appliance height in in.(mm)	14 1/4 (359)
Appliance depth in in.(mm)	16 7/8 (427)
Total connected load in kW	1.45
Voltage in V	120
Fuse rating in A	15
Number of phases	1
Pump pressure in bar	15
Length of electrical wire in ft (m)	4 (1.4)

Standard accessories

Stainless-steel milk rod	•
Glass milk container	•
Descaling tablets	•
Cleaning tablets	•
Brief operating instructions on rear of unit	•