

CM 6360 MilkPerfection

Countertop coffee machine

With WiFi Conn@ct, high-quality milk container, and many specialty coffees.



- Creamy milk froth for a wide range of specialty coffees
- Perfect results and intense coffee flavor – AromaticSystem
- Two coffees at once at the touch of a button – OneTouch for Two
- Convenient cleaning programs for care and maintenance
- Communication with the machine could not be easier – WiFiConn@ct

EAN: 4002516380672 / Material number: 11648200 / Old Material Number: 29636011USA

| Construction type and design | |
|---|--------------|
| Countertop bean-to-cup coffee machine | • |
| Convenience features | |
| AromaticSystem | • |
| OneTouch preparation | • |
| One Touch and OneTouch for Two | • |
| DoubleShot | • |
| Programmable User profile | 8 |
| Flavor preserving conical grinding unit | • |
| Grinding grade selectable | • |
| Additional coffee types in ground coffee form possible | • |
| Ground quantity programmable | • |
| Water quantity programmable | • |
| Water temperature programmable | • |
| Amount of milk can be programmed | • |
| Amount of milk froth can be programmed | • |
| Pre-brewing programmable | • |
| TeaTimer | • |
| User convenience | |
| Networking with Miele@home | • |
| Control panel | DirectSensor |
| Height adjustment of infinitely adjustable central spout min in in.(cm) | 3 1/4 (8.0) |
| Height adjustment of infinitely adjustable central spout max in in.(cm) | 5 5/8 (14.0) |
| PerformanceMode | • |
| BrilliantLight | • |
| Expert mode | • |
| Heated cup storage area | • |
| MultiLingua | • |
| No. of bean types | 1 |
| No. of bean containers | 1 |
| Bean container capacity, each in oz (g) | 300 |
| Bean container capacity, total in oz (g) | 10.58 (300) |
| Capacity of water container in fl oz (l) | 60.87 (1.8) |
| Milk container capacity in l | 0.7 |
| Capacity of waste container in servings | 10 |
| Drip tray capacity in fl oz (l) | 27.05 (0.8) |
| Easily accessible containers | • |
| Programmable stand-by time | • |
| Individual settings | • |
| Drink specialties | |
| Adjustable beverage portion size in ml | 20-300 |
| Ristretto, single | • |
| Ristretto, double | • |
| Espresso, single | • |
| Espresso, double | • |
| Coffee, single | • |
| Coffee, double | • |
| Long coffee, single | • |

CM 6360 MilkPerfection

Countertop coffee machine

With WiFi Conn@ct, high-quality milk container, and many specialty coffees.



EAN: 4002516380672 / Material number: 11648200 / Old Material Number: 29636011USA

| | |
|---|--------------|
| Long coffee, double | • |
| Cappuccino, single | • |
| Cappuccino, double | • |
| Latte macchiato, single | • |
| Latte macchiato, double | • |
| Hot milk, single | • |
| Latte macchiato, double | • |
| Milk froth, single | • |
| Milk froth, double | • |
| Espresso macchiato, single | • |
| Espresso macchiato, double | • |
| Cappuccino italiano, single | • |
| Cappuccino italiano, double | • |
| Flat white, single | • |
| Flat white, double | • |
| Café au lait, single | • |
| Café au lait, double | • |
| Caffè latte, single | • |
| Caffè latte, double | • |
| Allwater | • |
| Hot water, single | • |
| Black tea, single | • |
| Herbal tea, single | • |
| Fruit tea, single | • |
| Green tea, single | • |
| White tea, single | • |
| Japanese tea, single | • |
| Coffee pot | • |
| Efficiency and sustainability | |
| Energy-saving Eco mode option | • |
| Power rating in standby mode in W | 0.1 |
| Power rating in networked standby in W | 0.5 |
| Cleaning convenience | |
| Manual descaling | • |
| Automatic rinsing of the milk pipework from the water container | • |
| Convenient cleaning programs | • |
| Auto-Off function | • |
| ComfortClean | • |
| Removable milk pipework | • |
| Removable brew unit | • |
| Adjustable water hardness | • |
| Technical data | |
| Appliance width in in.(mm) | 10 (251) |
| Appliance height in in.(mm) | 14 1/4 (359) |
| Appliance depth in in.(mm) | 16 7/8 (427) |
| Total connected load in kW | 1.45 |
| Voltage in V | 120 |
| Fuse rating in A | 15 |
| Number of phases | 1 |
| Pump pressure in bar | 15 |
| Length of electrical wire in ft (m) | 4 (1.4) |

Miele

CM 6360 MilkPerfection

Countertop coffee machine

With WiFi Conn@ct, high-quality milk container, and many specialty coffees.