

PDR 914 [EL SOM]

Vented dryer, electric heating

with programmable M Touch Pro controls, for marine applications.



- Drum volume 8.83 (250.00) ft³ (l), load size 23 (10.0) lb (kg) – 31 (14.0) lb (kg)
- Unique, gentle fabric care – patented honeycomb drum
- Maximum energy efficiency thanks to Air Recycling Flex
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi

EAN: 4002516410775 / Material number: 11722680 / Old Material Number: 52914012SOM

Construction type and design	
Design	Front loader
Linie	Performance Plus
Front	Stainless Steel
Load size with a load ratio of 1:25	23 (10.0)
Load size with a load ratio of 1:18	31 (14.0)
Drum volume in ft ³ (l)	8.83 (250.00)
Drying system	Exhaust air
Door opening [Ø] in in.(mm)	20 1/2 (520)
Door opening angle in degrees	180
Door hinging	left
Convertible hinging	•
Stainless steel honeycomb drum	Yes
Application	
Suitable for off-shore use	•
Suitable for Marine use	•
Performance data	
Maximum evaporation capacity in l/hour and gal. qts./hour	13 (13) gal (US)/min (l)
Specific energy consumption in kWh/kg an d kWh/p	0.51
Program cycle in min.	24
Service life in drying cycles	40000
Control	
Control system	M Touch Pro
Programmability	programmable
Program controls	Residual moisture controlled
Max. delay start in h	24
Countdown indicator	•
Program sequence indicator	•
Choice of display language	•
Standard electrical connection	
Type of heating	Electric
Electrical connection	3 AC 400V 50/60HZ
Electric heater rating in kW	13.50
Total connected load in kW	14.10
Fuse rating in A	25
Dimensions and weight of dryer	
External dimensions, net height in inches	55 1/8 (1400)
External dimensions, net width in inches	35 11/16 (906)
External dimensions, net depth in inches	33 9/16 (852)
External dimensions, gross height in inches	60 1/8 (1526)
External dimensions, gross width in inches	42 15/16 (1090)
External dimensions, gross depth in inches	36 15/16 (938)
Net weight in lbs. (kg)	354 (160.4)
Gross weight in lbs. (kg)	380 (172)
Maximum floor load in N/m ²	2024
Emission values	
Emissions – sound pressure at workplace	51 dB(A) re 20 µPa
Heat output to the room in Mj/h and BTUs /h	3.90

PDR 914 [EL SOM]

Vented dryer, electric heating

with programmable M Touch Pro controls, for marine applications.



EAN: 4002516410775 / Material number: 11722680 / Old Material Number: 52914012SOM

Features	
Intelligent drum reversal	•
Axial airflow	•
Large-surface fluff filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecycling Flex	•
Communication slot	•
Emergency shut off	•
Machine-independent accessories	•
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
Capacities	
Respirator masks [number]	8
Standard and target group programs	1
Over jackets [number]	2
Synthetic duvets [number]	1
Synthetic pillows [number]	2
Feather duvets [number]	1
Feather pillows [number]	2
Cloths, 22 g/0.8 oz [number]	255
Cotton mops, 40 cm [number]	53
Cotton mops, 50 cm [number]	45
Microfibre mops, 40 cm [number]	83
Summer horse blankets [number]	2
Standards, test certificates, and symbols	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•
UKCA	•
EAC	•
Complies with Machinery Directive 2006/42/EC	•