

PDR 922 [EL SOM]

Vented dryer, electric heating

with programmable M Touch Pro controls, for marine applications.



- Drum volume 14.13 (400.00) ft³ (l), load size 36 (16.0) lb (kg) – 49 (22.0) lb (kg)
- Unique, gentle fabric care – patented honeycomb drum
- Maximum energy efficiency thanks to Air Recycling Flex
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi

EAN: 4002516410805 / Material number: 11722710 / Old Material Number: 52922006SOM

Construction type and design	
Design	Front loader
Linie	Performance Plus
Front	Stainless Steel
Load size with a load ratio of 1:25	36 (16.0)
Load size with a load ratio of 1:18	49 (22.0)
Drum volume in ft ³ (l)	14.13 (400.00)
Drying system	Exhaust air
Door opening [Ø] in in.(mm)	20 1/2 (520)
Door opening angle in degrees	180
Door hinging	left
Convertible hinging	•
Stainless steel honeycomb drum	Yes
Application	
Suitable for off-shore use	•
Suitable for Marine use	•
Performance data	
Maximum evaporation capacity in l/hour and gal. qts./hour	22 (22) gal (US)/min (l)
Specific energy consumption in kWh/kg an d kWh/p	0.50
Program cycle in min.	23
Service life in drying cycles	40000
Control	
Control system	M Touch Pro
Programmability	programmable
Program controls	Residual moisture controlled
Max. delay start in h	24
Countdown indicator	•
Program sequence indicator	•
Choice of display language	•
Standard electrical connection	
Type of heating	Electric
Electrical connection	3 AC 480V 50/60HZ
Electric heater rating in kW	26.50
Total connected load in kW	27.50
Fuse rating in A	50
Possible voltage variant 1	
Electrical connection	3 AC 440V 50/60HZ
Heater rating in kW	22.50
Total connected load in kW	23.50
Fuse rating in A	50
Dimensions and weight of dryer	
External dimensions, net height in inches	55 1/8 (1400)
External dimensions, net width in inches	35 11/16 (906)
External dimensions, net depth in inches	45 3/4 (1162)
External dimensions, gross height in inches	60 1/8 (1526)
External dimensions, gross width in inches	42 15/16 (1090)
External dimensions, gross depth in inches	49 3/8 (1254)
Net weight in lbs. (kg)	439 (198.9)
Gross weight in lbs. (kg)	470 (213)

PDR 922 [EL SOM]

Vented dryer, electric heating

with programmable M Touch Pro controls, for marine applications.



EAN: 4002516410805 / Material number: 11722710 / Old Material Number: 52922006SOM

Maximum floor load in N/m ²	2521
Emission values	
Emissions – sound pressure at workplace	62 dB(A) re 20 µPa
Heat output to the room in Mj/h and BTUs /h	2.60
Features	
Intelligent drum reversal	•
Axial airflow	•
Large-surface fluff filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecycling Flex	•
Communication slot	•
Emergency shut off	•
Machine-independent accessories	•
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
Capacities	
Respirator masks [number]	16
Standard and target group programs	3
Over jackets [number]	5
Synthetic duvets [number]	2
Synthetic pillows [number]	3
Feather duvets [number]	2
Feather pillows [number]	4
Cloths, 22 g/0.8 oz [number]	364
Cotton mops, 40 cm [number]	84
Cotton mops, 50 cm [number]	73
Microfibre mops, 40 cm [number]	133
Microfibre mops, 50 cm [number]	94
Summer horse blankets [number]	3
Standards, test certificates, and symbols	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•
UKCA	•
EAC	•
Complies with Machinery Directive 2006/42/EC	•