



- Large touch display with proximity sensor – M Touch + MotionReact
- Individual coffee enjoyment with 3 bean containers CoffeeSelect
- Perfect care fully automatic with AutoDescale and AutoClean
- Perfectly positioned: thanks to the patented CupSensor
- 2 coffees at once at the touch of a button OneTouch for Two

EAN: 4002516419440 / Material number: 11733820 / Old Material Number: 29777540USA

Construction type and design	
Built-in bean-to-cup coffee machine	•
VitroLine	•
ArtLine	•
Color	Stainless Steel/Clean Touch Steel
Convenience features	
AromaticSystemFresh	•
CoffeeSelect	•
OneTouch preparation	•
One Touch and OneTouch for Two	•
DoubleShot	•
Programmable User profile	10
Flavor preserving conical grinding unit	•
Grinding grade selectable	•
Ground quantity programmable	•
Water quantity programmable	•
Water temperature programmable	•
Amount of milk can be programmed	•
Amount of milk froth can be programmed	•
Pre-brewing programmable	•
TeaTimer	•
User convenience	
Networking with Miele@home	•
Control panel	M Touch
MotionReact: light comes on when movement is detected	•
MotionReact: display comes on when movement is detected	•
CupSensor	•
Height adjustment of infinitely adjustable central spout min in .(cm)	1 5/8 (4.0)
Height adjustment of infinitely adjustable central spout max in in.(cm)	6 1/2 (16.5)
PerformanceMode	•
EasyClick milk container	•
DirectWater	•
ComfortDoor	•
Hidden door handle	•
BrilliantLight	•
Brew unit lighting	•
Expert mode	•
MultiLingua	•
MyMiele	•
Help function	•
No. of bean types	3
No. of bean containers	3
Bean container capacity, each in oz (g)	300
Capacity of bean container B in g	150
Capacity of bean container C in g	150
Bean container capacity, total in oz (g)	21.16 (600)
Removable bean container	





Capacity of water container in fl oz (I)	91.3 (2.7)
Milk container capacity in I	0.7
Capacity of waste container in servings	17
Drip tray capacity in fl oz (l)	54.1 (1.6)
Easily accessible containers	•
Time-of-day display	•
Time synchronization	•
Date display	•
Programmable switch-on time	•
Programmable switch-off time	•
Programmable stand-by time	•
Individual settings	•
Drink specialties	
Adjustable beverage portion size in ml	20-300
Ristretto, single	·
Ristretto, double	•
Espresso, single	•
Espresso, double	•
Coffee, single	•
Coffee, double	•
Long coffee, single	•
Long coffee, double	•
Cappuccino, single	•
Cappuccino, double	•
Latte macchiato, single	•
Latte macchiato, double	•
Hot milk, single	•
Latte macchiato, double	•
Milk froth, single	•
Milk froth, double	•
Espresso macchiato, single	•
Espresso macchiato, double	•
Cappuccino italiano, single	•
Cappuccino italiano, double	•
Flat white, single	•
Flat white, double	•
Café au lait, single	•
Café au lait, double	•
Caffè latte, single	•
Caffè latte, double	•
Caffè americano, single	•
Caffè Americano, double	•
Long black, single	•
Long black, double	•
Allwater	•
Warm water, double	•
Hot water, single	•
Hot water, double	•
Black tea, single	•
Black tea, double	•
Herbal tea, single	•
Herbal tea, double	•

EAN: 4002516419440 / Material number: 11733820 / Old Material Number: 29777540USA








CVA 7775

Built-in coffee machine with DirectWater

Perfectly combinable design with CoffeeSelect + AutoDescale for highest demands.








CVA7775, installation drawing, side view, 30 Inch, Flush insert

7/8" - 22* mm - Glass, 15/16" - 23.3** mm - Stainless steel



CVA7370, CVA7775, installation drawing, view from

~11 3/4" (~299 mm) CVA7370, CVA7775, installation drawing, view from above, 30 Inch, Flush inset


281/2" 724 mm)

150/15/



29 13/16 (757 mm


 $7/8^{\rm "}-22^{\rm *}$ mm – Glass, 15/16^{\rm "}-23.3^{\rm **} mm – Stainless steel



CVA7370, CVA7775, installation drawing, view from above, 30 Inch, Flush inset


CVA7370, CVA7775, installation drawing, view from above, 30 Inch, Flush inset






CVA7775, installation drawing,30 Inch, Flush insert

A – Cut-out (1 1/2" x 20" / 38 mm x 508 mm) in the bottom of the cabinet for power cord and ventilation, – Electrical and water supplies are recommended to be placed in adjacent cabinetry. Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection, W = Water connection




CVA7370, CVA7775, installation drawing, view from above, 30 Inch, Proud




CVA7370, side view, 30 Inch, Proud


7/8" - 22* mm - Glass, 15/16" - 23.3** mm - Stainless steel



CVA7775, side view, 30 Inch, Proud 7/8" – 22* mm – Glass, 15/16" – 23.3** mm – Stainless steel



CVA7370, CVA7775, installation drawing, view from above, 30 Inch, Proud




CVA7370, CVA7775, installation drawing, view from above, 30 Inch, Proud




CVA 7775

Built-in coffee machine with DirectWater


Perfectly combinable design with CoffeeSelect + AutoDescale for highest demands.





CVA7370, CVA7775, installation drawing, view from above, 30 Inch, Proud

CVA7370, CVA7775, installation drawing, built in, 30 Inch, Proud



CVA7775, installation drawing, installation, 30 Inch, Proud

A – Cut-out (1 1/2" x 20" / 38 mm x 508 mm) in the bottom of the cabinet for power cord and ventilation, – Electrical and water supplies are recommended to be placed in adjacent cabinetry, Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection, W = Water connection