

CVA 7775

Built-in coffee machine with DirectWater

Perfectly combinable design with CoffeeSelect + AutoDescale for highest demands.



- Large touch display with proximity sensor – M Touch + MotionReact
- Individual coffee enjoyment with 3 bean containers – CoffeeSelect
- Perfect care – fully automatic with AutoDescale and AutoClean
- Perfectly positioned: thanks to the patented CupSensor
- 2 coffees at once at the touch of a button – OneTouch for Two

EAN: 4002516419440 / Material number: 11733820 / Old Material Number: 29777540USA

Construction type and design	
Built-in bean-to-cup coffee machine	•
VitroLine	•
ArtLine	•
Color	Clean Touch Steel
Convenience features	
AromaticSystemFresh	•
CoffeeSelect	•
OneTouch preparation	•
One Touch and OneTouch for Two	•
DoubleShot	•
Programmable User profile	10
Flavor preserving conical grinding unit	•
Grinding grade selectable	•
Ground quantity programmable	•
Water quantity programmable	•
Water temperature programmable	•
Amount of milk can be programmed	•
Amount of milk froth can be programmed	•
Pre-brewing programmable	•
TeaTimer	•
User convenience	
Networking with Miele@home	•
Control panel	M Touch
MotionReact: light comes on when movement is detected	•
MotionReact: display comes on when movement is detected	•
CupSensor	•
Height adjustment of infinitely adjustable central spout min in in.(cm)	1 5/8 (4.0)
Height adjustment of infinitely adjustable central spout max in in.(cm)	6 1/2 (16.5)
PerformanceMode	•
EasyClick milk container	•
DirectWater	•
ComfortDoor	•
Hidden door handle	•
BrilliantLight	•
Brew unit lighting	•
Expert mode	•
MultiLingua	•
MyMiele	•
Help function	•
No. of bean types	3
No. of bean containers	3
Bean container capacity, each in oz (g)	150
Capacity of bean container B in g	300
Capacity of bean container C in g	150
Bean container capacity, total in oz (g)	21.16 (600)
Removable bean container	•
Capacity of water container in fl oz (l)	91.3 (2.7)

CVA 7775

Built-in coffee machine with DirectWater

Perfectly combinable design with CoffeeSelect + AutoDescal for highest demands.



EAN: 4002516419440 / Material number: 11733820 / Old Material Number: 29777540USA

Milk container capacity in l	0.7
Capacity of waste container in servings	17
Drip tray capacity in fl oz (l)	54.1 (1.6)
Easily accessible containers	•
Time-of-day display	•
Time synchronization	•
Date display	•
Programmable switch-on time	•
Programmable switch-off time	•
Programmable stand-by time	•
Individual settings	•
Drink specialties	
Adjustable beverage portion size in ml	20-300
Ristretto, single	•
Ristretto, double	•
Espresso, single	•
Espresso, double	•
Coffee, single	•
Coffee, double	•
Long coffee, single	•
Long coffee, double	•
Cappuccino, single	•
Cappuccino, double	•
Latte macchiato, single	•
Latte macchiato, double	•
Hot milk, single	•
Latte macchiato, double	•
Milk froth, single	•
Milk froth, double	•
Espresso macchiato, single	•
Espresso macchiato, double	•
Cappuccino italiano, single	•
Cappuccino italiano, double	•
Flat white, single	•
Flat white, double	•
Café au lait, single	•
Café au lait, double	•
Caffè latte, single	•
Caffè latte, double	•
Caffè americano, single	•
Caffè Americano, double	•
Long black, single	•
Long black, double	•
Allwater	•
Warm water, double	•
Hot water, single	•
Hot water, double	•
Black tea, single	•
Black tea, double	•
Herbal tea, single	•
Herbal tea, double	•

CVA 7775

Built-in coffee machine with DirectWater

Perfectly combinable design with CoffeeSelect + AutoDescal for highest demands.

EAN: 4002516419440 / Material number: 11733820 / Old Material Number: 29777540USA

Fruit tea, single	•
Fruit tea, double	•
Green tea, single	•
Green tea, double	•
White tea, single	•
White tea, double	•
Japanese tea, single	•
Japanese tea, double	•
Chai latte, single	•
Chai latte, double	•
Coffee pot	•
Teapot	•
Efficiency and sustainability	
Energy-saving Eco mode option	•
Power rating in standby mode in W	0.8
Power rating in networked standby in W	1.4
Time until automatic switch to off mode in min	20
Time until automatic switch to standby in min	20
Time until automatic switch to networked standby in min	20
Cleaning convenience	
Stainless steel front with Clean Touch Steel surface	•
AutoDescal	•
Manual descaling	•
AutoClean	•
Automatic rinsing of the milk pipework from the water container	•
Convenient cleaning programs	•
Auto-Off function	•
ComfortClean	•
Removable milk pipework	•
Removable brew unit	•
Adjustable water hardness	•
Appliance networking	
MobileControl	•
RemoteService	•
WiFiConn@ct	•
Safety	
System lock	•
Technical data	
Niche width min in in.(mm)	28 5/8 (724)
Niche width max in in.(mm)	28 3/4 (728)
Niche height min in in.(mm)	18 1/8 (460)
Niche height max in in.(mm)	18 5/8 (472)
Niche depth in in.(mm)	24 1/8 (610)
Appliance width in in.(mm)	29 7/8 (757)
Appliance height in in.(mm)	18 7/8 (479)
Appliance depth in in.(mm)	18 7/8 (478)
Depth with door open in in.(cm)	48 3/4 (123.8)
Total connected load in kW	1.45
Voltage in V	120
Fuse rating in A	15

CVA 7775

Built-in coffee machine with DirectWater

Perfectly combinable design with CoffeeSelect + AutoDescal for highest demands.



EAN: 4002516419440 / Material number: 11733820 / Old Material Number: 29777540USA

Number of phases	1
Length of electrical wire in ft (m)	6 (2.0)
Standard accessories	
Glass milk container	•
Descaling cartridge	•
AutoCleaner	•
Available display languages	


Available display languages via MultiLingua

bahasa malaysia, dansk, deutsch, english, english (AU), english (CA), english (GB), english (US), español, français, français (CA), français (FR), hrvatski, italiano, magyar, nederlands, norsk, polski, portugês, русский, română, slovenčina, slovenščina, srpski, suomi, svenska, türkçe, українська, čeština, ελληνικά,

CVA 7775


Built-in coffee machine with DirectWater

Perfectly combinable design with CoffeeSelect + AutoDescal for highest demands.




CVA7775, CVA7875, installation drawing, side view, 30 Inch, Flush insert *(Footnote)


7/8" – 22* mm – Glass, 15/16" – 23.3** mm – Stainless steel




CVA7370, CVA7775, CVA7875, installation drawing, view from above, 30 Inch, Flush inset




CVA7370, CVA7775, CVA7875, installation drawing, view from above, 30 Inch, Flush inset



CVA7370, CVA7775, CVA7875, installation drawing, view from above, 30 Inch, Flush inset



CVA7370, CVA7775, CVA7875, installation drawing, view from above, 30 Inch, Flush inset




CVA7370, CVA7775, CVA7875, installation drawing, built in, 30 Inch, Flush inset

7/8" – 22* mm – Glass, 15/16" – 23.3** mm – Stainless steel

CVA 7775


Built-in coffee machine with DirectWater

Perfectly combinable design with CoffeeSelect + AutoDescale for highest demands.




CVA7775, CVA7875, installation drawing, 30 Inch, Flush insert

A – Cut-out (1 1/2" x 20" / 38 mm x 508 mm) in the bottom of the cabinet for power cord and ventilation. – Electrical and water supplies are recommended to be placed in adjacent cabinetry. Additional cabinet depth is required when placing the electrical and water supplies behind the appliance. E = Electric connection, W = Water connection




CVA7370, side view, 30 Inch, Proud

7/8" – 22* mm – Glass, 15/16" – 23.3** mm – Stainless steel




CVA7775, CVA7875, side view, 30 Inch, Proud


7/8" – 22* mm – Glass, 15/16" – 23.3** mm – Stainless steel



CVA7370, CVA7775, CVA7875, installation drawing, view from above, 30 Inch, Proud



CVA7370, CVA7775, CVA7875, installation drawing, view from above, 30 Inch, Flush




CVA7370, CVA7775, CVA7875, installation drawing, view from above, 30 Inch, Proud


CVA 7775

Built-in coffee machine with DirectWater


Perfectly combinable design with CoffeeSelect + AutoDescale for highest demands.



CVA7370, CVA7775, CVA7875, installation drawing, view from above, 30 Inch, Proud



CVA7370, CVA7775, CVA7875, installation drawing, built in, 30 Inch, Proud



CVA7775, CVA7875, installation drawing, installation, 30 Inch, Proud

A – Cut-out (1 1/2" x 20" / 38 mm x 508 mm) in the bottom of the cabinet for power cord and ventilation. – Electrical and water supplies are recommended to be placed in adjacent cabinetry. Additional cabinet depth is required when placing the electrical and water supplies behind the appliance. E = Electric connection, W = Water connection