

## CVA 7370

### Built-in coffee machine

In a perfectly combinable design with patented CupSensor for perfect coffee.



- Large clear text display with sensor controls – DirectSensor
- Perfectly positioned: thanks to the patented CupSensor
- 2 coffees at once at the touch of a button – OneTouch for Two
- Always freshly ground – AromaticSystemFresh
- Convenient when hosting lots of guests – coffee/tea pot function

EAN: 4002516419457 / Material number: 11733830 / Old Material Number: 29737040USA

Construction type and design	
Built-in bean-to-cup coffee machine	•
VitroLine	•
ArtLine	•
Color	Stainless Steel/Clean Touch Steel
Convenience features	
AromaticSystemFresh	•
OneTouch preparation	•
One Touch and OneTouch for Two	•
DoubleShot	•
Programmable User profile	10
Flavor preserving conical grinding unit	•
Grinding grade selectable	•
Ground quantity programmable	•
Water quantity programmable	•
Water temperature programmable	•
Amount of milk can be programmed	•
Amount of milk froth can be programmed	•
Pre-brewing programmable	•
TeaTimer	•
User convenience	
Networking with Miele@home	•
Control panel	DirectSensor
CupSensor	•
Height adjustment of infinitely adjustable central spout min in in.(cm)	1 5/8 (4.0)
Height adjustment of infinitely adjustable central spout max in in.(cm)	6 1/2 (16.5)
PerformanceMode	•
EasyClick milk container	•
ComfortDoor	•
Hidden door handle	•
BrilliantLight	•
Expert mode	•
MultiLingua	•
No. of bean types	1
No. of bean containers	2
Bean container capacity, each in oz (g)	300
Capacity of bean container B in g	300
Bean container capacity, total in oz (g)	21.16 (600)
Removable bean container	•
Capacity of water container in fl oz (l)	91.3 (2.7)
Milk container capacity in l	0.7
Capacity of waste container in servings	17
Drip tray capacity in fl oz (l)	54.1 (1.6)
Easily accessible containers	•
Time-of-day display	•
Time synchronization	•
Date display	•
Programmable switch-on time	•

CVA 7370

Built-in coffee machine

In a perfectly combinable design with patented CupSensor for perfect coffee.



EAN: 4002516419457 / Material number: 11733830 / Old Material Number: 29737040USA

Programmable switch-off time	•
Programmable stand-by time	•
Individual settings	•
<b>Drink specialties</b>	
Adjustable beverage portion size in ml	20-300
Ristretto, single	•
Ristretto, double	•
Espresso, single	•
Espresso, double	•
Coffee, single	•
Coffee, double	•
Long coffee, single	•
Long coffee, double	•
Cappuccino, single	•
Cappuccino, double	•
Latte macchiato, single	•
Latte macchiato, double	•
Hot milk, single	•
Latte macchiato, double	•
Milk froth, single	•
Milk froth, double	•
Espresso macchiato, single	•
Espresso macchiato, double	•
Cappuccino italiano, single	•
Cappuccino italiano, double	•
Flat white, single	•
Flat white, double	•
Café au lait, single	•
Café au lait, double	•
Caffè latte, single	•
Caffè latte, double	•
Caffè americano, single	•
Caffè Americano, double	•
Long black, single	•
Long black, double	•
Allwater	•
Warm water, double	•
Hot water, single	•
Hot water, double	•
Black tea, single	•
Black tea, double	•
Herbal tea, single	•
Herbal tea, double	•
Fruit tea, single	•
Fruit tea, double	•
Green tea, single	•
Green tea, double	•
White tea, single	•
White tea, double	•
Japanese tea, single	•
Japanese tea, double	•
Chai latte, single	•

**Miele**

CVA 7370


Built-in coffee machine

In a perfectly combinable design with patented CupSensor for perfect coffee.

## CVA 7370


### Built-in coffee machine

In a perfectly combinable design with patented CupSensor for perfect coffee.




CVA7370, installation drawing, side view, 30 Inch, Flush insert


7/8" – 22\* mm – Glass, 15/16" – 23.3\*\* mm – Stainless steel




CVA7370, CVA7775, installation drawing, view from above, 30 Inch, Flush inset




CVA7370, CVA7775, installation drawing, view from above, 30 Inch, Flush inset



CVA7370, CVA7775, installation drawing, view from above, 30 Inch, Flush inset



CVA7370, CVA7775, installation drawing, view from above, 30 Inch, Flush inset




CVA7370, CVA7775, installation drawing, built in, 30 Inch, Flush inset

7/8" – 22\* mm – Glass, 15/16" – 23.3\*\* mm – Stainless steel

## CVA 7370


Built-in coffee machine

In a perfectly combinable design with patented CupSensor for perfect coffee.




CVA7370, installation drawing, 30 Inch, Flush insert

A – Cut-out (1 1/2" x 20" / 38 mm x 508 mm) in the bottom of the cabinet for power cord and ventilation. – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection




CVA7370, side view, 30 Inch, Proud

7/8" – 22\* mm – Glass, 15/16" – 23.3\*\* mm – Stainless steel




CVA7775, side view, 30 Inch, Proud


7/8" – 22\* mm – Glass, 15/16" – 23.3\*\* mm – Stainless steel



CVA7370, CVA7775, installation drawing, view from above, 30 Inch, Proud



CVA7370, CVA7775, installation drawing, view from above, 30 Inch, Proud




CVA7370, CVA7775, installation drawing, view from above, 30 Inch, Proud


## CVA 7370

### Built-in coffee machine


In a perfectly combinable design with patented CupSensor for perfect coffee.



CVA7370, CVA7775, installation drawing, view from above, 30 Inch, Proud



CVA7370, CVA7775, installation drawing, built in, 30 Inch, Proud



CVA7370, installation drawing, installation, 30 Inch, Proud

A – Cut-out (1 1/2" x 20" / 38 mm x 508 mm) in the bottom of the cabinet for power cord and ventilation, – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection