

PRI 210 [EL STW AB]

Rotary iron, electric

With the latest controls and flexible working height.



- Performance 22.5 kg/h*, roller diameter 8 5/16 (210) in (mm), working width 39 3/8 (1000) in (mm)
- Ideal ergonomics – height-adjustable and optional base
- State-of-the-art controls – Touch display
- Selection of the most important settings – favorite programs
- Perfect rotary ironing performance – flexibly positioned heater plate

* With 15% residual moisture – performance data according to DIN 11 902: The achievable laundry throughput depends on overall conditions such as, for example, the type of laundry and the experience of the operator.

EAN: 4002516422433 / Material number: 11741330 / Old Material Number: 53210011NAM

Construction type and design	
Design	Infeed and outfeed of laundry at the front
Can be set up against a wall	•
Linie	Professional
Outer casing	Iron Grey
Drum diameter in in.(mm)	8 5/16 (210)
Working width in in.(mm)	39 3/8 (1000)
Heater plate material	Aluminium
Padding	Supple steel wool
Ironer cover	ARAMID needle-felt cloth
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for hospitals	•
Suitable for off-shore use	•
Suitable for Marine use	•
Performance data	
Max. ironing performance at 15 % residual moisture in kg/h	22.5
Tested operating hours	20000
Control	
Control system	Touch display
Touch display (optional)	Touch-Display PRI
Program setting	Setting of defined program parameters
Minimum ironer speed, can be set in ft/min	1.5
Maximum ironer speed, can be set in ft/min	4.0
Adjustable temperature	Infinitely variable
Standard electrical connection	
Type of heating	Electric
Electrical connection	AC 240V 50-60HZ
Electric heater rating in kW	3.30
Total connected load in kW	3.70
Fuse rating in A	20
Possible voltage variant 1	
Electrical connection	AC 220V 50-60 HZ
Electric heater rating in kW	2.70
Total connected load in kW	3.20
Fuse rating in A	20
Possible voltage variant 2	
Electrical connection	AC 208V 50-60 HZ
Electric heater rating in kW	2.50
Total connected load in kW	2.90
Fuse rating in A	20
Dimensions and weight	
External dimensions, height in mm	40 11/16 (1032)
External dimensions, width in mm	62 3/16 (1579)
External dimensions, depth in mm	18 3/4 (476)
External dimensions, gross height in inches	54 1/8 (1374)
External dimensions, gross width in inches	69 7/16 (1763)

PRI 210 [EL STW AB]

Rotary iron, electric

With the latest controls and flexible working height.



EAN: 4002516422433 / Material number: 11741330 / Old Material Number: 53210011NAM

External dimensions, gross depth in inches	26 (660)
Net weight in kg	269 (122)
Gross weight in lbs.	300 (136)
Maximum floor loading in p/force	1235
Emission values	
Emissions – sound pressure at workplace	<70 dB(A) re 20 µPa
Heat output to the room in Mj/h and BTUs /h	3.30
Features	
Finger guard	•
FlexControl footswitch	•
Airing bar	•
Feed-in board	•
Laundry pick-off bands	•
Laundry crates (optional)	•
Laundry return feed	•
Favorites program	•
Incorrect feed recognition	•
Air suspension	•
Pause function	•
High contact pressure	•
Heater plate cleaning and waxing indicator	•
Plinth (optional)	•
Option of ironing when seated	•
APRI 319 care set for the heater plate included in the scope of delivery	•
Appliance-independent accessories	•
Connection options	
Payment system (optional)	•
Peak load cut-out/energy management	•
Standards, test certificates, and symbols	
CE	•
WEEE	•
RCM	•
Complies with Machinery Directive 2006/42/EC	•