


PRI 214 [EL SOM STW]

Rotary iron, electric

with the latest controls and flexible working height for marine applications.



- Performance 33.0 kg/h*, roller diameter 8 5/16 (210) in (mm), working width 55 1/8 (1400) in (mm)
- Ideal ergonomics – height-adjustable and optional base
- State-of-the-art controls – Touch display
- Selection of the most important settings – favorite programs
- Perfect rotary ironing performance – flexibly positioned heater plate

* With 25% residual moisture – performance data according to DIN 11 902: The achievable laundry throughput depends on overall conditions such as, for example, the type of laundry and the experience of the operator.


EAN: 4002516422891 / Material number: 11744570 / Old Material Number: 53214006SOM

Construction type and design	
Design	Infeed and outfeed of laundry at the front
Can be set up against a wall	•
Linie	Professional
Outer casing	Iron Grey
Drum diameter in in.(mm)	8 5/16 (210)
Working width in in.(mm)	55 1/8 (1400)
Heater plate material	Aluminium
Padding	Supple steel wool
Ironer cover	ARAMID needle-felt cloth
Application	
Suitable for off-shore use	•
Suitable for Marine use	•
Performance data	
Max. ironing performance at 25 % residual moisture in kg/h	33.0
Tested operating hours	20000
Control	
Control system	Touch display
Touch display (optional)	Touch-Display PRI
Program setting	Setting of defined program parameters
Minimum ironer speed, can be set in ft/min	1.5
Maximum ironer speed, can be set in ft/min	4.0
Adjustable temperature	Infinitely variable
Standard electrical connection	
Type of heating	Electric
Electrical connection	3 AC 230V 50-60HZ
Electric heater rating in kW	6.50
Total connected load in kW	7.00
Fuse rating in A	25
Dimensions and weight	
External dimensions, height in mm	40 11/16 (1032)
External dimensions, width in mm	77 15/16 (1979)
External dimensions, depth in mm	25 5/8 (650)
External dimensions, gross height in inches	54 1/8 (1374)
External dimensions, gross width in inches	85 3/16 (2163)
External dimensions, gross depth in inches	26 (660)
Net weight in kg	309 (140)
Gross weight in lbs.	342 (155)
Maximum floor load in N/m ²	1400
Emission values	
Emissions – sound pressure at workplace	<70 dB(A) re 20 µPa
Heat output to the room in MJ/h and BTUs /h	11.00
Features	
Finger guard	•
FlexControl footswitch	•
Feed-in board	•
Laundry pick-off bands	•
Laundry crates	•

PRI 214 [EL SOM STW]

Rotary iron, electric

with the latest controls and flexible working height for marine applications.



EAN: 4002516422891 / Material number: 11744570 / Old Material Number: 53214006SOM

Laundry return feed	•
Favorites program	•
Incorrect feed recognition	•
Air suspension	•
Pause function	•
High contact pressure	•
Heater plate cleaning and waxing indicator	•
Plinth (optional)	•
Option of ironing when seated	•
APRI 319 care set for the heater plate included in the scope of delivery	•
Appliance-independent accessories	•
Connection options	
Payment system (optional)	•
Peak load cut-out/energy management	•
Standards, test certificates, and symbols	
VDE	•
CE	•
EAC	•
WEEE	•
VDE-EMC	•
RCM	•
Splash-proof IPX0	•
UKCA	•
Complies with Machinery Directive 2006/42/EC	•