

## PRI 217 [EL SOM STW]

Rotary iron, electric

with the latest controls and steel wool padding for marine applications.



- Performance 60.0 kg/h\*, roller diameter 9 7/8 (250) in (mm), working width 65 3/8 (1660) in (mm)
- Ideal ergonomics – height-adjustable and optional base
- State-of-the-art controls – Touch display
- Selection of the most important settings – favorite programs
- Perfect rotary ironing performance – flexibly positioned heater plate

\* With 25% residual moisture – performance data according to DIN 11 902: The achievable laundry throughput depends on overall conditions such as, for example, the type of laundry and the experience of the operator.


EAN: 4002516423065 / Material number: 11744780 / Old Material Number: 53217013SOM

<b>Construction type and design</b>	
Design	Infeed and outfeed of laundry at the front
Can be set up against a wall	•
Linie	Professional
Outer casing	Iron Grey
Drum diameter in in.(mm)	9 7/8 (250)
Working width in in.(mm)	65 3/8 (1660)
Heater plate material	Aluminium
Padding	Supple steel wool, Leaf-spring padding (option)
Ironer cover	ARAMID needle-felt cloth
<b>Application</b>	
Suitable for off-shore use	•
Suitable for Marine use	•
<b>Performance data</b>	
Max. ironing performance at 25 % residual moisture in kg/h	60.0
Tested operating hours	20000
<b>Control</b>	
Control system	Touch display
Touch display (optional)	Touch-Display PRI
Program setting	Setting of defined program parameters
Minimum ironer speed, can be set in ft/min	1.5
Maximum ironer speed, can be set in ft/min	4.5
Adjustable temperature	Infinitely variable
<b>Standard electrical connection</b>	
Type of heating	Electric
Electrical connection	3N AC 400V 50-60HZ
Electric heater rating in kW	11.00
Total connected load in kW	11.60
Fuse rating in A	25
<b>Dimensions and weight</b>	
External dimensions, height in mm	43 3/4 (1110)
External dimensions, width in mm	88 1/8 (2238)
External dimensions, depth in mm	25 5/8 (650)
External dimensions, gross height in inches	55 11/16 (1414)
External dimensions, gross width in inches	94 1/2 (2400)
External dimensions, gross depth in inches	33 7/8 (860)
Net weight in kg	417 (189)
Gross weight in lbs.	472 (214)
Maximum floor load in N/m <sup>2</sup>	1890
<b>Emission values</b>	
Emissions – sound pressure at workplace	<70 dB(A) re 20 µPa
Heat output to the room in Mj/h and BTUs /h	11.00
<b>Features</b>	
Finger guard	•
FlexControl footswitch	•
Feed-in board	•
Laundry pick-off bands	•
Laundry crates	•

PRI 217 [EL SOM STW]

Rotary iron, electric

with the latest controls and steel wool padding for marine applications.



EAN: 4002516423065 / Material number: 11744780 / Old Material Number: 53217013SOM

Favorites program	•
Incorrect feed recognition	•
Air suspension	•
Pause function	•
High contact pressure	•
Heater plate cleaning and waxing indicator	•
Plinth (optional)	•
Option of ironing when seated	•
APRI 319 care set for the heater plate included in the scope of delivery	•
Appliance-independent accessories	•
<b>Connection options</b>	
Payment system (optional)	•
Peak load cut-out/energy management	•
<b>Standards, test certificates, and symbols</b>	
VDE	•
CE	•
EAC	•
WEEE	•
VDE-EMC	•
RCM	•
Splash-proof IPX0	•
UKCA	•
Complies with Machinery Directive 2006/42/EC	•