

## PFD 104 SCVi XXL [MAR]

Fully integrated Full-sized dishwasher with 3D MultiFlex Tray with baskets approved by Lloyd's Register.



- Wash performance: 14 place settings in just 36 min\*
- 13% less energy consumption
- Door opens automatically after two knocks – Knock2open
- Door closes on its own – AutoClose
- Innovative design and maximum convenience – 3D MultiFlex Tray

\* Depending on site conditions (temperature of incoming water / power connection) values given may vary.

EAN: 4002516424178 / Material number: 11750880 / Old Material Number: 61010405MAR

<b>Construction type and design</b>	
Model	Fully integrated dishwasher
XXL dishwashers	•
Range	ProfiLine
Wash system	Fresh water front loader
Number of levels	2
Front	Without front
Side walls	Galvanised
Control panel color	Obsidian Black
<b>Application</b>	
Suitable for offshore and marine services	•
<b>Performance data</b>	
Tested virucidal efficacy	•
Certified hygiene	•
Shortest program duration in min.	36
Maximum final rinse temperature in °F (°C)	167 (75)
Cleaning performance, place settings/cycle	14
Service life in wash cycles	12500
<b>Control</b>	
Control system	Electronic controls
Program selection	Program selectors
Max. delay start in h	24
Countdown indicator	•
Dishwashing programs [number]	8
Program sequence indicator	•
Choice of display language	•
Check filter indicator	•
<b>Standard electrical connection</b>	
Electrical connection	3N AC 400V 50HZ
Heater rating in kW	7.10
Total connected load in kW	7.30
Fuse rating in A	16
Length of power cord in ft (m)	5 (1.70)
<b>Possible voltage variant 1</b>	
Electrical connection	AC 230V 50HZ
Heater rating in kW	1.90
Total connected load in kW	2.10
Fuse rating in A	10-16
<b>Water connection/drainage</b>	
Cold or hot water [number]	1
Required flow pressure in bar	1.00-10.00
Drain hose [DN]	22
Maximum delivery head for drain pump in inches (cm)	39 3/8 (100)
Integrated water softener	•
Maximum water hardness in gpg (mmol/l)	38.02 (6.50)
Water protection system	Waterproof system
Length of water drain hose in inches (cm)	59 1/8 (150)
<b>Dimensions and weight</b>	
External dimensions, net height in inches	33 5/16 (845)
External dimensions, net width in inches	23 9/16 (598)

## PFD 104 SCVi XXL [MAR]

Fully integrated Full-sized dishwasher with 3D MultiFlex Tray with baskets approved by Lloyd's Register.



EAN: 4002516424178 / Material number: 11750880 / Old Material Number: 61010405MAR

External dimensions, net depth in inches	21 11/16 (550)
External dimensions, gross height in inches	38 1/4 (970)
External dimensions, gross width in inches	26 7/16 (670)
External dimensions, gross depth in inches	27 3/16 (690)
Usable space in wash cabinet, width in inches (mm)	22 7/8 (580)
Usable space in wash cabinet, height in inches (mm)	20 1/8 (510)
Usable space in wash cabinet, depth of upper basket in inches (mm)	17 3/4 (450)
Usable space in wash cabinet, depth of lower basket in inches (mm)	17 3/4 (450)
In-feed height above floor in inches (mm)	8 5/16 (210)
Required niche width in mm	23 5/8 (600)
Net weight [kg]	106 (48)
Gross weight in lbs.	126 (57)
Maximum floor load in N/m <sup>2</sup>	1000
<b>Emission values</b>	
Emission sound pressure level in workplace (LpA)	33 dB(A) re 20 µPa
Sound power (LwA) in dB(A) re 1 pW	45.0
<b>Programs</b>	
Universal	•
Short	•
SaniWash	•
Cold/Pre-wash	•
Glasses	•
Plastic	•
EnergySave/Economy	•
Intensive	•
<b>Baskets</b>	
MaxiComfort P baskets	•
Flexible FlexLine basket design	•
FlexCare glass holder [number]	4
FlexCare cup rack [number]	2
Height-adjustable upper basket	•
Patented 3D MultiFlex tray	•
<b>Features</b>	
Drying	Active condensation drying, Additional drying
1 Combi dispenser/door for powder and liquid media	•
Wash cabinet made from high-quality stainless steel	•
LED Lighting	•
AutoClose	•
EcoFeedback	•
Brilliant GlassCare	•
Adjustable final rinse temperature	•
Optical interface	•
SmartStart	•
FlexiTimer with EcoStart	•
Wi-Fi	•
<b>Standards, test certificates, and symbols</b>	
CE	•
Complies with Machinery Directive 2006/42/EC	•

## PFD 104 SCVi XXL [MAR]

Fully integrated Full-sized dishwasher with 3D MultiFlex Tray  
with baskets approved by Lloyd's Register.



EAN: 4002516424178 / Material number: 11750880 / Old Material Number: 61010405MAR

VDE	•
EMC radio suppressed	•
DIN EN 17735	•
EN 1717	•
Lloyd's Register	•