

## PT 8303 SL [PTB Plus EL IGS]

Vented dryer, iron gray sides, electric

with SlimLine design, with residual moisture controls for perfect drying results.

EAN: 4002516431169 / Material number: 11772780 /  
Old Material Number: 52830306USA

Construction type and design	
Design	SlimLine
Linie	Professional
Front	Iron Grey
Load in lbs.(kg)	34 (15.0)
Load size with a load ratio of 1:25	27 (12.0)
Load size with a load ratio of 1:20	34 (15.0) lb (kg)
Drum volume in ft <sup>3</sup> (l)	10.59 (300.00)
Drying system	Exhaust air
Door opening [Ø] in in.(mm)	20 1/2 (520)
Door opening angle in degrees	180
Door hinging	left
Stainless steel drum	•
Stainless steel honeycomb drum	No
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for commercial laundries	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas and fitness centers	•
Performance data	
Maximum evaporation capacity in l/hour and gal. qts./hour	12 (12) gal (US)/min (l)
Specific energy consumption in kWh/kg and kWh/p	0.59
Program cycle in min.	33
Control	
Control system	Profitronic B Plus
Programmability	Setting of defined parameters
Program controls	Residual moisture controlled
Countdown indicator	•
Program sequence indicator	•
Fascia panel with clear text	•
Choice of display language	•
Standard/target group programs	
Basic programmes	•
Standard electrical connection	
Type of heating	Electric
Electrical connection	3 AC 220-240V 60HZ
Electric heater rating in kW	14.70
Total connected load in kW	13.10-15.40
Fuse rating in A	40
Possible voltage variant 1	
Electrical connection	3 AC 208V 60HZ
Heater rating in kW	11.00

- Drum volume 10.59 (300.00) ft<sup>3</sup> (l), load size 34 (15.0) lb (kg)
- Easiest installation – only 28 inches wide
- Simple transport – direct access underneath
- Shortest cycles thanks to diagonal air flow
- Precision drying of all fabrics – PerfectDry

## PT 8303 SL [PTB Plus EL IGS]

Vented dryer, iron gray sides, electric

with SlimLine design, with residual moisture controls for perfect drying results.

EAN: 4002516431169 / Material number: 11772780 /

Old Material Number: 52830306USA

Total connected load in kW	11.70
Fuse rating in A	35
<b>Possible voltage variant 2</b>	
Electrical connection	2 AC 208V 60HZ
Heater rating in kW	7.40
Total connected load in kW	8.10
Fuse rating in A	40
<b>Dimensions and weight of dryer</b>	
External dimensions, net height in inches	70 7/8 (1800)
External dimensions, net width in inches	28 (711)
External dimensions, net depth in inches	42 7/8 (1089)
External dimensions, gross height in inches	71 5/16 (1810)
External dimensions, gross width in inches	31 1/2 (800)
External dimensions, gross depth in inches	46 1/2 (1180)
Net weight in lbs. (kg)	307 (139.0)
Gross weight in lbs. (kg)	351 (159)
Maximum floor load in N	1584
<b>Emission values</b>	
Emissions – sound pressure at workplace	<70 dB(A) re 20 µPa
Heat output to the room in MJ/h and BTUs /h	1.70
<b>Features</b>	
Intelligent drum reversal	•
Large-surface fluff filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Retractable plinth	•
Machine-independent accessories	•
<b>Connection options</b>	
Payment system (optional)	•
Serial interface RS 232 (optional)	•
Optical interface for service access	•
Peak-load negotiation / energy management (optional)	•
<b>Standards, test certificates, and symbols</b>	
Complies with Machinery Directive 2006/42/EC	•