

HR 1935-3 G DF GR 36 inch range

- the Dual Fuel all-rounder with M Touch for the highest demands.



- Network-enabled WiFi appliance Miele@home
- Maximum variety four powerful burners and a grill
- Perfect baking and roasting results – Moisture plus
- Ergonomic and easy operation motorized lift-up control panel
- Precise cooking temperature Wireless Precision Probe

EAN: 4002516486794 / Material number: 11791600 / Old Material Number: 25193581USA

To a of hearten	
Type of heating	
Dual fuel	Niel vel ve
Gas type	Natural gas
Construction type	
Range	•
Appliance width in inches	36
Operating modes	
Speed oven automatic programs	
Maxi Broil	
Defrost	
Convection Bake	-
Convection Roast	·
Auto roast	·
Broil	<u>•</u>
Intensive Bake	
Moisture Plus	
Slow roast	•
Surround	•
Browning	•
Bake	•
Convection Roast	•
Special modes	•
Design	
Appliance color	Clean Touch Steel
Oven display	M Touch
Convenience features	
Convenience features Wireless Precision Probe	•
	•
Wireless Precision Probe	•
Wireless Precision Probe Keep-warm function	•
Wireless Precision Probe Keep-warm function Crisp function	•
Wireless Precision Probe Keep-warm function Crisp function Cooktop features	•
Wireless Precision Probe Keep-warm function Crisp function Cooktop features Number of gas burners	4
Wireless Precision Probe Keep-warm function Crisp function Cooktop features Number of gas burners Number of TrueSimmer burners x power in BTU	4 1 x 12 500 BTU/hod.
Wireless Precision Probe Keep-warm function Crisp function Cooktop features Number of gas burners Number of TrueSimmer burners x power in BTU Number of power burners x power in BTU	4 1 x 12 500 BTU/hod. 1 x 13.60
Wireless Precision Probe Keep-warm function Crisp function Cooktop features Number of gas burners Number of TrueSimmer burners x power in BTU Number of power burners x power in BTU Number of high burners x power in BTU	4 1 x 12 500 BTU/hod. 1 x 13.60
Wireless Precision Probe Keep-warm function Crisp function Cooktop features Number of gas burners Number of TrueSimmer burners x power in BTU Number of power burners x power in BTU Number of high burners x power in BTU True Simmer function	4 1 x 12 500 BTU/hod. 1 x 13.60
Wireless Precision Probe Keep-warm function Crisp function Cooktop features Number of gas burners Number of TrueSimmer burners x power in BTU Number of power burners x power in BTU Number of high burners x power in BTU True Simmer function GasStop	4 1 x 12 500 BTU/hod. 1 x 13.60 2 x 19.50
Wireless Precision Probe Keep-warm function Crisp function Cooktop features Number of gas burners Number of TrueSimmer burners x power in BTU Number of power burners x power in BTU Number of high burners x power in BTU True Simmer function GasStop Number and power rating of grill surface in BTU/h Width of broil surface in in.(mm)	4 1 x 12 500 BTU/hod. 1 x 13.60 2 x 19.50 1 x 19,000 11 1/4 (284) in (mm)
Wireless Precision Probe Keep-warm function Crisp function Cooktop features Number of gas burners Number of TrueSimmer burners x power in BTU Number of power burners x power in BTU Number of high burners x power in BTU True Simmer function GasStop Number and power rating of grill surface in BTU/h	4 1 x 12 500 BTU/hod. 1 x 13.60 2 x 19.50 • 1 x 19,000
Wireless Precision Probe Keep-warm function Crisp function Cooktop features Number of gas burners Number of TrueSimmer burners x power in BTU Number of power burners x power in BTU Number of high burners x power in BTU True Simmer function GasStop Number and power rating of grill surface in BTU/h Width of broil surface in in.(mm) Depth of broil surface in in.(mm)	4 1 x 12 500 BTU/hod. 1 x 13.60 2 x 19.50 1 x 19,000 11 1/4 (284) in (mm)
Wireless Precision Probe Keep-warm function Crisp function Cooktop features Number of gas burners Number of TrueSimmer burners x power in BTU Number of power burners x power in BTU Number of high burners x power in BTU True Simmer function GasStop Number and power rating of grill surface in BTU/h Width of broil surface in in.(mm) Depth of broil surface in in.(mm) User convenience	4 1 x 12 500 BTU/hod. 1 x 13.60 2 x 19.50 1 x 19,000 11 1/4 (284) in (mm) 22 1/8 (560) in (mm)
Wireless Precision Probe Keep-warm function Crisp function Cooktop features Number of gas burners Number of TrueSimmer burners x power in BTU Number of power burners x power in BTU Number of high burners x power in BTU True Simmer function GasStop Number and power rating of grill surface in BTU/h Width of broil surface in in.(mm) Depth of broil surface in in.(mm) User convenience Networking with Miele@home	1 x 12 500 BTU/hod. 1 x 13.60 2 x 19.50 1 x 19,000 11 1/4 (284) in (mm) 22 1/8 (560) in (mm)
Wireless Precision Probe Keep-warm function Crisp function Cooktop features Number of gas burners Number of TrueSimmer burners x power in BTU Number of power burners x power in BTU Number of high burners x power in BTU True Simmer function GasStop Number and power rating of grill surface in BTU/h Width of broil surface in in.(mm) Depth of broil surface in in.(mm) User convenience Networking with Miele@home Precision knobs	1 x 12 500 BTU/hod. 1 x 13.60 2 x 19.50 1 x 19,000 11 1/4 (284) in (mm) 22 1/8 (560) in (mm)
Wireless Precision Probe Keep-warm function Crisp function Cooktop features Number of gas burners Number of TrueSimmer burners x power in BTU Number of power burners x power in BTU Number of high burners x power in BTU True Simmer function GasStop Number and power rating of grill surface in BTU/h Width of broil surface in in.(mm) Depth of broil surface in in.(mm) User convenience Networking with Miele@home Precision knobs Illuminated knob	1 x 12 500 BTU/hod. 1 x 13.60 2 x 19.50 1 x 19,000 11 1/4 (284) in (mm) 22 1/8 (560) in (mm)
Wireless Precision Probe Keep-warm function Crisp function Cooktop features Number of gas burners Number of TrueSimmer burners x power in BTU Number of power burners x power in BTU Number of high burners x power in BTU True Simmer function GasStop Number and power rating of grill surface in BTU/h Width of broil surface in in.(mm) Depth of broil surface in in.(mm) User convenience Networking with Miele@home Precision knobs Illuminated knob ComfortSwivel handle Motorized lift-up control panel	4 1 x 12 500 BTU/hod. 1 x 13.60 2 x 19.50 1 x 19,000 11 1/4 (284) in (mm) 22 1/8 (560) in (mm)
Wireless Precision Probe Keep-warm function Crisp function Cooktop features Number of gas burners Number of TrueSimmer burners x power in BTU Number of power burners x power in BTU Number of high burners x power in BTU True Simmer function GasStop Number and power rating of grill surface in BTU/h Width of broil surface in in.(mm) Depth of broil surface in in.(mm) User convenience Networking with Miele@home Precision knobs Illuminated knob ComfortSwivel handle Motorized lift-up control panel Sabbath program	4 1 x 12 500 BTU/hod. 1 x 13.60 2 x 19.50 1 x 19,000 11 1/4 (284) in (mm) 22 1/8 (560) in (mm) • • • •
Wireless Precision Probe Keep-warm function Crisp function Cooktop features Number of gas burners Number of TrueSimmer burners x power in BTU Number of power burners x power in BTU Number of high burners x power in BTU True Simmer function GasStop Number and power rating of grill surface in BTU/h Width of broil surface in in.(mm) Depth of broil surface in in.(mm) User convenience Networking with Miele@home Precision knobs Illuminated knob ComfortSwivel handle Motorized lift-up control panel Sabbath program MultiLingua	4 1 x 12 500 BTU/hod. 1 x 13.60 2 x 19.50 1 x 19,000 11 1/4 (284) in (mm) 22 1/8 (560) in (mm)
Wireless Precision Probe Keep-warm function Crisp function Cooktop features Number of gas burners Number of TrueSimmer burners x power in BTU Number of power burners x power in BTU Number of high burners x power in BTU True Simmer function GasStop Number and power rating of grill surface in BTU/h Width of broil surface in in.(mm) Depth of broil surface in in.(mm) User convenience Networking with Miele@home Precision knobs Illuminated knob ComfortSwivel handle Motorized lift-up control panel Sabbath program MultiLingua MyMiele	4 1 x 12 500 BTU/hod. 1 x 13.60 2 x 19.50 1 x 19,000 11 1/4 (284) in (mm) 22 1/8 (560) in (mm)
Wireless Precision Probe Keep-warm function Crisp function Cooktop features Number of gas burners Number of TrueSimmer burners x power in BTU Number of power burners x power in BTU Number of high burners x power in BTU True Simmer function GasStop Number and power rating of grill surface in BTU/h Width of broil surface in in.(mm) Depth of broil surface in in.(mm) User convenience Networking with Miele@home Precision knobs Illuminated knob ComfortSwivel handle Motorized lift-up control panel Sabbath program MultiLingua	• 4 1 x 12 500 BTU/hod. 1 x 13.60 2 x 19.50 • 1 x 19,000 11 1/4 (284) in (mm) 22 1/8 (560) in (mm) • • • • • • • • • • • • • • • • • • •



HR 1935-3 G DF GR 36 inch range

- the Dual Fuel all-rounder with M Touch for the highest demands.



EAN: 4002516486794 / Material number: 11791600 / Old Material Number: 25193581USA

Date display	•
Minute minder	•
Automatic switch-off	•
Programmable cooking time	•
Actual temperature display	•
Default temperatures	•
Acoustic signal when desired temperature is reached	•
Favorites	•
Individual settings	•
Timed bursts of steam	•
Door	
CleanGlass door	•
Door contact switch	•
SoftClose oven door/ SoftOpen	•
Cavity	
Oven cavity volume in cu. ft. (I)	5.76 (163) ft ³ (l)
Number of oven shelf levels	6
No. of halogen lamps	double
TwinPower hot air fans	•
Efficiency and sustainability	
Energy-saving lighting circuit	•
Automatic residual heat utilization	•
Rapid PreHeat	•
Cleaning convenience	
Stainless-steel front with partial Clean Touch Steel finish	•
Oven with self-cleaning program	•
AirClean catalyzer	•
Catalyzer	heated
ComfortClean dishwasher-safe grates	•
Cooktop surface	Black enamel
Safety	Black charrer
Appliance cooling system and cool touch front	•
Safety cut-out	•
System lock	•
Door contact switch	•
Door lock during self cleaning	•
Technical data	
Appliance height min in in.(mm)	37 1/8 (942)
Dimensions (depth) in in. (mm) with bullnose	27 3/4 (702)
Appliance height max in in.(mm)	38 5/8 (980)
Fresh water connection for Moisture Plus	00 0/0 (000)
Plumbed water connection for Moisture Plus	1.5
Appliance width in in. (mm)	36 1/8 (915)
Power Rating in V	120
Voltage in V	240/208
Number of phases	1
Fuse rating in A	30
Standard accessories	
	1
Anti-splash insert	- 1 2
Self Clean ready baking and roasting rack Self clean ready baking and roasting racks with rail system	
Och Goarready Daning and Todoling racks Will rall System	



Side racks self clean ready

HR 1935-3 G DF GR 36 inch range

- the Dual Fuel all-rounder with M Touch for the highest demands.




EAN: 4002516486794 / Material number: 11791600 / Old Material Number: 25193581USA

Míele


HR 1935-3 G DF GR

36 inch range


- the Dual Fuel all-rounder with M Touch for the highest demands.



HR1935G, HR1935-2, HR1935-3 (installation drawing)
E = Electric Connection, W = Water connection, G = Gas




HR19x4, HR193x, HR195x (installation drawing)




HR11xx, HR19xx, HR 17xx – Installation drawing 1 Anti-tip device , 2 Screws, 3 Locking nut


(x) = Toe-kick height adjustment 5" – 6 1/2" (127 mm – 165.1 mm)



HR11xx, HR19xx – Installation drawing
1 Anti-tip device , 2 Screws, 3 Locking nut



HR11xx, HR19xx, HR17xx – Installation drawing 1 Anti-tip device , 2 Screws, 3 Locking nut



HR11xx, HR19xx, HR17xx – Installation drawing


X 3 13/16" (97 mm): HR1124, HR1134, HR1135, HR1136, HR1724, HR1924, HR1934, HR1935, HR1936, HR1954, HR1955, HR1956, , X 3 1/4" (82 mm): HR1134-2, HR1134-3, HR1135-2, HR1135-3, HR1136-2, HR1136-3, HR1934-2, HR1924-2, HR1936-3, HR1936-2, HR1936-3, HR1935-2, HR1935-3, HR1956-2, HR1956-3, HR1956-3, HR1956-3, HR1956-3, HR1956-3

Míele


HR 1935-3 G DF GR

36 inch range

- the Dual Fuel all-rounder with M Touch for the highest demands.




HR11xx, HR19xx, HR17xx – Installation drawing 1 Toe kick cover , 2 Locking clamp




HR11xx, HR19xx, HR17xx – Installation drawing

1 Opening in the range housing , 2 Bolt of the anti-tip device , 3 Locking clamp with slot $\,$




HR19xx - Installation drawing

Maximum depth of top cabinet , Minimum distance to bottom edge of top cabinet , Distance from the floor to cooktop surface, Minimum distance to combustible surfaces , , E = Electric connection, W = Water connection, G = Gas connection , , (A) Width of cabinet opening, (B) Minimum distance between the top of the cooking area and the bottom of an unprotected combustible surface. Minimum distance to a protected combustible surface or when a Miele Ventilation Hood is installed. For all other Hoods please consult the manufacturer's specifications for required distances., (C) Maximum connection width right and left , (D) Maximum connection height , (E) Maximum connection depth




HR11xx, HR19xx, HR17xx – Installation drawing A = Distance between the rear of the range to the supporting wall



HR1924-3, HR1934-3, HR1935-3, HR1936-3, Side view, installation drawing

(x) = Toe-kick height adjustment 5" – 6 1/2" (127 mm – 165.1 mm)



HR11xx-3, HR14xx-3, HR16xx-3i, HR17xx-3, HR19xx-3 installation drawings


30", 20 %" / 527,6 mm, 16 5/8" / 422,6 mm, 2 ½" / 64 mm, 1 11/16" / 43 mm, 1 11/16" / 42,5 mm, 36", 28 9/16" / 725 mm, 22 5/8" / 575 mm, 2 ½" / 64 mm, 1 11/16" / 43 mm, 1 11/16" / 42,5 mm



HR 1935-3 G DF GR

36 inch range

- the Dual Fuel all-rounder with M Touch for the highest demands.



HR1924-3, HR1934-3, HR1935-3, HR1936-3, HR1954-3, HR1955-3, HR1956-3 (installation drawing)