

PWM 912 [EH DV DD]

Professional washing machine, external heating
with detergent drawer, M Touch Pro Plus – freely programmable.



- Drum volume 3.88 (110) ft³ (l), load size 25 (11.0) lb (kg)
- Top cleaning & consumption values – innovative Miele technology
- Ideal operation thanks to touch color display – M Touch Pro Plus
- Simple and safe operation thanks to automatic door lock
- Connected for the future using LAN and WiFi

EAN: 4002516444701 / Material number: 11803080 / Old Material Number: 51912059NAM

| Construction type and design | |
|--|------------------|
| Design | Front loader |
| Product line | Performance Plus |
| Front | Stainless Steel |
| Control panel color | Stainless Steel |
| Maximum load with a load ratio of 1:9 in lbs | 27 (12.0) |
| Load ratio | 1:9 |
| Load in lbs | 25 (11.0) |
| Drum volume in cubic feet (l) | 3.88 (110) |
| Door opening [Ø] in in.(mm) | 16 3/8 (415) |
| Door opening angle in degrees | 180 |
| Door hinging | right |
| Automatic door lock | • |
| Innovative suds container | • |
| Maintenance-free motor with frequency converter | • |
| Patented honeycomb drum 2.0 | • |
| Application | |
| Suitable for the hotel and catering industry | • |
| Suitable for senior living facilities | • |
| Suitable for facility management | • |
| Suitable for dry cleaners | • |
| Suitable for commercial laundries | • |
| Suitable for small businesses | • |
| Suitable for fire brigades and rescue services | • |
| Suitable for studs, riding schools and stables | • |
| Suitable for universities, nurseries, and schools | • |
| Suitable for hospitals | • |
| Suitable for camp sites | • |
| Suitable for sports clubs | • |
| Suitable for beauty salons, spas, and fitness centers | • |
| Suitable for the petrochemical industry | • |
| Suitable for amusement parks and holiday complexes | • |
| Suitable for public/community care facilities | • |
| Performance data | |
| Tested virucidal efficacy | • |
| Proven hygiene | • |
| Specific water consumption for hot water connection in l/kg | 5.90 |
| Specific energy consumption for hot water connection in kWh/lb | 0.02 |
| Water consumption for hot water connection in l | 70.8 |
| Water consumption for hot water connection in Mops standard program in gal | 133.6 |
| Energy consumption for hot water connection in kW | 0.27 |
| Program duration in minutes with hot water connection | 42 |
| Water consumption in ECO program for hot water connection in l | 68.4 |
| Energy consumption in ECO program for hot water connection in kWh | 0.19 |
| Program duration in minutes for ECO program with hot water connection | 31 |

PWM 912 [EH DV DD]

Professional washing machine, external heating
with detergent drawer, M Touch Pro Plus – freely programmable.



EAN: 4002516444701 / Material number: 11803080 / Old Material Number: 51912059NAM

| | |
|--|-----------------------------|
| Program runtime in minutes for Mops standard program with hot water connection | 43 |
| Residual moisture with cold rinse in % | 48 |
| Residual moisture with hot rinse in % | 44 |
| Residual moisture when processing cleaning cloths in % | 25 |
| Spin speed in rpm | 1150 |
| g factor | 458 |
| Tested operating hours | 30000 |
| Control | |
| Control system | M Touch Pro Plus |
| Programmability | Freely programmable |
| Max. delay start in h | Can be selected freely |
| Countdown indicator | • |
| Program sequence indicator | • |
| Choice of display language | • |
| Option to enter weight prior to start of program | • |
| Standard/target group programs | |
| Basic programmes | • |
| Dispensing | |
| Detergent dispenser drawer | 3 compartments |
| Maximum number of connections for liquid dispenser pumps [number] | 12 |
| Empty sensor | • |
| Standard electrical connection | |
| Type of heating | External heating |
| Electrical connection | 240V 60HZ 1 PH 3 WIRE |
| Total connected load in kW | 2.30 |
| Fuse rating in A | 20 |
| Water connection/drainage | |
| Cold water [number] | 3 x 1/2" hose w/ 3/4" union |
| Hot water [number] | 1 x 3/4" w/ 1" union |
| Hard water (optional) [number] | 2 x 1/2" w/ 3/4" union |
| Dump valve | DN 70 |
| Dimensions and weight | |
| External dimensions, net height in inches | 53 3/16 (1350) |
| External dimensions, net width in inches | 31 1/2 (799) |
| External dimensions, net depth in inches | 40 3/8 (1024) |
| External dimensions, gross height in inches | 58 5/16 (1480) |
| External dimensions, gross width in inches | 47 11/16 (1210) |
| External dimensions, gross depth in inches | 44 1/2 (1130) |
| Net weight in lbs.(kg) | 627 (284.0) |
| Gross weight in lbs. | 677 (307) |
| Maximum floor load in N/m ² | 4483 |
| Emission values | |
| Emissions – sound pressure at workplace | 65 dB(A) re 20 µPa |
| Heat dissipation into the room in BTU/h | 6.48 |
| Features | |
| Patented preliminary drainage | • |
| Patented cleaning cloth program | • |
| 3-dimensional imbalance monitoring | • |
| Efficient scoop-and-ladle ribs | • |

PWM 912 [EH DV DD]

Professional washing machine, external heating
with detergent drawer, M Touch Pro Plus – freely programmable.



EAN: 4002516444701 / Material number: 11803080 / Old Material Number: 51912059NAM

| | |
|--|-----|
| EcoSpeed | • |
| Spring-in-spring system | • |
| Temperature monitoring | • |
| Automatic load control Plus | • |
| Volumetric flow meter (optional) | • |
| Weighing base (optional) | • |
| Add laundry | • |
| Program selection via color frame | • |
| Emergency shut off | • |
| Appliance-independent accessories | • |
| Efficiency and sustainability | |
| Recycling rate in % | 91 |
| Connection options | |
| Payment system (optional) | • |
| Optical interface for service access | • |
| Peak-load negotiation/energy management (optional) | • |
| Water recovery (optional) | • |
| LAN | • |
| WiFi | • |
| Connector Box | • |
| Capacities | |
| Respirator masks [number] | 10 |
| Helmets [number] | 3 |
| Overalls [number] | 2 |
| Over jackets [number] | 3 |
| Chemical protection overalls [number] | 1 |
| Synthetic duvets [number] | 1 |
| Synthetic pillows [number] | 2 |
| Feather duvets [number] | 1 |
| Feather pillows [number] | 2 |
| Cloths, 22 g/0.8 oz[number] | 289 |
| Cotton mops, 40 cm/15.7 in[number] | 100 |
| Cotton mops, 50 cm/19.7 in[number] | 72 |
| Microfibre mops, 40 cm/15.7 in [number] | 102 |
| Microfibre mops, 50 cm/19.7 in [number] | 72 |
| Mops, office, 100 g [quantity] | 120 |
| Mops, stairway, 150 g [quantity] | 80 |
| Summer horse blankets [number] | 2 |
| Standards, test certificates, and symbols | |
| Splash protection IPX4 | • |
| c ETL US | • |
| Complies with Machinery Directive 2006/42/EC | • |