

H 7240 BM AM 24" compact speed oven

in a perfectly combinable design with automatic programs and combi modes.



- Clear-text display with sensor controls – DirectSensor S
- Easy cleaning cavity with linenweave pattern & PerfectClean
- Faster and more consistent results Quick & Gentle
- Network-enabled WiFi appliance Miele@home
- What you want is just a button away – Quick MW and Popcorn button

EAN: 4002516484554 / Material number: 11804510 / Old Material Number: 22724046USA

Design	
Appliance color	Clean Touch Steel
Construction type and design	
Built-in wall speed oven	•
PureLine	•
Convenience features	
Quick & Gentle	•
Rapid PreHeat	•
Operating modes	
Defrost	•
MasterChef automatic programs	•
Auto roast	•
Maxi Broil	•
Microwave	•
Combi Auto Roast	•
Combi Bake	•
Combi Broil	•
Convection Roast	•
User convenience	
Networking with Miele@home	•
Control panel	DirectSensor S
SoftOpen	•
SoftClose	•
3 in 1	Oven, Microwave, Oven
	with microwave function
MultiLingua	•
Popcorn function	•
Time of day display	•
Time synchronization	•
Minute minder	•
Programming start of cooking duration	•
Programming end of cooking duration	•
Programmable cooking time	•
Actual temperature display	•
Audible signal when desired temperature is reached	•
Default temperature	•
Recommended microwave power	•
Minute Plus button	•
Individual settings	•
Cleaning convenience	
Clean Touch Steel surface	•
Stainless-steel cavity with linen surface structure	•
Foldable broil heater element	•
CleanGlass door	•
Safety	
Appliance cooling system and cool touch front	•
Safety cut-out	•
System lock	•
Technical data	
Cavity volume in cu.ft (I)	1.52 (43)



H 7240 BM AM 24" compact speed oven in a perfectly combinable design with automatic programs and combi modes.



EAN: 4002516484554 / Material number: 11804510 / Old Material Number: 22724046USA

No. of rack levels	3
Number of shelf levels oven compartment 1	3
Number of shelf levels oven compartment 2	3
Oven interior lighting	1 LED spot
Temperatures in °F (°C)	85-475 (30-250)
Electronically controlled microwave power	•
Microwave power levels	1 - 7
Niche width min. in inches (mm)	22 1/8 (560)
Niche width max. in inches (mm)	22 3/8 (568)
Niche height min. in inches (mm)	17 3/4 (450)
Niche height max. in inches (mm)	17 7/8 (452)
Niche depth in in. (mm)	21 3/4 (550)
Appliance width in in. (mm)	23 1/2 (595)
Appliance height in in. (mm)	18 (456)
Appliance depth in in. (mm)	22 5/8 (572)
Weight in lbs. (kg)	94 (42.5)
Weight in lbs. (kg)	93.7 (42.5)
Weight in lbs. (kg)	94 (42.5)
Total connected load in kW	3.40
Power Rating in V	120
Voltage in V	240/208
Frequency in Hz	60
Fuse rating in A	30
Number of phases	1
Connection wire with plug	•
Length of power cord in in. (m)	1.80
Standard accessories	
Wire rack with PerfectClean	1
Glass tray	1
Available display languages	
Available display languages via MultiLingua	bahasa malaysia, dansk, deutsch, english, español,


deutsch, english, español, français, hrvatski, italiano, magyar, nederlands, norsk, polski, português, pycский, română, slovenčina, slovenščina, srpski, suomi, svenska, türkçe, українська, čeština, ελληνικά, , , ,

,


H 7240 BM AM

24" compact speed oven

in a perfectly combinable design with automatic programs and combi modes.




side view 30 inch Flush inset 450S, installation drawing, NA 7/8"-22* mm – Glas, 15/16"-23.3** mm – Edelstahl




side view 30 inch Flush inset built-under 450S, installation drawing, NA






installation 30 inch Flush inset built-under wide front, installation drawing, NA

7/8" - 22* mm - Glas, 15/16" - 23.3** mm - Edelstahl




installation 30 inch Flush inset 450S, installation drawing, NA

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance, E = Electric connection



installation 30 inch Flush inset built-under 450S, installation drawing, NA

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance, E = Electric connection,




installation 30 inch Flush inset wide front 450S, installation drawing, NA

H 7240 BM AM

24" compact speed oven


in a perfectly combinable design with automatic programs and combi modes.






installation 30 inch Flush inset built-under wide front 450S, installation drawing, NA

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection,




side view 30 inch Proud 450S, installation drawing, NA 7/8" - 22* mm - Glas, 15/16" - 23.3** mm - Edelstahl



side view 30 inch Proud built-under 450S, installation drawing, NA


7/8" - 22* mm - Glas, 15/16" - 23.3** mm - Edelstahl





installation 30 inch Proud 450S, installation drawing, NA


A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance, E = Electric connection





installation 30 inch Proud built-under 450S, installation drawing, NA

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, – Electrical and water supplies are recommended to be placed in adjacent cabinetry. Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection,






installation 30 inch Proud wide front 450S, installation drawing, NA

H 7240 BM AM


24" compact speed oven

in a perfectly combinable design with automatic programs and combi modes.




installation 30 inch Proud built-under wide front 450S, installation drawing, NA

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection,




H 6x00 BM + EBA 6808, H7xxx, EBA7848 Combi, Installation drawing, Flush inset, NA

7/8" - 22* mm - Glas, 15/16" - 23.3** mm - Edelstahl




DGC 6x00-1 + EBA 6808, H 6x00 BM + EBA 6808, DGC7xxx, H7xxx, EBA7848 Combi, Installation drawing, Flush inset, NA

7/8" - 22* mm - Glas, 15/16" - 23.3** mm - Edelstahl




DGC 6x6x (AM)+EBA 6808, H 6x00+EBA 6808, DGC 786x, EBA78x8, H7xxx Combi, Install. drawing, Flush inset Flush inset NA

7/8" - 22* mm - Glas, 15/16" - 23.3** mm - Edelstahl



H 6560 B + EBA 6808, H 6x60 BP + EBA 6808, H 6x00 BM + EBA 6808, H7xxx, EBA 78x8 Combi, Install drawing, Flush inset, NA

7/8" - 22* mm - Glas, 15/16" - 23.3** mm - Edelstahl




H 6x00 BM + EBA 6808, H 7x40BM, EBA 7848 Installation Combi, Installation drawing, Flush inset, NA $\,$

H 7240 BM AM


24" compact speed oven

in a perfectly combinable design with automatic programs and combi modes.




H 6560 B + EBA 6808, H 6x60 BP + EBA 6808, H 6x00 BM, H 7xxx, EBA 78x8, Installation drawing, Flush inset, NA

 $A-Cut\mbox{-}out (4" \times 28" \mbox{'}/100 \mbox{ mm} \times 720 \mbox{ mm}) in the bottom of the cabinet for power cord and ventilation, – Electrical and water supplies are recommended to be placed in adjacent cabinetry. Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., <math display="inline">E=Electric \mbox{ connection}$




DGC6x6x(AM) + EBA6808, H6x00+EBA6808, DGC786x+EBA7868, H7x40BM+EBA7848, Combi, Installation drawing, Proud, Flush inset, NA

7/8" - 22* mm - Glas, 15/16" - 23.3** mm - Edelstahl




H 6560 B + EBA 6808, H 6x60 BP, H 6x00 BM, H 7xxx BM/BP, EBA 78x8, Installation drawing, Flush inset, NA

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection




H 6x00 BM + EBA 6808, H7x40BM(+EBA7848), Combi, Installation drawing, Proud, NA

7/8" - 22* mm - Glas, 15/16" - 23.3** mm - Edelstahl



DGC 6x00-1 + EBA6808, H 6x00 BM+EBA 6808, DGC7x4x(+EBA7848), H7x40BM(+EBA7848), Combi, Installation drawing, Proud, NA

7/8" - 22* mm - Glas, 15/16" - 23.3** mm - Edelstahl




H 6560 B + EBA 6808, H 6x60 BP + EBA 6808, H 6x00 BM + EBA 6808, H7xxx+EBA7x7x, Combi, Installation drawing, Proud, NA

7/8" - 22* mm - Glas, 15/16" - 23.3** mm - Edelstahl

H 7240 BM AM

24" compact speed oven


in a perfectly combinable design with automatic programs and combi modes.





H 6x00 BM + EBA 6808, H7x40BM(+EBA7848) NA7000 Installation Combi, Installation drawing, Proud, NA


A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection





H 6560 B + EBA 6808, H 6x60 BP + EBA6808, H6x00BM + EBA6808, NA7000 Installation Combi, Installation drawing, Proud, NA


A - Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, - Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., $\mathsf{E} = \mathsf{Electric}$ connection






H 6x00 BM + EBA 6808, H7x40BM (+EBA7848), Installation Combi wide front, Installation drawing, Proud,

A - Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., $\mathsf{E} = \mathsf{Electric}$ connection






(H6560B, H6x60BP, H6x00BM) + EBA6808, NA7000Installation Combi wide front, Installation drawing, Proud, NA



installation Proud 450S, installation drawing, NA




installation Proud built-under 450S, installation drawing, NA


H 7240 BM AM

24" compact speed oven


in a perfectly combinable design with automatic programs and combi modes.



installation Proud wide front 450S, installation drawing, NA




installation Proud build-under wide front 450S, installation drawing, NA




installation Flush inset built-under 450S, installation drawing, NA

 $7/8^{\prime\prime}$ – 22^{\star} mm – Glass, 15/16" – $23.3^{\star\star}$ mm – Stainless steel




installation Flush inset wide front 450S, installation drawing, $\ensuremath{\mathsf{NA}}$

 $7/8^{\prime\prime}$ – 22^{\star} mm – Glass, 15/16" – 23.3** mm – Stainless steel




installation Flush inset build-under wide front 450S, Skizze, NA $\,$

 $7/8^{\prime\prime}$ – 22^{\star} mm – Glass, 15/16" – 23.3** mm – Stainless steel




DGC7x4x, H7x40BM, Einbau, 30 Zoll, Flush inset, combi

 $7/8^{\prime\prime}$ – 22^{\star} mm – Glass, 15/16" – 23.3** mm – Stainless steel




DGC7x40, DGC7485, H7x40BM, ESW7x10, EVS7010, Einbau 30 Zoll, Flush inset, combi, 450S

7/8``-22'' mm – Glass, 15/16" – 23.3** mm – Stainless



DGC7x4x, H7x40BM, H7x6xBP, Einbau, 30 Zoll Flush inset, combi, 650S, 450S

7/8" – 22* mm – Glass, 15/16" – 23.3** mm – Stainless steel




DGC7x4x, DGC7485, H7x40BM, Einbau, 30 Zoll, Flush inset, combi, wide front, 450S

7/8" - 22* mm - Glass, 15/16" - 23.3** mm - Stainless

H 7240 BM AM


24" compact speed oven

in a perfectly combinable design with automatic programs and combi modes.




DGC7xxx, H7x40BM, ESW7x10, EVS7010, Einbau, 30 Zoll, Flush inset, combi, wide front, 450S

 $7/8^{\prime\prime}$ – 22^{\star} mm – Glass, 15/16" – 23.3** mm – Stainless steel




DGC7xxx, H7x40BM, H7x6xBP, Einbau, 30 Zoll, Flush inset, combi, wide front, 650S, 450S

7/8" - 22* mm - Glass, 15/16" - 23.3** mm - Stainless




DGC7xxx+EBA7848, H7x40BM (+EBA7848), Installation, 30 Zoll, Flushinset, combi, XL, 450S

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection




DGC786x(+EBA7848), H7x40BM(+EBA7848), Installation, 30 Zoll, Flush inset, combi, XXL, 450S

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection



DGC7x40(+EBA7848), H7x40BM(+EBA7848), H7840+EBA6808, Installation, 30 Zoll, flush inset, combi, wide front, XL, 450S

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection




DGC786x+EBA7868, H7x40BM(+EBA7848), Installation, 30 Zoll, Flush inset, combi, wide front, XXL, 450S

H 7240 BM AM


24" compact speed oven

in a perfectly combinable design with automatic programs and combi modes.




 $\mbox{H7x40BM}$ (+EBA7848), Installation, 30 Zoll, Flush inset, combi, wide front, 450S

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance, E = Electric connection




H7x40BM+EBA7848, ESW7x10, EVS7010, side view, 30 Zoll, Proud, combi, 450S

7/8" - 22* mm - Glass, 15/16" - 23.3** mm - Stainless




DDGC7xxx, H7x40BM, Einbau, 30 Zoll, Proud, combi, 450S

7/8``-22'` mm – Glass, 15/16" – 23.3** mm – Stainless steel




DGC7xxx, H7x40BM, ESW7x10, EVS, Einbau, 30 Zoll, Proud, combi, 450S

7/8" - 22* mm - Glass, 15/16" - 23.3** mm - Stainless



DGC7xxx, H7x4xBM, H7x6xBP, Einbau, 30 Zoll, Proud, combi, 650S, 450S

7/8" - 22* mm - Glass, 15/16" - 23.3** mm - Stainless




DGC7x4x, H7x40BM, Einbau, 30 Zoll, Proud, combi, wide front, 450S


H 7240 BM AM

24" compact speed oven


in a perfectly combinable design with automatic programs and combi modes.



DGC7x4x, H7x40BM, ESW7x10, EVS7010, Einbau, 30 Zoll, Proud, combi, wide front, 450S




DGC7x4x, H7x40Bm, H7x6xBP, Einbau, 30 Zoll, Proud, combi, wide front, 650S, 450S




DGC7x4x(+EBA7848), H7x40BM(+EBA7848), Installation, 30 Zoll, Proud, combi, XL, 450S

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection




DGC786x(+EBA7848), H7x40BM(+EBA7848), Installation, 30 Zoll, Proud, combi, XXL, 450S

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection



DGC7x4x(+EBA7848), H7x40BM(+EBA7848), Installation, 30 Zoll, Proud, combi, wide front XL, 450S

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, – Electrical and water supplies are recommended to be placed in adjacent cabinetry. Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection






DGC786x(+EBA7848), H7x40BM(+EBA7848), Installation, 30 Zoll, Proud, combi, wide front, XXL, 450S



H 7240 BM AM


24" compact speed oven

in a perfectly combinable design with automatic programs and combi modes.



Handle H72xx, H76xx, H78xx, PureLine – NA7000 - Installation drawing

H2880BP, H7270BM, H7670BM, H7870BM, H7280BP, H7680BP, H7880BP, H7880BP2:, 19 11/16" / 500 mm, 17 1/2" / 444 mm, 1 7/8" / 47 mm, 15/16" / 24 mm, 11/4" / 32,5 mm, 2 9/16" / 65 mm, H7240BM, H7640BM, H7840BM, H7263BP, H7660BP:, 15 3/4" / 400 mm, 14 3/16" / 32,5 mm, 2 9/16" / 65 mm



installation Flush inset 450S, installation drawing, NA

 $7/8"-22"\,mm-Glass,\,15/16"-23.3"^*\,mm-Stainless$ steel, DGC: Minimum installation height $36"-914\,mm$ from floor to the device installation surface