

Triflex HX1 Facelift
Cordless stick vacuum cleaner
Triflex HX1 with 3-in-1 design for exceptional flexibility



- Up to 60 minutes of cleaning* with a single charge
- As powerful as a conventional Miele vacuum cleaner**
- Hygiene Lifetime filter with >99.99%*** dust retention capacity
- Wide Electrobrush with automatic flooring recognition

* Valid for power level 1 without connected Multi Floor XXL Electrobrush.

** Cleaning performance compared with a Miele Complete C3 Canister Vacuum Cleaner (SGEF3) with STB 305-3 Turbobrush (dust pickup from carpet and hard floor with crevices, fiber pickup from carpet). In accordance with IEC 62885-2.

*** IEC 62885-4

EAN: 4002516452898 / Material number: 11826980 / Old Material Number: 41MUL105USA

| Design | |
|--|-------------------------|
| Cordless stick vacuum cleaner | • |
| Product line | Triflex HX1 |
| Product type | SMUL1 |
| Appliance color | Obsidian black |
| Cleaning | |
| Vortex Technology | • |
| Electric brush Multi Floor XXL SEB 430 | • |
| User convenience | |
| Electronic suction power setting | 3-level slide control |
| Exchangeable Li-Ion battery | • |
| 3 in 1 - Function | • |
| Filter system | |
| ComfortClean | • |
| Exhaust filter | Hygiene lifetime filter |
| Dustbag volume in cu. ft. (l) | 0.02 (0.5) |
| Technical data | |
| Battery type | Li-ion |
| Nominal battery capacity in mAh | 2500 |
| Volume in dB | 80.0 |
| Width in inches (mm) | 10 1/4 (260) |
| Height in inch (mm) | 1297 |
| Weight in lbs (kg) | 8 (3.6) |
| Volt | 25,2 |
| Running time MIN-stage PowerUnit solo | 60 |
| Running time MIN-stage with electrical accessories | 30 |
| Running time MAX-stage with electrical accessories | 17 |
| Cleaning area in m ² | 125 |
| Recharging time in min. | 240 |
| Nominal power consumption in W | 120 |
| Standard accessories | |
| Three-piece accessory set | Integrated wall bracket |
| Crevice nozzle | • |
| Dusting brush with synthetic bristles | • |
| Upholstery nozzle XXL SPD 20 | • |
| Electric brush Multi Floor XXL SEB 430 | • |
| Cleaning brush | No |
| Wall Mount | • |
| Power supply unit | • |