

Triflex HX2 Runner

Cordless stick vacuum cleaner

Consistently high suction power | up to 60+60 min runtime | automatic floor detection



- Electrobrush with LED light and automatic flooring detection
- 99.999%* dust retention capacity with HEPA* filter
- Miele's most powerful vacuum cleaner**
- Patented*** 3-in-1 design for versatile cleaning
- Two VARTA batteries for up to 2 x 60 minutes of cleaning****

* IEC 62885-4

** Cleaning performance compared with a Miele Complete C3 Canister Vacuum Cleaner (SGEF3) with STB 305-3 Turbobrush (dust pickup from carpet and hard floor with crevices, fiber pickup from carpet). In accordance with IEC 62885-2.

*** Patent: DE 10 2016 105 475 B4

**** Valid for power level 1 without connected Multi Floor XXL Electrobrush

EAN: 4002516453055 / Material number: 11827050 / Old Material Number: 41OML531USA

Design	
Cordless stick vacuum cleaner	•
Product line	Triflex HX2
Product type	SOML5
Construction type and design	
Color	Obsidian black
Cleaning	
Vortex Technology	•
Electric brush Multi Floor XXL SEB 435 with BrilliantLight	•
User convenience	
Electronic suction power setting	3-level slide control
Exchangeable Li-Ion battery	•
3 in 1 - Function	•
Filter system	
ComfortClean	•
Exhaust filter	HEPA lifetime filter
Dustbag volume in cu. ft. (l)	0.02 (0.5)
Technical data	
Battery type	Li-ion
Nominal battery capacity in mAh	2500
Volume in dB	77.0
Width in inches (mm)	10 1/4 (260)
Height in inch (mm)	1297
Weight in lbs (kg)	8 (3.6)
Volt	25,2
Running time MIN-stage PowerUnit solo	2 x 60
Running time MIN-stage with electrical accessories	2 x 30
Running time MAX-stage with electrical accessories	2 x 14
Cleaning area in m ²	2 x 125
Recharging time in min.	240
Power rating in W	192
Standard accessories	
Three-piece accessory set	Integrated wall bracket
Crevice nozzle	•
Dusting brush with synthetic bristles	•
Upholstery nozzle XXL SPD 20	•
Electric brush Electro Compact SEB 23	•
Electric brush Multi Floor XXL SEB 435 with BrilliantLight	•
Cleaning brush	No
Wall Mount	•
Power supply unit	•
Additional battery	•